

ULTRA FOAM WASH – 20L

Version 1.2 Revision Date: 23.08.2019 SDS Number: 3951502-00003 Date of last issue: 29.05.2019
Date of first issue: 18.01.2019

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Product name : ULTRA FOAM WASH – 20L

Product code : 0893 039 020

Manufacturer or supplier's details

Company : Wurth Australia Pty Ltd

Address : 2/1 Healey Road
Dandenong South, Victoria, 3175

Telephone : +61 3 8788 1111

Emergency telephone number : 1300 657 765. Advisory office in case of poisoning - National Poisons Centre: 131 126

E-mail address : prodsafe@wurth.com

Recommended use of the chemical and restrictions on use

Recommended use : Washing and cleaning products (including solvent based products)
Detergent

SECTION 2. HAZARDS IDENTIFICATION**GHS Classification**

Serious eye damage/eye irritation : Category 1

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H318 Causes serious eye damage.

Precautionary statements : **Prevention:**
P280 Wear eye protection/ face protection.

Response:
P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor/ physician.

ULTRA FOAM WASH – 20L

Version Revision Date: SDS Number: Date of last issue: 29.05.2019
1.2 23.08.2019 3951502-00003 Date of first issue: 18.01.2019

Other hazards which do not result in classification

None known.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Sodium dodecylbenzene sulfonate	25155-30-0	>= 3 -< 10

SECTION 4. FIRST AID MEASURES

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water.
Remove contaminated clothing and shoes.
Get medical attention.
Wash clothing before reuse.
Thoroughly clean shoes before reuse.
- In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.
If easy to do, remove contact lens, if worn.
Get medical attention immediately.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Causes serious eye damage.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.

SECTION 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

- Dry chemical
- Unsuitable extinguishing media : None known.
- Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Carbon oxides
Sulphur oxides
Metal oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.
- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.
-

SECTION 6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Follow safe handling advice and personal protective equipment recommendations.
- Environmental precautions : Discharge into the environment must be avoided.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.
-

SECTION 7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Do not get on skin or clothing.
Avoid inhalation of vapour or mist.
Do not swallow.
Do not get in eyes.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Keep container tightly closed.
Take care to prevent spills, waste and minimize release to the environment.
- Hygiene measures : Ensure that eye flushing systems and safety showers are located close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.
- Conditions for safe storage : Keep in properly labelled containers.
Keep tightly closed.
Store in accordance with the particular national regulations.
- Materials to avoid : Do not store with the following product types:
Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Components with workplace control parameters**

Contains no substances with occupational exposure limit values.

- Engineering measures** : Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

- Respiratory protection : Use respiratory protection unless adequate local exhaust ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.
- Filter type : Particulates type
- Hand protection
- Material : Nitrile rubber
 - Break through time : 200 min
 - Glove thickness : 0.38 mm

- Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

- aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.
- Eye protection : Wear the following personal protective equipment:
Chemical resistant goggles must be worn.
If splashes are likely to occur, wear:
Face-shield
- Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : liquid
- Colour : red
- Odour : slight
- Odour Threshold : No data available
- pH : 7.3 - 7.7
- Melting point/freezing point : -4 °C
- Initial boiling point and boiling range : 103 °C
- Flash point : No data available
- Evaporation rate : No data available
- Flammability (solid, gas) : Not applicable
- Flammability (liquids) : Does not sustain combustion.
- Upper explosion limit / Upper flammability limit : No data available
- Lower explosion limit / Lower flammability limit : No data available
- Vapour pressure : No data available
- Relative vapour density : No data available
- Density : 1.07 g/cm³ (20 °C)

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Solubility(ies)
Water solubility : completely miscible

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, kinematic : No data available

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle size : Not applicable

SECTION 10. STABILITY AND REACTIVITY

Reactivity : Not classified as a reactivity hazard.

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : Can react with strong oxidizing agents.

Conditions to avoid : None known.

Incompatible materials : Oxidizing agents

Hazardous decomposition products : No hazardous decomposition products are known.

SECTION 11. TOXICOLOGICAL INFORMATION

Exposure routes : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity : Acute toxicity estimate: > 2,000 mg/kg
Method: Calculation method

Components:

Sodium dodecylbenzene sulfonate:

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Acute oral toxicity : LD50 (Rat): 500 - 2,000 mg/kg
Method: OECD Test Guideline 401

Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 402
Remarks: Based on data from similar materials

Skin corrosion/irritation

Not classified based on available information.

Components:**Sodium dodecylbenzene sulfonate:**

Species : Rabbit
Method : OECD Test Guideline 404
Result : Skin irritation
Remarks : Based on data from similar materials

Serious eye damage/eye irritation

Causes serious eye damage.

Components:**Sodium dodecylbenzene sulfonate:**

Species : Rabbit
Result : Irreversible effects on the eye
Method : OECD Test Guideline 405
Remarks : Based on data from similar materials

Respiratory or skin sensitisation**Skin sensitisation**

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:**Sodium dodecylbenzene sulfonate:**

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative
Remarks : Based on data from similar materials

Chronic toxicity**Germ cell mutagenicity**

Not classified based on available information.

Components:**Sodium dodecylbenzene sulfonate:**

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Test Type: Chromosome aberration test in vitro
Method: OECD Test Guideline 473
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

Carcinogenicity

Not classified based on available information.

Components:**Sodium dodecylbenzene sulfonate:**

Species : Rat
Application Route : Ingestion
Exposure time : 2 Years
Result : negative
Remarks : Based on data from similar materials

Reproductive toxicity

Not classified based on available information.

Components:**Sodium dodecylbenzene sulfonate:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 422
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Repeated dose toxicity

Components:

Sodium dodecylbenzene sulfonate:

Species	:	Rat
NOAEL	:	100 mg/kg
LOAEL	:	200 mg/kg
Application Route	:	Ingestion
Exposure time	:	54 Days
Method	:	OECD Test Guideline 422
Remarks	:	Based on data from similar materials

Aspiration toxicity

Not classified based on available information.

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

Components:

Sodium dodecylbenzene sulfonate:

Toxicity to fish	:	LC50 (Oncorhynchus mykiss (rainbow trout)): 3.2 - 5.6 mg/l Exposure time: 96 h Method: OECD Test Guideline 203
Toxicity to daphnia and other aquatic invertebrates	:	EC50 (Daphnia magna (Water flea)): 6.3 mg/l Exposure time: 48 h
Toxicity to algae/aquatic plants	:	ErC50 (Pseudokirchneriella subcapitata (green algae)): 65.3 mg/l Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials
		NOEC (Pseudokirchneriella subcapitata (green algae)): 7.9 mg/l Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: Based on data from similar materials
Toxicity to fish (Chronic toxicity)	:	NOEC (Pimephales promelas (fathead minnow)): 0.9 mg/l Exposure time: 28 d Remarks: Based on data from similar materials
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	:	NOEC (Daphnia magna (Water flea)): 1.65 mg/l Exposure time: 21 d Method: OECD Test Guideline 211
Toxicity to microorganisms	:	EC50: 500 - 723 mg/l Exposure time: 3 h Method: OECD Test Guideline 209 Remarks: Based on data from similar materials

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Persistence and degradability**Components:****Sodium dodecylbenzene sulfonate:**

Biodegradability : Result: Readily biodegradable.
Biodegradation: > 60 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Bioaccumulative potential**Components:****Sodium dodecylbenzene sulfonate:**

Bioaccumulation : Species: Pimephales promelas (fathead minnow)
Bioconcentration factor (BCF): 87
Remarks: Based on data from similar materials

Partition coefficient: n-
octanol/water : log Pow: 1.96

Mobility in soil

No data available

Other adverse effects

No data available

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.

SECTION 14. TRANSPORT INFORMATION**International Regulations****UNRTDG**

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

National Regulations**ADG**

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION**Safety, health and environmental regulations/legislation specific for the substance or mixture**Standard for the Uniform : No poison schedule number allocated
Scheduling of Medicines and
PoisonsProhibition/Licensing Requirements : There is no applicable prohibition or
notification/licensing requirements,
including for carcinogens under
Commonwealth, State or Territory
legislation.**The components of this product are reported in the following inventories:**

AICS : All ingredients listed or exempt.

SECTION 16. OTHER INFORMATION**Further information**

Revision Date : 23.08.2019

Sources of key data used to : Internal technical data, data from raw material SDSs, OECD
compile the Safety Data eChem Portal search results and European Chemicals Agen-
Sheet cy, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

Full text of other abbreviations

AICS - Australian Inventory of Chemical Substances; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemi-

ULTRA FOAM WASH – 20L

Version	Revision Date:	SDS Number:	Date of last issue: 29.05.2019
1.2	23.08.2019	3951502-00003	Date of first issue: 18.01.2019

cal Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

AU / EN