

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : MARKING SOLUTION BLACK - 100 ML
Product code : 0893984801

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub- : Processing aid
stance/Mixture : Professional use product

1.3 Details of the supplier of the safety data sheet

Company : Adolf Wuerth GmbH & Co. KG
Reinhold-Würth-Str. 12-17
74653 Künzelsau

Telephone : +49 794015 0

Telefax : +49 794015 10 00

E-mail address of person : prodsafe@wuerth.com
responsible for the SDS

1.4 Emergency telephone number

+49 (0)6132 – 84463

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

Additional Labelling

EUH210 Safety data sheet available on request.

2.3 Other hazards

None known.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version 4.5 Revision Date: 18.12.2020 SDS Number: 1092994-00005 Date of last issue: 05.11.2020
Date of first issue: 11.06.2010

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
Citric acid	77-92-9 201-069-1	Eye Irrit. 2; H319	>= 1 - < 10

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- Protection of first-aiders : No special precautions are necessary for first aid responders.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

None known.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically and supportively.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : Not applicable
Will not burn
- Unsuitable extinguishing media : Not applicable
Will not burn

5.2 Special hazards arising from the substance or mixture

- Specific hazards during fire- : Exposure to combustion products may be a hazard to health.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

fighting

Hazardous combustion products : Carbon oxides
Metal oxides
Chlorine compounds

5.3 Advice for firefighters

Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version 4.5 Revision Date: 18.12.2020 SDS Number: 1092994-00005 Date of last issue: 05.11.2020
Date of first issue: 11.06.2010

SECTION 7: Handling and storage

7.1 Precautions for safe handling

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Take care to prevent spills, waste and minimize release to the environment.
- Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

- Requirements for storage areas and containers : Keep in properly labelled containers. Store in accordance with the particular national regulations.
- Advice on common storage : No special restrictions on storage with other products.
- Storage class (TRGS 510) : 12, Non Combustible Liquids

7.3 Specific end use(s)

- Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Citric acid	77-92-9	AGW (Inhalable fraction)	2 mg/m ³	DE TRGS 900
Peak-limit: excursion factor (category): 2;(I)				
Further information: Senate commission for the review of compounds at the work place dangerous for the health (MAK-commission)., When there is compliance with the OEL and biological tolerance values, there is no risk of harming the unborn child				

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value
Sodium chloride	Workers	Inhalation	Long-term systemic	2068,62

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version 4.5 Revision Date: 18.12.2020 SDS Number: 1092994-00005 Date of last issue: 05.11.2020
Date of first issue: 11.06.2010

			effects	mg/m3
	Workers	Inhalation	Acute systemic effects	2068,62 mg/m3
	Workers	Skin contact	Long-term systemic effects	295,52 mg/kg bw/day
	Workers	Skin contact	Acute systemic effects	295,52 mg/kg bw/day
	Consumers	Inhalation	Long-term systemic effects	443,28 mg/m3
	Consumers	Inhalation	Acute systemic effects	443,28 mg/m3
	Consumers	Skin contact	Long-term systemic effects	126,65 mg/kg bw/day
	Consumers	Skin contact	Acute systemic effects	126,65 mg/kg bw/day
	Consumers	Ingestion	Long-term systemic effects	126,65 mg/kg bw/day
	Consumers	Ingestion	Acute systemic effects	126,65 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
Citric acid	Fresh water	0,44 mg/l
	Marine water	0,044 mg/l
	Sewage treatment plant	1000 mg/l
	Fresh water sediment	34,6 mg/kg dry weight (d.w.)
	Marine sediment	3,46 mg/kg dry weight (d.w.)
	Soil	33,1 mg/kg dry weight (d.w.)
Sodium chloride	Fresh water	5 mg/l
	Sewage treatment plant	500 mg/l
	Soil	4,86 mg/kg dry weight (d.w.)

8.2 Exposure controls

Engineering measures

Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye protection : Please follow all applicable local/national requirements when selecting protective measures for a specific workplace.

Wear the following personal protective equipment:
Safety glasses

Always wear eye protection when the potential for inadvertent eye contact with the product cannot be excluded.

Equipment should conform to DIN EN 166

Hand protection

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

Remarks	:	Wash hands before breaks and at the end of workday.
Skin and body protection	:	Skin should be washed after contact.
Respiratory protection	:	If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection. Equipment should conform to DIN EN 143
Filter type	:	Particulates type (P)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance	:	liquid
Colour	:	colourless
Odour	:	odourless
Odour Threshold	:	No data available
pH	:	No data available
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	No data available
Flash point	:	> 60 °C
Evaporation rate	:	No data available
Flammability (solid, gas)	:	Not applicable
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Density	:	1,065 g/cm ³
Solubility(ies) Water solubility	:	completely soluble
Partition coefficient: n-octanol/water	:	Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

Auto-ignition temperature : > 60 °C

Decomposition temperature : No data available

Viscosity
Viscosity, kinematic : No data available

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

9.2 Other information

Flammability (liquids) : No data available

Particle size : Not applicable

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : None known.

10.4 Conditions to avoid

Conditions to avoid : None known.

10.5 Incompatible materials

Materials to avoid : None.

10.6 Hazardous decomposition products

No hazardous decomposition products are known.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version 4.5 Revision Date: 18.12.2020 SDS Number: 1092994-00005 Date of last issue: 05.11.2020
Date of first issue: 11.06.2010

Components:

Citric acid:

Acute oral toxicity : LD50 (Mouse): 5.400 mg/kg

Acute dermal toxicity : LD50 (Rat): > 2.000 mg/kg
Method: OECD Test Guideline 402
Assessment: The substance or mixture has no acute dermal toxicity

Skin corrosion/irritation

Not classified based on available information.

Components:

Citric acid:

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Components:

Citric acid:

Species : Rabbit
Method : OECD Test Guideline 405
Result : Irritation to eyes, reversing within 21 days

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Components:

Citric acid:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Test Type: in vitro micronucleus test
Result: positive

Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mutagenicity (in vivo mammalian bone-marrow)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

cytogenetic test, chromosomal analysis)
Species: Rat
Application Route: Ingestion
Result: negative

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

Components:

Citric acid:

Effects on foetal development : Test Type: One-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Result: negative

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Repeated dose toxicity

Components:

Citric acid:

Species : Rat
NOAEL : 4.000 mg/kg
LOAEL : 8.000 mg/kg
Application Route : Ingestion
Exposure time : 10 Days

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

Components:

Citric acid:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): > 100 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 1.535 mg/l
Exposure time: 24 h

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

12.2 Persistence and degradability

Components:

Citric acid:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 97 %
Exposure time: 28 d
Method: OECD Test Guideline 301B

12.3 Bioaccumulative potential

Components:

Citric acid:

Partition coefficient: n-octanol/water : log Pow: -1,72

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Not relevant

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.
According to the European Waste Catalogue, Waste Codes are not product specific, but application specific.
Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.

Waste Code : The following Waste Codes are only suggestions:

used product
06 03 14, solid salts and solutions other than those mentioned in 06 03 11 and 06 03 13

unused product
06 03 14, solid salts and solutions other than those mentioned in 06 03 11 and 06 03 13

uncleaned packagings
15 01 06, mixed packaging

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

Acc. Packaging Act properly emptied packaging:
Properly emptied, non-contaminated packaging of non-hazardous products can be supplied to a system for the collection of sales packaging.

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Water contaminating class : WGK 1 slightly hazardous to water
(Germany) Classification according to AwSV, Annex 1 (5.2)

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 0 %

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

Other information : Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

Full text of H-Statements

H319 : Causes serious eye irritation.

Full text of other abbreviations

Eye Irrit. : Eye irritation
DE TRGS 900 : Germany. TRGS 900 - Occupational exposure limit values.
DE TRGS 900 / AGW : Time Weighted Average

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION BLACK - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 05.11.2020
4.5	18.12.2020	1092994-00005	Date of first issue: 11.06.2010

tative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

DE / EN