

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : MARKING SOLUTION WHITE - 100 ML
Product code : 0893984802

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-
stance/Mixture : Processing aid
Professional use product

1.3 Details of the supplier of the safety data sheet

Company : Adolf Wuerth GmbH & Co. KG
Reinhold-Würth-Str. 12-17
74653 Künzelsau

Telephone : +49 794015 0
Telefax : +49 794015 10 00

E-mail address of person
responsible for the SDS : prodsafe@wuerth.com

1.4 Emergency telephone number

+49 (0)6132 – 84463

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.3 Other hazards

None known.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components
Remarks : No hazardous ingredients

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

SECTION 4: First aid measures

4.1 Description of first aid measures

- Protection of first-aiders : No special precautions are necessary for first aid responders.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

None known.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically and supportively.
-

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : Not applicable
Will not burn
- Unsuitable extinguishing media : Not applicable
Will not burn

5.2 Special hazards arising from the substance or mixture

- Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Metal oxides
Chlorine compounds

5.3 Advice for firefighters

- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use only with adequate ventilation.

Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : If exposure to chemical is likely during typical use, provide eye

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version 3.9 Revision Date: 18.12.2020 SDS Number: 1096077-00005 Date of last issue: 20.08.2020
Date of first issue: 11.06.2010

flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store in accordance with the particular national regulations.

Advice on common storage : No special restrictions on storage with other products.

Storage class (TRGS 510) : 12, Non Combustible Liquids

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value
Sodium chloride	Workers	Inhalation	Long-term systemic effects	2068,62 mg/m ³
	Workers	Inhalation	Acute systemic effects	2068,62 mg/m ³
	Workers	Skin contact	Long-term systemic effects	295,52 mg/kg bw/day
	Workers	Skin contact	Acute systemic effects	295,52 mg/kg bw/day
	Consumers	Inhalation	Long-term systemic effects	443,28 mg/m ³
	Consumers	Inhalation	Acute systemic effects	443,28 mg/m ³
	Consumers	Skin contact	Long-term systemic effects	126,65 mg/kg bw/day
	Consumers	Skin contact	Acute systemic effects	126,65 mg/kg bw/day
	Consumers	Ingestion	Long-term systemic effects	126,65 mg/kg bw/day
	Consumers	Ingestion	Acute systemic effects	126,65 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
Sodium chloride	Fresh water	5 mg/l
	Sewage treatment plant	500 mg/l
	Soil	4,86 mg/kg dry

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

		weight (d.w.)
--	--	---------------

8.2 Exposure controls

Engineering measures

Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye protection : Please follow all applicable local/national requirements when selecting protective measures for a specific workplace.

Wear the following personal protective equipment:

Safety glasses

Always wear eye protection when the potential for inadvertent eye contact with the product cannot be excluded.

Equipment should conform to DIN EN 166

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Skin and body protection : Skin should be washed after contact.

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.
Equipment should conform to DIN EN 143

Filter type : Particulates type (P)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid

Colour : colourless

Odour : odourless

Odour Threshold : No data available

pH : No data available

Melting point/freezing point : No data available

Initial boiling point and boiling range : No data available

Flash point : boils before flash

Evaporation rate : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

Flammability (solid, gas)	:	Not applicable
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Relative density	:	No data available
Solubility(ies) Water solubility	:	completely soluble
Partition coefficient: n-octanol/water	:	Not applicable
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity Viscosity, kinematic	:	No data available
Explosive properties	:	Not explosive
Oxidizing properties	:	The substance or mixture is not classified as oxidizing.

9.2 Other information

Flammability (liquids)	:	No data available
Particle size	:	Not applicable

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions	:	None known.
---------------------	---	-------------

10.4 Conditions to avoid

Conditions to avoid	:	None known.
---------------------	---	-------------

10.5 Incompatible materials

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

Materials to avoid : None.

10.6 Hazardous decomposition products

No hazardous decomposition products are known.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Not relevant

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- Product : Dispose of in accordance with local regulations.
According to the European Waste Catalogue, Waste Codes are not product specific, but application specific.
Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.
- Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.
- Waste Code : The following Waste Codes are only suggestions:
- used product
06 03 14, solid salts and solutions other than those mentioned in 06 03 11 and 06 03 13
- unused product
06 03 14, solid salts and solutions other than those mentioned in 06 03 11 and 06 03 13
- uncleaned packagings
15 01 06, mixed packaging
- Acc. Packaging Act properly emptied packaging:
Properly emptied, non-contaminated packaging of non-hazardous products can be supplied to a system for the collection of sales packaging.
-

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Water contaminating class (Germany) : WGK 1 slightly hazardous to water
Classification according to AwSV, Annex 1 (5.2)

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 0 %

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

Other information : Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AIIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS mate-

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



MARKING SOLUTION WHITE - 100 ML

Version	Revision Date:	SDS Number:	Date of last issue: 20.08.2020
3.9	18.12.2020	1096077-00005	Date of first issue: 11.06.2010

Material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

DE / EN