

Exhaust Assembly Paste

Version 3.7 Revision Date: 05/03/2022 SDS Number: 10669832-00005 Date of last issue: 06/01/2021
Date of first issue: 04/21/2011

Chemical name	CAS-No.	Concentration (% w/w)
Kaolin	1332-58-7	>= 50 - < 70

4. FIRST AID MEASURES

- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : None known.
- Protection of first-aiders : No special precautions are necessary for first aid responders.
- Notes to physician : Treat symptomatically and supportively.

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Not applicable
Will not burn
- Unsuitable extinguishing media : Not applicable
Will not burn
- Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Silicon oxides
Metal oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.
- Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary.
Use personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

Exhaust Assembly Paste

Version 3.7 Revision Date: 05/03/2022 SDS Number: 10669832-00005 Date of last issue: 06/01/2021
 Date of first issue: 04/21/2011

- Personal precautions, protective equipment and emergency procedures : Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).
- Environmental precautions : Avoid release to the environment.
 Prevent further leakage or spillage if safe to do so.
 Prevent spreading over a wide area (e.g. by containment or oil barriers).
 Retain and dispose of contaminated wash water.
 Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Soak up with inert absorbent material.
 For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
 Clean up remaining materials from spill with suitable absorbent.
 Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
 Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : Use only with adequate ventilation.
- Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
 Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labelled containers.
 Store in accordance with the particular national regulations.
- Materials to avoid : No special restrictions on storage with other products.
- Recommended storage temperature : 15 - 30 °C

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis

Exhaust Assembly Paste

Version 3.7 Revision Date: 05/03/2022 SDS Number: 10669832-00005 Date of last issue: 06/01/2021
 Date of first issue: 04/21/2011

Kaolin	1332-58-7	TWA (Respirable particulate matter)	2 mg/m ³	ACGIH
--------	-----------	-------------------------------------	---------------------	-------

Engineering measures : Ensure adequate ventilation, especially in confined areas. Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.

Filter type : Particulates type

Hand protection

Material : Nitrile rubber
 Break through time : 30 min
 Glove thickness : 0.4 mm

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
 Safety glasses
 Always wear eye protection when the potential for inadvertent eye contact with the product cannot be excluded.
 Please follow all applicable local/national requirements when selecting protective measures for a specific workplace.

Skin and body protection : Skin should be washed after contact.

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
 When using do not eat, drink or smoke.
 Wash contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : paste

Colour : grey

Odour : characteristic

Exhaust Assembly Paste

Version 3.7 Revision Date: 05/03/2022 SDS Number: 10669832-00005 Date of last issue: 06/01/2021
Date of first issue: 04/21/2011

Odour Threshold : No data available

pH : 10.5 (20 °C)
Concentration: 100 %

Melting point/freezing point : No data available

Initial boiling point and boiling range : 100 °C

Flash point : No data available

Evaporation rate : No data available

Flammability (solid, gas) : Not applicable

Flammability (liquids) : Will not burn

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : No data available

Relative vapour density : No data available

Density : 1.71 g/cm³ (20 °C)

Solubility(ies)
Water solubility : partly soluble (20 °C)

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, kinematic : No data available

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle size : Not applicable

10. STABILITY AND REACTIVITY

Exhaust Assembly Paste

Version 3.7 Revision Date: 05/03/2022 SDS Number: 10669832-00005 Date of last issue: 06/01/2021
Date of first issue: 04/21/2011

Reactivity : Not classified as a reactivity hazard.

Chemical stability : Stable under normal conditions.

Possibility of hazardous reactions : None known.

Conditions to avoid : None known.

Incompatible materials : Acids

Hazardous decomposition products : No hazardous decomposition products are known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Components:**Kaolin:**

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Remarks: Based on data from similar materials

Acute inhalation toxicity : LC50 (Rat): > 2.07 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rat): > 5,000 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Skin corrosion/irritation

Not classified based on available information.

Components:**Kaolin:**

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation
Remarks : Based on data from similar materials

Exhaust Assembly Paste

Version	Revision Date:	SDS Number:	Date of last issue: 06/01/2021
3.7	05/03/2022	10669832-00005	Date of first issue: 04/21/2011

Other adverse effectsNo data available

13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
If not otherwise specified: Dispose of as unused product.

14. TRANSPORT INFORMATION**International Regulations****UNRTDG**

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to IMO instruments

Not applicable for product as supplied.

Special precautions for userNot applicable

15. REGULATORY INFORMATION**Safety, health and environmental regulations/legislation specific for the substance or mixture**

16. OTHER INFORMATION**Further information**

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)

ACGIH / TWA : 8-hour, time-weighted average

Exhaust Assembly Paste

Version	Revision Date:	SDS Number:	Date of last issue: 06/01/2021
3.7	05/03/2022	10669832-00005	Date of first issue: 04/21/2011

AIIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

IN / EN