

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : ALL IN ONE 50g
Product code : 0893555050

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-
stance/Mixture : Adhesives
Professional use product

Recommended restrictions
on use : Not applicable

1.3 Details of the supplier of the safety data sheet

Company : WÜRTH IRELAND LTD.
Monaclinoe Ind. Est. Ballysimon
Limerick
Telephone : +353 61 430200
Telefax : +353 61 412428
E-mail address of person
responsible for the SDS : prodsafe@wuerth.com

1.4 Emergency telephone number

Location Ireland:
(NPIC) +353 1 8092566

Location Northern Ireland:
(NPIS) 0344 892 0111

Reachable for both Locations:
(GBK) +49 (0)6132 84463

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

|| No hazard pictogram, no signal word, no hazard statement(s), no precautionary statement(s) required

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Remarks : No hazardous ingredients

SECTION 4: First aid measures

4.1 Description of first aid measures

|| Protection of first-aiders : No special precautions are necessary for first aid responders.

|| If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.

|| In case of skin contact : Wash with water and soap as a precaution.
Get medical attention if symptoms occur.

|| In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.

|| If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.

4.2 Most important symptoms and effects, both acute and delayed

None known.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical

Unsuitable extinguishing media : None known.

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.

Hazardous combustion products : Silicon oxides
Carbon oxides
Nitrogen oxides (NO_x)
Sulphur oxides
Fluorine compounds

5.3 Advice for firefighters

Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022



cannot be contained.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use only with adequate ventilation.

Advice on safe handling : Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store in accordance with the particular national regulations.

Advice on common storage : Do not store with the following product types:
Strong oxidizing agents
Gases

Storage period : 12 Months

Recommended storage temperature : 20 °C

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version 3.0 Revision Date: 17.03.2023 SDS Number: 10646480-00005 Date of last issue: 02.02.2023
Date of first issue: 30.03.2022

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value
1,2-Benzisothiazol-3(2H)-one 1,1-dioxide	Workers	Inhalation	Long-term systemic effects	4.19 mg/m ³
	Workers	Skin contact	Long-term systemic effects	2.381 mg/kg bw/day
	Consumers	Inhalation	Long-term systemic effects	1.035 mg/m ³
	Consumers	Skin contact	Long-term systemic effects	1.190 mg/kg bw/day
	Consumers	Skin contact	Long-term systemic effects	0.595 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
1,2-Benzisothiazol-3(2H)-one 1,1-dioxide	Fresh water	0.104 mg/l
	Marine water	0.0104 mg/l
	Intermittent use/release	1.044 mg/l
	Fresh water sediment	104.403 mg/kg
	Marine sediment	104.403 mg/kg
	Soil	29.024 mg/kg
	Sewage treatment plant	12.304 mg/l

8.2 Exposure controls

Engineering measures

Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye/face protection : Please follow all applicable local/national requirements when selecting protective measures for a specific workplace.

Wear the following personal protective equipment:

Safety glasses

Always wear eye protection when the potential for inadvertent eye contact with the product cannot be excluded.

Equipment should conform to I.S. EN 166

Hand protection

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

Material : Nitrile rubber
Break through time : 480 min
Glove thickness : > 0.4 mm
Directive : Equipment should conform to I.S. EN 374

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

|| Skin and body protection : Skin should be washed after contact.

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection. Equipment should conform to I.S. EN 143

Filter type : Particulates type (P)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state : liquid
Colour : yellow
Odour : mild
Odour Threshold : No data available
Melting point/freezing point : No data available
Initial boiling point and boiling range : No data available
Flammability (solid, gas) : Not applicable
Flammability (liquids) : Ignitable (see flash point)
Upper explosion limit / Upper flammability limit : No data available
Lower explosion limit / Lower flammability limit : No data available
Flash point : > 100 °C
Auto-ignition temperature : No data available
Decomposition temperature : No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

pH : substance/mixture is non-soluble (in water)

Viscosity

Viscosity, dynamic : 18,000 - 30,000 mPa.s (25 °C)
Method: Brookfield

Viscosity, kinematic : No data available

Solubility(ies)

Water solubility : immiscible

Partition coefficient: n-octanol/water : Not applicable

Vapour pressure : No data available

Relative density : No data available

Density : 1.05 g/cm³ (25 °C)

Relative vapour density : No data available

Particle characteristics

Particle size : Not applicable

9.2 Other information

Explosives : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Evaporation rate : No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : Can react with strong oxidizing agents.

10.4 Conditions to avoid

Conditions to avoid : None known.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

10.6 Hazardous decomposition products

No hazardous decomposition products are known.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity : Acute toxicity estimate: > 2,000 mg/kg
Method: Calculation method

Acute inhalation toxicity : Acute toxicity estimate: > 20 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Method: Calculation method

Acute dermal toxicity : Acute toxicity estimate: > 2,000 mg/kg
Method: Calculation method

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

Aspiration toxicity

Not classified based on available information.

11.2 Information on other hazards

Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

|||Product : Dispose of in accordance with local regulations.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

According to the European Waste Catalogue, Waste Codes are not product specific, but application specific. Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities. Do not dispose of waste into sewer.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal. If not otherwise specified: Dispose of as unused product.

Waste Code : The following Waste Codes are only suggestions:

used product
08 04 10, waste adhesives and sealants other than those mentioned in 08 04 09

unused product
08 04 10, waste adhesives and sealants other than those mentioned in 08 04 09

uncleaned packagings
15 01 06, mixed packaging

SECTION 14: Transport information

14.1 UN number or ID number

ADN : Not regulated as a dangerous good
ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.2 UN proper shipping name

ADN : Not regulated as a dangerous good
ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.3 Transport hazard class(es)

ADN : Not regulated as a dangerous good
ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version 3.0 Revision Date: 17.03.2023 SDS Number: 10646480-00005 Date of last issue: 02.02.2023
Date of first issue: 30.03.2022

14.4 Packing group

ADN : Not regulated as a dangerous good
ADR : Not regulated as a dangerous good
RID : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA (Cargo) : Not regulated as a dangerous good
IATA (Passenger) : Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles (Annex XVII) : Conditions of restriction for the following entries should be considered:
Number on list 75
If you intend to use this product as tattoo ink, please contact your vendor.

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 73 %

Other regulations:

Take note of Directive 92/85/EEC regarding maternity protection or stricter national regulations, where applicable.

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

Other information : Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - Agreement concerning the International Carriage of Dangerous Goods by Road; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



ALL IN ONE 50g

Version	Revision Date:	SDS Number:	Date of last issue: 02.02.2023
3.0	17.03.2023	10646480-00005	Date of first issue: 30.03.2022

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

IE / EN