

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name : CO2 LEAK DETECTOR FLUID - 500 ML  
Product code : 0893202

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-  
stance/Mixture : Test substance  
Professional use product  
Recommended restrictions : Not applicable  
on use

#### 1.3 Details of the supplier of the safety data sheet

Company : Adolf Wuerth GmbH & Co. KG  
Reinhold-Würth-Str. 12-17  
74653 Künzelsau  
Telephone : +49 794015 0  
Telefax : +49 794015 10 00  
E-mail address of person  
responsible for the SDS : isi@wuerth.com

#### 1.4 Emergency telephone number

+49 (0)6132 – 84463

---

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

**Classification (REGULATION (EC) No 1272/2008)**  
Not a hazardous substance or mixture.

#### 2.2 Label elements

**Labelling (REGULATION (EC) No 1272/2008)**  
No hazard pictogram, no signal word, no hazard statement(s), no precautionary statement(s) required.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### 2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

---

## SECTION 3: Composition/information on ingredients

### 3.2 Mixtures

#### Components

Remarks : No hazardous ingredients

---

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

Protection of first-aiders : No special precautions are necessary for first aid responders.

If inhaled : If inhaled, remove to fresh air.  
Get medical attention if symptoms occur.

In case of skin contact : Wash with water and soap as a precaution.  
Get medical attention if symptoms occur.

In case of eye contact : Flush eyes with water as a precaution.  
Get medical attention if irritation develops and persists.

If swallowed : If swallowed, DO NOT induce vomiting.  
Get medical attention if symptoms occur.  
Rinse mouth thoroughly with water.

### 4.2 Most important symptoms and effects, both acute and delayed

None known.

### 4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### SECTION 5: Firefighting measures

#### 5.1 Extinguishing media

Suitable extinguishing media : Not applicable  
Will not burn

Unsuitable extinguishing media : Not applicable  
Will not burn

#### 5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.

Hazardous combustion products : No hazardous combustion products are known

#### 5.3 Advice for firefighters

Special protective equipment for firefighters : Wear self-contained breathing apparatus for firefighting if necessary. Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.  
Use water spray to cool unopened containers.  
Remove undamaged containers from fire area if it is safe to do so.  
Evacuate area.

---

### SECTION 6: Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

#### 6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.  
Prevent further leakage or spillage if safe to do so.  
Prevent spreading over a wide area (e.g. by containment or oil barriers).  
Retain and dispose of contaminated wash water.  
Local authorities should be advised if significant spillages cannot be contained.

#### 6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.  
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

Clean up remaining materials from spill with suitable absorbent.  
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.  
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

### 6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

---

## SECTION 7: Handling and storage

### 7.1 Precautions for safe handling

- |                         |   |  |
|-------------------------|---|--|
| Technical measures      | : | See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.  |
| Local/Total ventilation | : | Use only with adequate ventilation.  |
| Advice on safe handling | : | Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment<br>Take care to prevent spills, waste and minimize release to the environment.    |
| Hygiene measures        | : | If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use. |

### 7.2 Conditions for safe storage, including any incompatibilities

- |   |   |   |
|---|---|---|
| Requirements for storage areas and containers | : | Keep in properly labelled containers. Store in accordance with the particular national regulations. |
| Advice on common storage                      | : | No special restrictions on storage with other products.   |
| Storage class (TRGS 510)                      | : | 12  |
| Recommended storage temperature               | : | 0 - 45 °C   |

### 7.3 Specific end use(s)

- |                 |   |                   |
|-----------------|---|-------------------|
| Specific use(s) | : | No data available |
|-----------------|---|-------------------|

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### SECTION 8: Exposure controls/personal protection

#### 8.1 Control parameters

##### Occupational Exposure Limits

Contains no substances with occupational exposure limit values.

#### 8.2 Exposure controls

##### Engineering measures

Ensure adequate ventilation, especially in confined areas.  
Minimize workplace exposure concentrations.

##### Personal protective equipment

Eye/face protection : Please follow all applicable local/national requirements when selecting protective measures for a specific workplace.

Wear the following personal protective equipment:

Safety glasses

Always wear eye protection when the potential for inadvertent eye contact with the product cannot be excluded.

Equipment should conform to DIN EN 166

##### Hand protection

Material : Nitrile rubber  
Break through time :  $\geq 480$  min  
Glove thickness : 0,11 mm  
Directive : Equipment should conform to DIN EN 374

Material : Rubber gloves  
Break through time :  $\geq 480$  min  
Glove thickness : 0,11 mm  
Directive : Equipment should conform to DIN EN 374

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Skin and body protection : Skin should be washed after contact.

Respiratory protection : No personal respiratory protective equipment normally required.

---

### SECTION 9: Physical and chemical properties

#### 9.1 Information on basic physical and chemical properties

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

Physical state	:	liquid
Colour	:	blue
Odour	:	odourless
Odour Threshold	:	No data available
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	No data available
Flammability (solid, gas)	:	Not applicable
Flammability (liquids)	:	Will not burn
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Flash point	:	Not applicable
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
pH	:	6,6 - 6,8
Viscosity	:	
Viscosity, kinematic	:	No data available
Solubility(ies)	:	
Water solubility	:	completely soluble
Partition coefficient: n-	:	Not applicable

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

octanol/water

Vapour pressure : No data available

Density : 0,92 g/cm<sup>3</sup> (20 °C)

Relative vapour density : No data available

Particle characteristics  
Particle size : Not applicable

### 9.2 Other information

Explosives : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Evaporation rate : No data available

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

Not classified as a reactivity hazard.

### 10.2 Chemical stability

Stable under normal conditions.

### 10.3 Possibility of hazardous reactions

Hazardous reactions : None known.

### 10.4 Conditions to avoid

Conditions to avoid : None known.

### 10.5 Incompatible materials

Materials to avoid : None.

### 10.6 Hazardous decomposition products

No hazardous decomposition products are known.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### SECTION 11: Toxicological information

#### 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure : Inhalation  
Skin contact  
Ingestion  
Eye contact

##### **Acute toxicity**

Not classified based on available information.

##### **Skin corrosion/irritation**

Not classified based on available information.

##### **Serious eye damage/eye irritation**

Not classified based on available information.

##### **Respiratory or skin sensitisation**

##### **Skin sensitisation**

Not classified based on available information.

##### **Respiratory sensitisation**

Not classified based on available information.

##### **Germ cell mutagenicity**

Not classified based on available information.

##### **Carcinogenicity**

Not classified based on available information.

##### **Reproductive toxicity**

Not classified based on available information.

##### **STOT - single exposure**

Not classified based on available information.

##### **STOT - repeated exposure**

Not classified based on available information.

##### **Aspiration toxicity**

Not classified based on available information.

#### 11.2 Information on other hazards

##### **Endocrine disrupting properties**

##### **Product:**

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.



# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

### SECTION 12: Ecological information

#### 12.1 Toxicity

No data available

#### 12.2 Persistence and degradability

No data available

#### 12.3 Bioaccumulative potential

No data available

#### 12.4 Mobility in soil

No data available

#### 12.5 Results of PBT and vPvB assessment

**Product:**

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

#### 12.6 Endocrine disrupting properties

**Product:**

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

#### 12.7 Other adverse effects

No data available

---

### SECTION 13: Disposal considerations

#### 13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations. According to the European Waste Catalogue, Waste Codes are not product specific, but application specific. Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities. Do not dispose of waste into sewer.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal. If not otherwise specified: Dispose of as unused product.

Waste Code : The following Waste Codes are only suggestions:  
used product

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

16 03 06, organic wastes other than those mentioned in 16 03 05

unused product

16 03 06, organic wastes other than those mentioned in 16 03 05

uncleaned packagings

15 01 06, mixed packaging

Acc. Packaging Act properly emptied packaging:  
Properly emptied, non-contaminated packaging of non-hazardous products can be supplied to a system for the collection of sales packaging.

---

### SECTION 14: Transport information

#### 14.1 UN number or ID number

ADN : Not regulated as a dangerous good  
ADR : Not regulated as a dangerous good  
RID : Not regulated as a dangerous good  
IMDG : Not regulated as a dangerous good  
IATA : Not regulated as a dangerous good

#### 14.2 UN proper shipping name

ADN : Not regulated as a dangerous good  
ADR : Not regulated as a dangerous good  
RID : Not regulated as a dangerous good  
IMDG : Not regulated as a dangerous good  
IATA : Not regulated as a dangerous good

#### 14.3 Transport hazard class(es)

ADN : Not regulated as a dangerous good  
ADR : Not regulated as a dangerous good  
RID : Not regulated as a dangerous good  
IMDG : Not regulated as a dangerous good  
IATA : Not regulated as a dangerous good

#### 14.4 Packing group

ADN : Not regulated as a dangerous good  
ADR : Not regulated as a dangerous good  
RID : Not regulated as a dangerous good

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

**IMDG** : Not regulated as a dangerous good

**IATA (Cargo)** : Not regulated as a dangerous good

**IATA (Passenger)** : Not regulated as a dangerous good

### 14.5 Environmental hazards

Not regulated as a dangerous good

### 14.6 Special precautions for user

Not applicable

### 14.7 Maritime transport in bulk according to IMO instruments

Remarks : Not applicable for product as supplied.

---

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles (Annex XVII) :

Substance(s) or mixture(s) are listed here according to their appearance in the regulation, irrespective of their use/purpose or the conditions of the restriction. Please refer to the conditions in corresponding Regulation to determine whether an entry is applicable to the placing on the market or not.

Conditions of restriction for the following entries should be considered: Number on list 75: If you intend to use this product as tattoo ink, please contact your vendor.

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : Not applicable

Regulation (EC) on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EU) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

---

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.  
Not applicable

Water hazard class (Germany) : nwg not water endangering  
Classification according to AwSV §6(4)

TA Luft List (Germany) : 5.2.1: Total dust:  
Not applicable  
5.2.2: Inorganic substances in powdered form:  
Not applicable  
5.2.4: Inorganic substances in gaseous form:  
Not applicable  
5.2.5: Organic Substances:  
Not applicable  
5.2.7.1.1: Carcinogenic substance:  
Not applicable  
5.2.7.1.1: Quartz fine dust PM4:  
Not applicable  
5.2.7.1.1: Formaldehyde:  
Not applicable  
5.2.7.1.1: fibres:  
Not applicable  
5.2.7.1.2: Germ cell mutagens:  
Not applicable  
5.2.7.1.3: Substances toxic to reproduction:  
Not applicable  
5.2.7.2: Poorly degradable, easily enrichable and highly toxic organic substances:  
Not applicable

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)  
Volatile organic compounds (VOC) content: 0 %

### 15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

---

## SECTION 16: Other information

Other information : Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

### Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - Agreement concerning the International Carriage of Dangerous Goods by

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## CO2 LEAK DETECTOR FLUID - 500 ML

Version	Revision Date:	SDS Number:	Date of last issue: 18.06.2024
5.1	14.11.2024	10682220-00012	Date of first issue: 11.06.2010

Road; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

### Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

DE / EN