

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name	:	DIESEL-TREATMENT - 300 ML
Product code	:	5861001301
Unique Formula Identifier (UFI)	:	7KA1-40U7-F00H-0QGG

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-stance/Mixture	:	Additive Professional use product
-------------------------------	---	--------------------------------------

1.3 Details of the supplier of the safety data sheet

Company	:	Adolf Wuerth GmbH & Co. KG Reinhold-Würth-Str. 12-17 74653 Künzelsau
Telephone	:	+49 794015 0
Telefax	:	+49 794015 10 00
E-mail address of person responsible for the SDS	:	prodsafe@wuerth.com

1.4 Emergency telephone number

+49 (0)6132 – 84463

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Aspiration hazard, Category 1	H304: May be fatal if swallowed and enters airways.
Long-term (chronic) aquatic hazard, Category 3	H412: Harmful to aquatic life with long lasting effects.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version 1.9 Revision Date: 21.09.2021 SDS Number: 2654040-00009 Date of last issue: 12.03.2021
Date of first issue: 29.03.2018

Signal word : Danger

Hazard statements : H304 May be fatal if swallowed and enters airways.
H412 Harmful to aquatic life with long lasting effects.

Supplemental Hazard Statements : EUH044 Risk of explosion if heated under confinement.
EUH066 Repeated exposure may cause skin dryness or cracking.

Precautionary statements : **Prevention:**
P273 Avoid release to the environment.
Response:
P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
P331 Do NOT induce vomiting.
Storage:
P405 Store locked up.
Disposal:
P501 Dispose of contents/ container to an approved waste disposal plant.

Hazardous components which must be listed on the label:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Vapours may form explosive mixture with air.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
Hydrocarbons, C10-C13, n-	Not Assigned	Asp. Tox. 1; H304	>= 90 - <= 100

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version 1.9 Revision Date: 21.09.2021 SDS Number: 2654040-00009 Date of last issue: 12.03.2021
Date of first issue: 29.03.2018

alkanes, isoalkanes, cyclics, <2% aromatics	01-2119457273-39	EUH066	
2-Ethylhexyl nitrate	27247-96-7 248-363-6	Acute Tox. 4; H302 Acute Tox. 4; H332 Acute Tox. 4; H312 Aquatic Chronic 2; H411 EUH044, EUH066 Acute toxicity estimate Acute oral toxicity: 500 mg/kg Acute inhalation toxicity (vapour): 11 mg/l Acute dermal toxicity: 1.100 mg/kg	>= 10 - < 20

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water.
Remove contaminated clothing and shoes.
Get medical attention.
Wash clothing before reuse.
Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
If vomiting occurs have person lean forward.
Call a physician or poison control centre immediately.
Never give anything by mouth to an unconscious person.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

4.2 Most important symptoms and effects, both acute and delayed

Risks : May be fatal if swallowed and enters airways.
Repeated exposure may cause skin dryness or cracking.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical

Unsuitable extinguishing media : High volume water jet

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Do not use a solid water stream as it may scatter and spread fire.
Flash back possible over considerable distance.
Vapours may form explosive mixtures with air.
Exposure to combustion products may be a hazard to health.

Hazardous combustion products : Carbon oxides
Nitrogen oxides (NO_x)

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Remove all sources of ignition.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : If sufficient ventilation is unavailable, use with local exhaust ventilation.

Advice on safe handling : Do not get on skin or clothing.
Avoid inhalation of vapour or mist.
Do not swallow.
Avoid contact with eyes.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Keep container tightly closed.
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
Take precautionary measures against static discharges.
Take care to prevent spills, waste and minimize release to the environment.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version 1.9 Revision Date: 21.09.2021 SDS Number: 2654040-00009 Date of last issue: 12.03.2021
Date of first issue: 29.03.2018

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store locked up. Keep tightly closed. Keep in a cool, well-ventilated place. Store in accordance with the particular national regulations. Keep away from heat and sources of ignition.

Advice on common storage : Do not store with the following product types:
Strong oxidizing agents
Explosives
Gases

Storage class (TRGS 510) : 10, Combustible liquids

Storage period : 36 Months

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics	Not Assigned	AGW	300 mg/m ³	DE TRGS 900
Peak-limit: excursion factor (category): 2;(II)				
Further information: Group exposure limit for hydrocarbon solvent mixtures				

Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health effects	Value
2-Ethylhexyl nitrate	Workers	Inhalation	Long-term systemic effects	0,35 mg/m ³
		Skin contact	Long-term systemic effects	1 mg/kg bw/day
	Workers	Skin contact	Long-term local effects	0,44 mg/kg bw/day
		Consumers	Inhalation	Long-term systemic effects
	Consumers		Skin contact	Long-term systemic

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version 1.9 Revision Date: 21.09.2021 SDS Number: 2654040-00009 Date of last issue: 12.03.2021
Date of first issue: 29.03.2018

			effects	bw/day
	Consumers	Ingestion	Long-term local effects	0,025 mg/kg bw/day

Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
2-Ethylhexyl nitrate	Fresh water	0,0008 mg/l
	Marine sediment	0,00008 mg/l
	Sewage treatment plant	10 mg/l
	Fresh water sediment	0,00074 mg/l
	Marine sediment	0,00074 mg/l
	Soil	0,000191 mg/l

8.2 Exposure controls

Engineering measures

Ensure adequate ventilation, especially in confined areas.
Minimize workplace exposure concentrations.

Personal protective equipment

Eye protection : Wear the following personal protective equipment:
Safety glasses
Equipment should conform to DIN EN 166

Hand protection :
Material : Nitrile rubber
Break through time : > 240 min
Glove thickness : 0,35 mm

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Wear the following personal protective equipment:
If assessment demonstrates that there is a risk of explosive atmospheres or flash fires, use flame retardant antistatic protective clothing.
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.
Equipment should conform to DIN EN 14387

Filter type : Combined particulates and organic vapour type (A-P)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state	:	liquid
Colour	:	transparent
Odour	:	characteristic
Odour Threshold	:	No data available
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	> 100 °C
Flammability (solid, gas)	:	Not applicable
Flammability (liquids)	:	Ignitable (see flash point)
Upper explosion limit / Upper flammability limit	:	7,0 %(V)
Lower explosion limit / Lower flammability limit	:	0,6 %(V)
Flash point	:	62 °C
Auto-ignition temperature	:	> 200 °C
Decomposition temperature	:	No data available
pH	:	Solvent mixture; pH value determination not possible, no aqueous solution
Viscosity		
Viscosity, kinematic	:	7 mm ² /s (40 °C)
Solubility(ies)		
Water solubility	:	insoluble
Partition coefficient: n-octanol/water	:	Not applicable
Vapour pressure	:	1 hPa (20 °C)
Density	:	0,81 g/cm ³ (20 °C)
Relative vapour density	:	No data available
Particle characteristics		
Particle size	:	Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

9.2 Other information

Explosives : Risk of explosion if heated under confinement.

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Evaporation rate : No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Not classified as a reactivity hazard.

10.2 Chemical stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

Hazardous reactions : Combustible liquid.
Vapours may form explosive mixture with air.
Can react with strong oxidizing agents.
Risk of explosion if heated under confinement.

10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

10.6 Hazardous decomposition products

No hazardous decomposition products are known.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity : Acute toxicity estimate: > 2.000 mg/kg
Method: Calculation method

Acute inhalation toxicity : Acute toxicity estimate: > 20 mg/l
Exposure time: 4 h
Test atmosphere: vapour

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

Method: Calculation method

Acute dermal toxicity : Acute toxicity estimate: > 2.000 mg/kg
Method: Calculation method

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Acute oral toxicity : LD50 (Rat): > 5.000 mg/kg
Remarks: Based on data from similar materials

Acute inhalation toxicity : LC50 (Rat): > 4.951 mg/m³
Exposure time: 4 h
Test atmosphere: vapour
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): >= 3.160 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

2-Ethylhexyl nitrate:

Acute oral toxicity : LD50 (Rat): > 9.600 mg/kg
Acute toxicity estimate: 500 mg/kg
Method: Expert judgement

Acute inhalation toxicity : Acute toxicity estimate: 11 mg/l
Test atmosphere: vapour
Method: Expert judgement

Acute dermal toxicity : LD50 (Rabbit): > 4.800 mg/kg
Acute toxicity estimate: 1.100 mg/kg
Method: Expert judgement

Skin corrosion/irritation

Repeated exposure may cause skin dryness or cracking.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rabbit
Result : Mild skin irritation

Assessment : Repeated exposure may cause skin dryness or cracking.

2-Ethylhexyl nitrate:

Species : Rabbit
Method : OECD Test Guideline 404

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

Result : No skin irritation

Assessment : Repeated exposure may cause skin dryness or cracking.

Serious eye damage/eye irritation

Not classified based on available information.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation
Remarks : Based on data from similar materials

2-Ethylhexyl nitrate:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Result : negative
Remarks : Based on data from similar materials

2-Ethylhexyl nitrate:

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative

Germ cell mutagenicity

Not classified based on available information.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Genotoxicity in vitro : Test Type: In vitro mammalian cell gene mutation test
Result: negative

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative

Germ cell mutagenicity- Assessment : Classified based on benzene content < 0.1% (Regulation (EC) 1272/2008, Annex VI, Part 3, Note P)

2-Ethylhexyl nitrate:

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro
Method: OECD Test Guideline 473
Result: negative

Test Type: Ames test
Method: OECD Test Guideline 471
Result: negative

Test Type: In vitro mammalian cell gene mutation test
Method: OECD Test Guideline 476
Result: negative

Carcinogenicity

Not classified based on available information.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 105 weeks
Result : negative
Remarks : Based on data from similar materials

Carcinogenicity - Assessment : Classified based on benzene content < 0.1% (Regulation (EC) 1272/2008, Annex VI, Part 3, Note P)

Reproductive toxicity

Not classified based on available information.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test
Species: Rat
Application Route: inhalation (vapour)
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

Application Route: inhalation (vapour)
Result: negative

2-Ethylhexyl nitrate:

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 421
Result: negative

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Repeated dose toxicity

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rat
NOAEL : ≥ 1.000 mg/kg
Application Route : Ingestion
Exposure time : 54 Days
Remarks : Based on data from similar materials

2-Ethylhexyl nitrate:

Species : Rabbit
NOAEL : 500 mg/kg
Application Route : Skin contact
Exposure time : 90 Days

Aspiration toxicity

May be fatal if swallowed and enters airways.

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

11.2 Information on other hazards

Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

levels of 0.1% or higher.

SECTION 12: Ecological information

12.1 Toxicity

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 1.000 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 1.000 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): > 1.000 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

NOELR (Pseudokirchneriella subcapitata (green algae)):
1.000 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOELR: > 1 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

2-Ethylhexyl nitrate:

Toxicity to fish : LC50 (Brachydanio rerio (zebrafish)): 2 mg/l
Exposure time: 96 h
Method: OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 12,6 mg/l
Exposure time: 48 h
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : ErC50 (Pseudokirchneriella subcapitata (green algae)): 3,22 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

EC10 (Pseudokirchneriella subcapitata (green algae)): 1,54 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

Toxicity to microorganisms : EC50 : > 1.000 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209

12.2 Persistence and degradability

Components:

Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 80 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

2-Ethylhexyl nitrate:

Biodegradability : Result: Not readily biodegradable.
Biodegradation: 0 %
Exposure time: 28 d
Method: OECD Test Guideline 310

12.3 Bioaccumulative potential

Components:

2-Ethylhexyl nitrate:

Partition coefficient: n-octanol/water : log Pow: 5,24

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

(EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

- Product : Dispose of in accordance with local regulations.
According to the European Waste Catalogue, Waste Codes are not product specific, but application specific.
Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.
- Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.
- Waste Code : The following Waste Codes are only suggestions:
- used product
16 03 05, organic wastes containing hazardous substances
- unused product
16 03 05, organic wastes containing hazardous substances
- uncleaned packagings
15 01 10, packaging containing residues of or contaminated by hazardous substances
- Acc. Packaging Act properly emptied packaging:
Properly emptied, non-contaminated packaging of non-hazardous products can be supplied to a system for the collection of sales packaging.
-

SECTION 14: Transport information

14.1 UN number or ID number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Remarks : Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Conditions of restriction for the following entries should be considered: Number on list 3
REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Water hazard class (Germany) : WGK 2 obviously hazardous to water
Classification according to AwSV, Annex 1 (5.2)

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 1,69 %

15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

Other information : Items where changes have been made to the previous version are highlighted in the body of this document by two vertical

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

lines.

Full text of H-Statements

H302	: Harmful if swallowed.
H304	: May be fatal if swallowed and enters airways.
H312	: Harmful in contact with skin.
H332	: Harmful if inhaled.
H411	: Toxic to aquatic life with long lasting effects.
EUH044	: Risk of explosion if heated under confinement.
EUH066	: Repeated exposure may cause skin dryness or cracking.

Full text of other abbreviations

Acute Tox.	: Acute toxicity
Aquatic Chronic	: Long-term (chronic) aquatic hazard
Asp. Tox.	: Aspiration hazard
DE TRGS 900	: Germany. TRGS 900 - Occupational exposure limit values.
DE TRGS 900 / AGW	: Time Weighted Average

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AIIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to : Internal technical data, data from raw material SDSs, OECD

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006



DIESEL-TREATMENT - 300 ML

Version	Revision Date:	SDS Number:	Date of last issue: 12.03.2021
1.9	21.09.2021	2654040-00009	Date of first issue: 29.03.2018

compile the Safety Data Sheet

eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Classification of the mixture:

Asp. Tox. 1	H304
Aquatic Chronic 3	H412

Classification procedure:

Calculation method
Calculation method

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

DE / EN