

Cleaner additive

Version Revision Date: SDS Number: Date of last issue: 12/23/2020
2.1 09/21/2021 6285816-00003 Date of first issue: 08/24/2020

1. PRODUCT AND COMPANY IDENTIFICATION

Product name : Cleaner additive

Product code : 5861111303

Manufacturer or supplier's details

Company : Wurth Lanka (PVT) LTD

Address : 375/B, High Level Road
Makumbura, Pannipitya, Sri Lanka

Telephone : 0094-112894930

Emergency telephone number : 0094-777328880

E-mail address : prodsafe@wuerth.com

Telefax : 0094-112894955

Recommended use of the chemical and restrictions on use

Recommended use : Additive

2. HAZARDS IDENTIFICATION**GHS Classification**

Flammable liquids : Category 4

Aspiration hazard : Category 1

Skin corrosion/irritation : Category 3

Short-term (acute) aquatic hazard : Category 3

Long-term (chronic) aquatic hazard : Category 3

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H227 Combustible liquid.
H304 May be fatal if swallowed and enters airways.

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
 Date of first issue: 08/24/2020

H316 Causes mild skin irritation.
 H412 Harmful to aquatic life with long lasting effects.

Precautionary statements :

Prevention:

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P273 Avoid release to the environment.
 P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response:

P301 + P316 IF SWALLOWED: Get emergency medical help immediately.
 P331 Do NOT induce vomiting.
 P332 + P317 If skin irritation occurs: Get medical help.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards which do not result in classification

Vapours may form explosive mixture with air.
 Repeated exposure may cause skin dryness or cracking.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics	64742-48-9	>= 90 - <= 100
Hydrocarbons, C10-C13, aromatics, <1% naphthalene	64742-94-5	>= 5 - < 10
Polyolefin alkyl phenol alkyl amine	Not Assigned	>= 1 - < 5
Naphthalene	91-20-3	>= 0.25 - < 1

4. FIRST AID MEASURES

General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
 When symptoms persist or in all cases of doubt seek medical advice.

If inhaled : If inhaled, remove to fresh air.
 Get medical attention.

In case of skin contact : In case of contact, immediately flush skin with plenty of water.
 Remove contaminated clothing and shoes.

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

- Get medical attention.
Wash clothing before reuse.
Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
If vomiting occurs have person lean forward.
Call a physician or poison control centre immediately.
Rinse mouth thoroughly with water.
Never give anything by mouth to an unconscious person.
- Most important symptoms and effects, both acute and delayed : May be fatal if swallowed and enters airways.
Causes mild skin irritation.
Prolonged or repeated contact may dry skin and cause irritation.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Do not use a solid water stream as it may scatter and spread fire.
Flash back possible over considerable distance.
Vapours may form explosive mixtures with air.
Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Carbon oxides
Nitrogen oxides (NO_x)
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.
- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

Cleaner additive

Version Revision Date: SDS Number: Date of last issue: 12/23/2020
2.1 09/21/2021 6285816-00003 Date of first issue: 08/24/2020

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).
- Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : If sufficient ventilation is unavailable, use with local exhaust ventilation.
- Advice on safe handling : Do not get on skin or clothing.
Avoid inhalation of vapour or mist.
Do not swallow.
Avoid contact with eyes.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Keep container tightly closed.
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
Take precautionary measures against static discharges.
Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labelled containers.

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
 Date of first issue: 08/24/2020

Store locked up.
 Keep tightly closed.
 Keep in a cool, well-ventilated place.
 Store in accordance with the particular national regulations.
 Keep away from heat and sources of ignition.

Materials to avoid : Do not store with the following product types:
 Strong oxidizing agents

Storage period : 36 Months

Further information on storage stability : Keep away from direct sunlight.
 Keep away from heat.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics	64742-48-9	TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH
Naphthalene	91-20-3	TWA	10 ppm	ACGIH

Engineering measures : Ensure adequate ventilation, especially in confined areas.
 Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.

Filter type : Combined particulates and organic vapour type

Hand protection

Material : Nitrile rubber
 Break through time : 60 min
 Glove thickness : 0.35 mm
 Protective index : Class 3

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
 Safety glasses

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

- Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Wear the following personal protective equipment:
If assessment demonstrates that there is a risk of explosive atmospheres or flash fires, use flame retardant antistatic protective clothing.
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).
- Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.
-

9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : liquid
- Colour : transparent
- Odour : characteristic
- Odour Threshold : No data available
- pH : Solvent mixture; pH value determination not possible, no aqueous solution
- Melting point/freezing point : No data available
- Initial boiling point and boiling range : 160 °C
- Flash point : 62 °C
- Evaporation rate : No data available
- Flammability (solid, gas) : Not applicable
- Flammability (liquids) : Ignitable (see flash point)
- Upper explosion limit / Upper flammability limit : 7 %(V)
- Lower explosion limit / Lower flammability limit : 0.6 %(V)
- Vapour pressure : 1 hPa (20 °C)
-

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

Relative vapour density	:	No data available
Density	:	0.80 g/cm ³ (20 °C)
Solubility(ies)	:	
Water solubility	:	insoluble
Partition coefficient: n-octanol/water	:	Not applicable
Auto-ignition temperature	:	> 200 °C
Decomposition temperature	:	No data available
Viscosity	:	
Viscosity, kinematic	:	7 mm ² /s (40 °C)
Explosive properties	:	Not explosive
Oxidizing properties	:	The substance or mixture is not classified as oxidizing.
Particle size	:	Not applicable

10. STABILITY AND REACTIVITY

Reactivity	:	Not classified as a reactivity hazard.
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Combustible liquid. Vapours may form explosive mixture with air. Can react with strong oxidizing agents.
Conditions to avoid	:	Heat, flames and sparks.
Incompatible materials	:	Oxidizing agents
Hazardous decomposition products	:	No hazardous decomposition products are known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure	:	Inhalation Skin contact Ingestion Eye contact
--	---	--

Acute toxicity

Not classified based on available information.

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
Date of first issue: 08/24/2020

Components:**Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

- Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): > 4,951 mg/m³
Exposure time: 4 h
Test atmosphere: vapour
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rabbit): ≥ 3,160 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

- Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 401
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rabbit): > 2,000 mg/kg
Remarks: Based on data from similar materials

Naphthalene:

- Acute oral toxicity : LD50 (Mouse): 553 mg/kg
Method: OECD Test Guideline 401
- Acute inhalation toxicity : LC50 (Rat): > 0.4 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Method: OECD Test Guideline 403
- Acute dermal toxicity : LD50 (Rat): > 2,500 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity

Skin corrosion/irritation

Causes mild skin irritation.

Components:**Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

- Species : Rabbit
Result : Mild skin irritation
- Assessment : Repeated exposure may cause skin dryness or cracking.

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
Date of first issue: 08/24/2020

Species : Rabbit
Result : No skin irritation
Remarks : Based on data from similar materials

Assessment : Repeated exposure may cause skin dryness or cracking.

Polyolefin alkyl phenol alkyl amine:

Result : Skin irritation

Naphthalene:

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Components:**Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation
Remarks : Based on data from similar materials

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

Species : Rabbit
Result : No eye irritation
Remarks : Based on data from similar materials

Naphthalene:

Species : Guinea pig
Method : OECD Test Guideline 405
Result : No eye irritation

Respiratory or skin sensitisation**Skin sensitisation**

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:**Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Result : negative
Remarks : Based on data from similar materials

Cleaner additive

Version Revision Date: SDS Number: Date of last issue: 12/23/2020
2.1 09/21/2021 6285816-00003 Date of first issue: 08/24/2020

Components:**Naphthalene:**

Exposure routes : inhalation (vapour)
Assessment : No significant health effects observed in animals at concentrations of 1 mg/l/6h/d or less.

Repeated dose toxicity**Components:****Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

Species : Rat
NOAEL : $\geq 1,000$ mg/kg
Application Route : Ingestion
Exposure time : 54 Days
Remarks : Based on data from similar materials

Naphthalene:

Species : Mouse
NOAEL : 133 mg/kg
Application Route : Ingestion
Exposure time : 90 Days
Method : OECD Test Guideline 408

Species : Rat
NOAEL : 0.011 mg/l
Application Route : inhalation (vapour)
Exposure time : 13 Weeks
Method : OECD Test Guideline 413

Species : Rat
NOAEL : 300 mg/kg
Application Route : Skin contact
Exposure time : 13 Weeks
Method : OECD Test Guideline 411

Aspiration toxicity

May be fatal if swallowed and enters airways.

Components:**Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
Date of first issue: 08/24/2020

12. ECOLOGICAL INFORMATION**Ecotoxicity****Components:****Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 1,000 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 1,000 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): > 1,000 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

NOELR (Pseudokirchneriella subcapitata (green algae)): 1,000 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOELR: > 1 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): 3.6 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): 1.1 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): 7.9 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Cleaner additive

Version 2.1 Revision Date: 09/21/2021 SDS Number: 6285816-00003 Date of last issue: 12/23/2020
Date of first issue: 08/24/2020

NOELR (Pseudokirchneriella subcapitata (green algae)): 0.22 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Naphthalene:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 6.08 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 2.16 mg/l
Exposure time: 48 h
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : EC50 (Skeletonema costatum (marine diatom)): 0.4 mg/l
Exposure time: 72 h

M-Factor (Acute aquatic toxicity) : 1

Toxicity to microorganisms : IC50 (Nitrosomonas sp.): 29 mg/l
Exposure time: 24 h

Toxicity to fish (Chronic toxicity) : NOEC: 0.37 mg/l
Exposure time: 40 d
Species: Oncorhynchus kisutch (coho salmon)

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC: 0.59 mg/l
Exposure time: 125 d
Species: Daphnia pulex (Water flea)

M-Factor (Chronic aquatic toxicity) : 1

Persistence and degradability**Components:****Hydrocarbons, C10-C13, n-alkanes, isoalkanes, cyclics, <2% aromatics:**

Biodegradability : Result: Readily biodegradable.
Biodegradation: 80 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Hydrocarbons, C10-C13, aromatics, <1% naphthalene:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 70 %
Exposure time: 28 d
Method: OECD Test Guideline 301F

Naphthalene:

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

Biodegradability : Result: Not readily biodegradable.
Biodegradation: 2 %
Exposure time: 4 Weeks
Method: OECD Test Guideline 302

Bioaccumulative potential**Components:****Hydrocarbons, C10-C13, aromatics, <1% naphthalene:**

Partition coefficient: n- : log Pow: > 3
octanol/water

Naphthalene:

Bioaccumulation : Species: Cyprinus carpio (Carp)
Bioconcentration factor (BCF): 36.5 - 168
Method: OECD Test Guideline 305

Partition coefficient: n- : log Pow: 3.4
octanol/water

Mobility in soil

No data available

Other adverse effects

No data available

13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.

14. TRANSPORT INFORMATION**International Regulations****UNRTDG**

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

Transport in bulk according to IMO instruments

Not applicable for product as supplied.

Special precautions for user

Not applicable

15. REGULATORY INFORMATION**Safety, health and environmental regulations/legislation specific for the substance or mixture**

16. OTHER INFORMATION**Further information**

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)

ACGIH / TWA : 8-hour, time-weighted average

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECl - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECl - Thailand Existing Chemicals Inventory; TSCA - Toxic Sub-

Cleaner additive

Version	Revision Date:	SDS Number:	Date of last issue: 12/23/2020
2.1	09/21/2021	6285816-00003	Date of first issue: 08/24/2020

stances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

LK / EN