

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

**1. PRODUCT AND COMPANY IDENTIFICATION**

Product name : HHS 2000

Product code : 893-106

**Manufacturer or supplier's details**

Company : Wurth Lanka (PVT) LTD

Address : 375/B, High Level Road  
Makumbura, Pannipitya, Sri Lanka

Telephone : 0094-112894930

Emergency telephone number : 0094-777328880

E-mail address : prodsafe@wuerth.com

Telefax : 0094-112894955

**Recommended use of the chemical and restrictions on use**

Recommended use : Lubricant

---

**2. HAZARDS IDENTIFICATION****GHS Classification**

Aerosols : Category 1

Skin corrosion/irritation : Category 2

Specific target organ toxicity -  
single exposure : Category 3

Short-term (acute) aquatic  
hazard : Category 2

Long-term (chronic) aquatic  
hazard : Category 2

**GHS label elements**

Hazard pictograms :



Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.

---

**HHS 2000**

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
 Date of first issue: 04/21/2011

H229 Pressurised container: May burst if heated.  
 H315 Causes skin irritation.  
 H336 May cause drowsiness or dizziness.  
 H411 Toxic to aquatic life with long lasting effects.

## Precautionary statements

:

**Prevention:**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
 P211 Do not spray on an open flame or other ignition source.  
 P251 Do not pierce or burn, even after use.  
 P261 Avoid breathing spray.  
 P264 Wash skin thoroughly after handling.  
 P271 Use only outdoors or in a well-ventilated area.  
 P273 Avoid release to the environment.  
 P280 Wear protective gloves.

**Response:**

P302 + P352 IF ON SKIN: Wash with plenty of water.  
 P304 + P340 + P319 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Get medical help if you feel unwell.  
 P332 + P317 If skin irritation occurs: Get medical help.  
 P362 + P364 Take off contaminated clothing and wash it before reuse.  
 P391 Collect spillage.

**Storage:**

P405 Store locked up.  
 P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

**Disposal:**

P501 Dispose of contents/ container to an approved waste disposal plant.

**Other hazards which do not result in classification**

None known.

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Substance / Mixture : Mixture

**Components**

Chemical name	CAS-No.	Concentration (% w/w)
Isobutane	75-28-5	>= 30 - < 50
Hydrocarbons, C6, isoalkanes, <5% n-hexane	64742-49-0	>= 25 - < 30
Residual oils (petroleum), hydrotreated	64742-57-0	>= 10 - < 20
Propane	74-98-6	>= 5 - < 10
Butane	106-97-8	>= 1 - < 5

**4. FIRST AID MEASURES**

**HHS 2000**

Version	Revision Date:	SDS Number:	Date of last issue: 10/13/2020
8.7	12/18/2020	320847-00007	Date of first issue: 04/21/2011

---

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.  
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.  
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes.  
Get medical attention.  
Wash clothing before reuse.  
Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.  
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.  
Get medical attention if symptoms occur.  
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Causes skin irritation.  
May cause drowsiness or dizziness.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.

**5. FIREFIGHTING MEASURES**

- Suitable extinguishing media : Water spray  
Alcohol-resistant foam  
Carbon dioxide (CO<sub>2</sub>)  
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Flash back possible over considerable distance.  
Vapours may form explosive mixtures with air.  
Exposure to combustion products may be a hazard to health.  
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
- Hazardous combustion products : Carbon oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.  
Use water spray to cool unopened containers.

**HHS 2000**

Version	Revision Date:	SDS Number:	Date of last issue: 10/13/2020
8.7	12/18/2020	320847-00007	Date of first issue: 04/21/2011

---

Remove undamaged containers from fire area if it is safe to do so.  
Evacuate area.

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.  
Use personal protective equipment.

---

**6. ACCIDENTAL RELEASE MEASURES**

Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition.  
Use personal protective equipment.  
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

Environmental precautions : Avoid release to the environment.  
Prevent further leakage or spillage if safe to do so.  
Prevent spreading over a wide area (e.g. by containment or oil barriers).  
Retain and dispose of contaminated wash water.  
Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up : Non-sparking tools should be used.  
Soak up with inert absorbent material.  
Suppress (knock down) gases/vapours/mists with a water spray jet.  
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.  
Clean up remaining materials from spill with suitable absorbent.  
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.  
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

---

**7. HANDLING AND STORAGE**

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : If sufficient ventilation is unavailable, use with local exhaust ventilation.  
If advised by assessment of the local exposure potential, use only in an area equipped with explosion-proof exhaust ventilation.

Advice on safe handling : Do not get on skin or clothing.  
Avoid breathing spray.  
Do not swallow.  
Avoid contact with eyes.

**HHS 2000**

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
 Date of first issue: 04/21/2011

Wash skin thoroughly after handling.  
 Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment  
 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
 Take precautionary measures against static discharges.  
 Take care to prevent spills, waste and minimize release to the environment.  
 Do not spray on an open flame or other ignition source.

Conditions for safe storage : Store locked up.  
 Keep in a cool, well-ventilated place.  
 Store in accordance with the particular national regulations.  
 Do not pierce or burn, even after use.  
 Keep cool. Protect from sunlight.

Materials to avoid : Do not store with the following product types:  
 Self-reactive substances and mixtures  
 Organic peroxides  
 Oxidizing agents  
 Flammable liquids  
 Pyrophoric liquids  
 Pyrophoric solids  
 Self-heating substances and mixtures  
 Explosives

Recommended storage temperature : < 40 °C

Storage period : 24 Months

Further information on storage stability : No decomposition if stored and applied as directed.

**8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Components with workplace control parameters**

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Isobutane	75-28-5	STEL	1,000 ppm	ACGIH
Hydrocarbons, C6, isoalkanes, <5% n-hexane	64742-49-0	TWA	500 ppm	ACGIH
		STEL	1,000 ppm	ACGIH
Residual oils (petroleum), hydrotreated	64742-57-0	TWA (Inhalable particulate matter)	5 mg/m <sup>3</sup>	ACGIH
Butane	106-97-8	STEL	1,000 ppm	ACGIH

**Engineering measures** : Minimize workplace exposure concentrations.  
 If sufficient ventilation is unavailable, use with local exhaust ventilation.

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

If advised by assessment of the local exposure potential, use only in an area equipped with explosion-proof exhaust ventilation.

**Personal protective equipment**

- Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.
- Filter type : Self-contained breathing apparatus
- Hand protection
- Material : Nitrile rubber
  - Break through time : 480 min
  - Glove thickness : 0.45 mm
- Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.
- Eye protection : Wear the following personal protective equipment:  
Safety glasses
- Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.  
Wear the following personal protective equipment:  
If assessment demonstrates that there is a risk of explosive atmospheres or flash fires, use flame retardant antistatic protective clothing.  
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).
- Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.  
When using do not eat, drink or smoke.  
Wash contaminated clothing before re-use.

---

**9. PHYSICAL AND CHEMICAL PROPERTIES**

- Appearance : Aerosol containing a liquefied gas
- Propellant : Isobutane, Propane, Butane
- Colour : brown

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Odour : solvent-like

Odour Threshold : No data available

pH : substance/mixture is non-soluble (in water)

Melting point/freezing point : No data available

Initial boiling point and boiling range : -42 °C

Flash point : -33 °C  
Flash point is only valid for liquid portion in the aerosol can.

Evaporation rate : Not applicable

Flammability (solid, gas) : Extremely flammable aerosol.

Upper explosion limit / Upper flammability limit : 15 %(V)

Lower explosion limit / Lower flammability limit : 1.0 %(V)

Vapour pressure : Not applicable

Relative vapour density : Not applicable

Density : 0.742 g/cm<sup>3</sup> (20 °C)  
Method: DIN 51757

Solubility(ies)  
Water solubility : insoluble

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : 250 °C

Decomposition temperature : No data available

Viscosity  
Viscosity, kinematic : > 20.5 mm<sup>2</sup>/s ( 40 °C)

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle size : Not applicable

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

**10. STABILITY AND REACTIVITY**

- Reactivity : Not classified as a reactivity hazard.
- Chemical stability : Stable under normal conditions.
- Possibility of hazardous reactions : Extremely flammable aerosol.  
Vapours may form explosive mixture with air.  
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.  
Can react with strong oxidizing agents.
- Conditions to avoid : Heat, flames and sparks.
- Incompatible materials : Oxidizing agents
- Hazardous decomposition products : No hazardous decomposition products are known.
- 

**11. TOXICOLOGICAL INFORMATION**

- Information on likely routes of exposure : Inhalation  
Skin contact  
Ingestion  
Eye contact

**Acute toxicity**

Not classified based on available information.

**Components:****Isobutane:**

- Acute inhalation toxicity : LC50 (Mouse): 260200 ppm  
Exposure time: 4 h  
Test atmosphere: gas

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

- Acute oral toxicity : LD50 (Rat): 16,750 mg/kg  
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): 259.354 mg/l  
Exposure time: 4 h  
Test atmosphere: vapour  
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rabbit): > 3,350 mg/kg  
Assessment: The substance or mixture has no acute dermal toxicity  
Remarks: Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

- Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg  
Method: OECD Test Guideline 401



## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Remarks: Based on data from similar materials

Acute inhalation toxicity : LC50 (Rat): > 5.53 mg/l  
Exposure time: 4 h  
Test atmosphere: dust/mist  
Method: OECD Test Guideline 403  
Assessment: The substance or mixture has no acute inhalation toxicity  
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg  
Method: OECD Test Guideline 402

**Propane:**

Acute inhalation toxicity : LC50 (Rat): > 800000 ppm  
Exposure time: 15 min  
Test atmosphere: gas

**Butane:**

Acute inhalation toxicity : LC50 (Rat): 658 mg/l  
Exposure time: 4 h  
Test atmosphere: vapour

**Skin corrosion/irritation**

Causes skin irritation.

**Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Species : Rabbit  
Method : OECD Test Guideline 404  
Result : Skin irritation

**Residual oils (petroleum), hydrotreated:**

Species : Rabbit  
Result : No skin irritation

**Serious eye damage/eye irritation**

Not classified based on available information.

**Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Species : Rabbit  
Result : No eye irritation  
Remarks : Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Species : Rabbit  
Result : No eye irritation

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

**Respiratory or skin sensitisation****Skin sensitisation**

Not classified based on available information.

**Respiratory sensitisation**

Not classified based on available information.

**Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Test Type : Local lymph node assay (LLNA)  
Exposure routes : Skin contact  
Species : Mouse  
Result : negative  
Remarks : Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Test Type : Maximisation Test  
Exposure routes : Skin contact  
Species : Guinea pig  
Result : negative

**Germ cell mutagenicity**

Not classified based on available information.

**Components:****Isobutane:**

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro  
Method: OECD Test Guideline 473  
Result: negative  
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative  
Remarks: Based on data from similar materials

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative  
Remarks: Based on data from similar materials

Test Type: Chromosome aberration test in vitro  
Result: negative  
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test  
Result: negative  
Remarks: Based on data from similar materials

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Genotoxicity in vivo : Test Type: Mutagenicity (in vivo mammalian bone-marrow cytogenetic test, chromosomal analysis)  
Species: Rat  
Application Route: inhalation (vapour)  
Result: negative

**Residual oils (petroleum), hydrotreated:**

Genotoxicity in vitro : Test Type: In vitro mammalian cell gene mutation test  
Method: OECD Test Guideline 476  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Mouse  
Application Route: Intraperitoneal injection  
Method: OECD Test Guideline 474  
Result: negative

**Propane:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative

**Butane:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative  
Remarks: Based on data from similar materials

**Carcinogenicity**

Not classified based on available information.

**Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Species : Rat  
Application Route : inhalation (vapour)  
Exposure time : 2 Years  
Result : negative

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Remarks : Based on data from similar materials

Species : Mouse  
Application Route : inhalation (vapour)  
Exposure time : 2 Years  
Result : negative  
Remarks : Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Species : Mouse  
Application Route : Skin contact  
Exposure time : 78 weeks  
Result : negative

**Reproductive toxicity**

Not classified based on available information.

**Components:****Isobutane:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: Inhalation  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study  
Species: Rat  
Application Route: inhalation (vapour)  
Result: negative  
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rat  
Application Route: inhalation (vapour)  
Result: negative  
Remarks: Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Species: Rat  
Application Route: Ingestion  
Method: OECD Test Guideline 421  
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rat  
Application Route: Skin contact  
Result: negative

**Propane:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

**Butane:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

**STOT - single exposure**

May cause drowsiness or dizziness.

**Components:****Isobutane:**

Assessment : May cause drowsiness or dizziness.

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Assessment : May cause drowsiness or dizziness.

**Propane:**

Assessment : May cause drowsiness or dizziness.

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

**Butane:**

Assessment : May cause drowsiness or dizziness.

**STOT - repeated exposure**

Not classified based on available information.

**Repeated dose toxicity****Components:****Isobutane:**

Species : Rat  
NOAEL : 9000 ppm  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Species : Rat, male  
NOAEL : 10.504 mg/l  
Application Route : inhalation (vapour)  
Exposure time : 90 Days  
Remarks : Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Species : Rat  
NOAEL : > 2,000 mg/kg  
Application Route : Skin contact  
Exposure time : 13 Weeks  
Method : OECD Test Guideline 411

**Propane:**

Species : Rat  
NOAEL : 7.214 mg/l  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

**Butane:**

Species : Rat  
NOAEL : 9000 ppm  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

**Aspiration toxicity**

Not classified based on available information.

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

**Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

---

**12. ECOLOGICAL INFORMATION****Ecotoxicity****Components:****Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 10 - 100 mg/l  
Exposure time: 96 h  
Test substance: Water Accommodated Fraction  
Method: OECD Test Guideline 203  
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 1 - 10 mg/l  
Exposure time: 48 h  
Test substance: Water Accommodated Fraction  
Method: OECD Test Guideline 202  
Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EL50 ( Selenastrum capricornutum (green algae)): > 10 - 100 mg/l  
Exposure time: 72 h  
Test substance: Water Accommodated Fraction  
Method: OECD Test Guideline 201  
Remarks: Based on data from similar materials

NOELR ( Selenastrum capricornutum (green algae)): 0.1 mg/l  
Exposure time: 72 h  
Test substance: Water Accommodated Fraction  
Method: OECD Test Guideline 201  
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOELR: > 0.1 - 1 mg/l  
Exposure time: 21 d  
Species: Daphnia magna (Water flea)  
Method: OECD Test Guideline 211  
Remarks: Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Toxicity to fish : LL50 (Pimephales promelas (fathead minnow)): > 100 mg/l  
Exposure time: 96 h  
Method: OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 10,000 mg/l  
Exposure time: 48 h  
Remarks: Based on data from similar materials

## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

Toxicity to algae/aquatic plants : NOEL ( Pseudokirchneriella subcapitata (green algae)): > 100 mg/l  
Exposure time: 72 h  
Method: OECD Test Guideline 201  
Remarks: Based on data from similar materials

**Persistence and degradability****Components:****Isobutane:**

Biodegradability : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Biodegradability : Result: Readily biodegradable.  
Biodegradation: 98 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301F  
Remarks: Based on data from similar materials

**Residual oils (petroleum), hydrotreated:**

Biodegradability : Result: Inherently biodegradable.  
Biodegradation: 31 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301F

**Propane:**

Biodegradability : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

**Butane:**

Biodegradability : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

**Bioaccumulative potential****Components:****Isobutane:**

Partition coefficient: n-octanol/water : log Pow: 2.8

**Hydrocarbons, C6, isoalkanes, <5% n-hexane:**

Partition coefficient: n- : log Pow: 3.6



## HHS 2000

Version 8.7      Revision Date: 12/18/2020      SDS Number: 320847-00007      Date of last issue: 10/13/2020  
Date of first issue: 04/21/2011

---

octanol/water

**Butane:**

Partition coefficient: n-octanol/water : log Pow: 2.31

**Mobility in soil**

No data available

**Other adverse effects**

No data available

---

**13. DISPOSAL CONSIDERATIONS****Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.  
Empty containers retain residue and can be dangerous.  
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.  
If not otherwise specified: Dispose of as unused product.  
Please ensure aerosol cans are sprayed completely empty (including propellant)

---

**14. TRANSPORT INFORMATION****International Regulations****UNRTDG**

UN number : UN 1950  
Proper shipping name : AEROSOLS  
Class : 2.1  
Packing group : Not assigned by regulation  
Labels : 2.1

**IATA-DGR**

UN/ID No. : UN 1950  
Proper shipping name : Aerosols, flammable  
Class : 2.1  
Packing group : Not assigned by regulation  
Labels : Flammable Gas  
Packing instruction (cargo aircraft) : 203  
Packing instruction (passenger aircraft) : 203

**IMDG-Code**

UN number : UN 1950  
Proper shipping name : AEROSOLS  
(Hydrocarbons, C6, isoalkanes, <5% n-hexane)

---

## HHS 2000

Version	Revision Date:	SDS Number:	Date of last issue: 10/13/2020
8.7	12/18/2020	320847-00007	Date of first issue: 04/21/2011

---

Class	:	2.1
Packing group	:	Not assigned by regulation
Labels	:	2.1
EmS Code	:	F-D, S-U
Marine pollutant	:	yes

**Transport in bulk according to IMO instruments**

Not applicable for product as supplied.

**Special precautions for user**

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

---

**15. REGULATORY INFORMATION****Safety, health and environmental regulations/legislation specific for the substance or mixture****16. OTHER INFORMATION****Further information**

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

**Full text of other abbreviations**

ACGIH : USA. ACGIH Threshold Limit Values (TLV)

ACGIH / TWA : 8-hour, time-weighted average

ACGIH / STEL : Short-term exposure limit

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect

## HHS 2000

Version	Revision Date:	SDS Number:	Date of last issue: 10/13/2020
8.7	12/18/2020	320847-00007	Date of first issue: 04/21/2011

---

Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

LK / EN