

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

1. PRODUCT AND COMPANY IDENTIFICATION

Product name : ADD-ENGCLNR - 250 ML

Product code : 0893016250

Manufacturer or supplier's details

Company : Wuerth India Pvt. Ltd.

Address : 703/704, Windfall, Sahar Plaza Complex
Andheri (East), Mumbai 400059

Telephone : +91 8828111830

Emergency telephone number : 1800 102 5061

E-mail address : customer.care@wuerth.in

Recommended use of the chemical and restrictions on use

Recommended use : Cleaning agent

Restrictions on use :
Not applicable

2. HAZARDS IDENTIFICATION
Manufacture, Storage and Import of Hazardous Chemicals Rules 1989
Classification

Flammable liquid

GHS Classification

Flammable liquids : Category 4

Skin corrosion/irritation : Category 2

Specific target organ toxicity - : Category 3
single exposure

Specific target organ toxicity - : Category 1 (Central nervous system)
repeated exposure

Aspiration hazard : Category 1

Short-term (acute) aquatic : Category 2
hazard

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Long-term (chronic) aquatic hazard : Category 2

GHS label elements

Hazard pictograms :



Signal word : Danger

Hazard statements : H227 Combustible liquid.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H336 May cause drowsiness or dizziness.
H372 Causes damage to organs (Central nervous system) through prolonged or repeated exposure.
H411 Toxic to aquatic life with long lasting effects.

Precautionary statements :

Prevention:

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P260 Do not breathe mist or vapours.
P264 Wash skin thoroughly after handling.
P270 Do not eat, drink or smoke when using this product.
P271 Use only outdoors or in a well-ventilated area.
P273 Avoid release to the environment.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.

Response:

P301 + P316 IF SWALLOWED: Get emergency medical help immediately.
P302 + P352 IF ON SKIN: Wash with plenty of water.
P304 + P340 + P319 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Get medical help if you feel unwell.
P331 Do NOT induce vomiting.
P332 + P317 If skin irritation occurs: Get medical help.
P362 + P364 Take off contaminated clothing and wash it before reuse.
P391 Collect spillage.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards which do not result in classification

Vapours may form explosive mixture with air.

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Solvent naphtha (petroleum), medium aliph.	64742-88-7	$\geq 90 - \leq 100$
Distillates (petroleum), solvent-dewaxed heavy paraffinic	64742-65-0	$\geq 5 - < 10$

4. FIRST AID MEASURES

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes.
Get medical attention.
Wash clothing before reuse.
Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
If vomiting occurs have person lean forward.
Call a physician or poison control centre immediately.
Rinse mouth thoroughly with water.
Never give anything by mouth to an unconscious person.
- Most important symptoms and effects, both acute and delayed : May be fatal if swallowed and enters airways.
Causes skin irritation.
May cause drowsiness or dizziness.
Causes damage to organs through prolonged or repeated exposure.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

- Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Do not use a solid water stream as it may scatter and spread fire.
Flash back possible over considerable distance.
Vapours may form explosive mixtures with air.
Exposure to combustion products may be a hazard to health.
- Hazardous combustion products : Carbon oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.
- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).
- Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
 Date of first issue: 06/07/2016

certain local or national requirements.

7. HANDLING AND STORAGE

- Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
- Local/Total ventilation : If sufficient ventilation is unavailable, use with local exhaust ventilation.
- Advice on safe handling : Do not get on skin or clothing.
 Do not breathe mist or vapours.
 Do not swallow.
 Avoid contact with eyes.
 Wash skin thoroughly after handling.
 Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
 Keep container tightly closed.
 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 Take precautionary measures against static discharges.
 Do not eat, drink or smoke when using this product.
 Take care to prevent spills, waste and minimize release to the environment.
- Conditions for safe storage : Keep in properly labelled containers.
 Store locked up.
 Keep tightly closed.
 Keep in a cool, well-ventilated place.
 Store in accordance with the particular national regulations.
 Keep away from heat and sources of ignition.
- Materials to avoid : Do not store with the following product types:
 Strong oxidizing agents
- Recommended storage temperature : 0 - 50 °C

8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Components with workplace control parameters**

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Distillates (petroleum), solvent-dewaxed heavy paraffinic	64742-65-0	TWA (Mist)	5 mg/m ³	IN OEL
		STEL (Mist)	10 mg/m ³	IN OEL
		TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Engineering measures : Minimize workplace exposure concentrations.
If sufficient ventilation is unavailable, use with local exhaust ventilation.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.

Filter type : Combined particulates and organic vapour type

Hand protection

Material : Nitrile rubber
Break through time : < 480 min
Glove thickness : 0.45 - 1 mm

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
Safety glasses

Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Wear the following personal protective equipment:
If assessment demonstrates that there is a risk of explosive atmospheres or flash fires, use flame retardant antistatic protective clothing.
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Colour : light red

Odour : slight, hydrocarbon-like

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Odour Threshold : No data available

pH : No data available

Melting point/freezing point : No data available

Initial boiling point and boiling range : No data available

Flash point : 68 °C

Evaporation rate : No data available

Flammability (solid, gas) : Not applicable

Flammability (liquids) : No data available

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : No data available

Relative vapour density : > 1

Density : 0.78 - 0.82 g/cm³ (25 °C)

Solubility(ies)
Water solubility : insoluble

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : 68 °C

Decomposition temperature : 80 °C

Viscosity
Viscosity, kinematic : < 20.5 mm²/s (40 °C)

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle size : Not applicable

10. STABILITY AND REACTIVITY

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

Reactivity	:	Not classified as a reactivity hazard.
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Combustible liquid. Vapours may form explosive mixture with air. Can react with strong oxidizing agents.
Conditions to avoid	:	Heat, flames and sparks.
Incompatible materials	:	Oxidizing agents
Hazardous decomposition products	:	No hazardous decomposition products are known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Acute oral toxicity	:	LD50 (Rat): > 5,000 mg/kg Remarks: Based on data from similar materials
Acute inhalation toxicity	:	LC50 (Rat): > 5.28 mg/l Exposure time: 4 h Test atmosphere: dust/mist Assessment: The substance or mixture has no acute inhalation toxicity Remarks: Based on data from similar materials
Acute dermal toxicity	:	LD50 (Rabbit): > 2,000 mg/kg Assessment: The substance or mixture has no acute dermal toxicity Remarks: Based on data from similar materials

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Acute oral toxicity	:	LD50 (Rat): > 5,000 mg/kg Method: OECD Test Guideline 401 Remarks: Based on data from similar materials
Acute inhalation toxicity	:	LC50 (Rat): > 5.53 mg/l Exposure time: 4 h Test atmosphere: dust/mist Method: OECD Test Guideline 403 Assessment: The substance or mixture has no acute inhalation toxicity

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg
Method: OECD Test Guideline 402
Remarks: Based on data from similar materials

Skin corrosion/irritation

Causes skin irritation.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Species : Rabbit
Result : Skin irritation

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Species : Rabbit
Result : No skin irritation
Remarks : Based on data from similar materials

Serious eye damage/eye irritation

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Species : Rabbit
Result : No eye irritation
Remarks : Based on data from similar materials

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation
Remarks : Based on data from similar materials

Respiratory or skin sensitisation**Skin sensitisation**

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Test Type : Buehler Test
Exposure routes : Skin contact
Species : Guinea pig
Result : negative
Remarks : Based on data from similar materials

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Test Type : Buehler Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative
Remarks : Based on data from similar materials

Germ cell mutagenicity

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Rodent dominant lethal test (germ cell) (in vivo)
Species: Rat (male)
Application Route: Intraperitoneal injection
Result: negative
Remarks: Based on data from similar materials

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Intraperitoneal injection
Method: OECD Test Guideline 474
Result: negative
Remarks: Based on data from similar materials

Carcinogenicity

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Species : Mouse, male
Application Route : Skin contact
Exposure time : 24 month(s)
Result : negative
Remarks : Based on data from similar materials

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Species : Mouse

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Application Route : Skin contact
Exposure time : 78 weeks
Method : OECD Test Guideline 451
Result : negative

Reproductive toxicity

Not classified based on available information.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 421
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 414
Result: negative

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Skin contact
Method: OECD Test Guideline 414
Result: negative
Remarks: Based on data from similar materials

STOT - single exposure

May cause drowsiness or dizziness.

Components:**Solvent naphtha (petroleum), medium aliph.:**

Assessment : May cause drowsiness or dizziness.

STOT - repeated exposure

Causes damage to organs (Central nervous system) through prolonged or repeated exposure.

ADD-ENGCLNR - 250 ML

Version Revision Date: SDS Number: Date of last issue: 06/09/2022
1.10 11/21/2022 10790007-00007 Date of first issue: 06/07/2016

Components:**Solvent naphtha (petroleum), medium aliph.:**

Target Organs : Central nervous system
Assessment : Causes damage to organs through prolonged or repeated exposure.

Repeated dose toxicity**Components:****Solvent naphtha (petroleum), medium aliph.:**

Species : Rat
NOAEL : 750 mg/kg
Application Route : Ingestion
Exposure time : 90 Days

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Species : Rabbit
NOAEL : 1,000 mg/kg
Application Route : Skin contact
Exposure time : 4 Weeks
Method : OECD Test Guideline 410
Remarks : Based on data from similar materials

Species : Rat
NOAEL : > 980 mg/m³
Application Route : inhalation (dust/mist/fume)
Exposure time : 4 Weeks
Remarks : Based on data from similar materials

Aspiration toxicity

May be fatal if swallowed and enters airways.

Components:**Solvent naphtha (petroleum), medium aliph.:**

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

12. ECOLOGICAL INFORMATION**Ecotoxicity****Components:****Solvent naphtha (petroleum), medium aliph.:**

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): 2 - 5 mg/l

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

Exposure time: 96 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 203
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): 1.4 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): 3.1 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

NOELR (Pseudokirchneriella subcapitata (green algae)): 0.5 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOELR: 0.48 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Test substance: Water Accommodated Fraction

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): > 100 mg/l
Exposure time: 96 h
Method: OECD Test Guideline 203
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 10,000 mg/l
Exposure time: 48 h
Method: OECD Test Guideline 202
Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EC50 (Pseudokirchneriella subcapitata (green algae)): > 100 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Toxicity to microorganisms : NOEC: > 1.93 mg/l
Exposure time: 10 min
Method: DIN 38 412 Part 8
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC: 10 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)

ADD-ENGCLNR - 250 ML

Version 1.10 Revision Date: 11/21/2022 SDS Number: 10790007-00007 Date of last issue: 06/09/2022
Date of first issue: 06/07/2016

Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

Persistence and degradability**Components:****Solvent naphtha (petroleum), medium aliph.:**

Biodegradability : Result: Not readily biodegradable.
Biodegradation: 56.8 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Distillates (petroleum), solvent-dewaxed heavy paraffinic:

Biodegradability : Result: Not readily biodegradable.
Biodegradation: 2 - 8 %
Exposure time: 28 d
Method: OECD Test Guideline 301B

Bioaccumulative potential

No data available

Mobility in soil

No data available

Other adverse effects

No data available

13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.

14. TRANSPORT INFORMATION**International Regulations****UNRTDG**

UN number : UN 3082
Proper shipping name : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
(Solvent naphtha (petroleum), medium aliph.)
Class : 9

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

Packing group : III
Labels : 9

IATA-DGR

UN/ID No. : UN 3082
Proper shipping name : Environmentally hazardous substance, liquid, n.o.s.
(Solvent naphtha (petroleum), medium aliph.)
Class : 9
Packing group : III
Labels : Miscellaneous
Packing instruction (cargo aircraft) : 964
Packing instruction (passenger aircraft) : 964
Environmentally hazardous : yes

IMDG-Code

UN number : UN 3082
Proper shipping name : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S.
(Solvent naphtha (petroleum), medium aliph.)
Class : 9
Packing group : III
Labels : 9
EmS Code : F-A, S-F
Marine pollutant : yes

Transport in bulk according to IMO instruments

Not applicable for product as supplied.

Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

15. REGULATORY INFORMATION

Safety, health and environmental regulations/legislation specific for the substance or mixture

16. OTHER INFORMATION**Further information**

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)
IN OEL : India. Permissible levels of certain chemical substances in

ADD-ENGCLNR - 250 ML

Version	Revision Date:	SDS Number:	Date of last issue: 06/09/2022
1.10	11/21/2022	10790007-00007	Date of first issue: 06/07/2016

work environment.

ACGIH / TWA	:	8-hour, time-weighted average
IN OEL / TWA	:	Time-Weighted Average Concentration (TWA) (8 hrs.)
IN OEL / STEL	:	Short-term exposure Limit STEL (15 min)

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECl - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

IN / EN