

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

Trade name : WIT-PE 510 - 585 ML (Comp. A)

Product code : 5918615585

Unique Formula Identifier (UFI) : P2C3-M0A7-E00T-J7QF

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub-stance/Mixture : Construction material, Dual-component adhesive  
Professional use product

Recommended restrictions on use : Not applicable

#### 1.3 Details of the supplier of the safety data sheet

Company : Adolf Wuerth GmbH & Co. KG  
Reinhold-Würth-Str. 12-17  
74653 Künzelsau

Telephone : +49 794015 0

Telefax : +49 794015 10 00

E-mail address of person responsible for the SDS : isi@wuerth.com

#### 1.4 Emergency telephone number

+49 (0)6132 – 84463

---

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

##### Classification (REGULATION (EC) No 1272/2008)

Skin irritation, Category 2	H315: Causes skin irritation.
Eye irritation, Category 2	H319: Causes serious eye irritation.
Skin sensitisation, Category 1	H317: May cause an allergic skin reaction.
Long-term (chronic) aquatic hazard, Cat-	H411: Toxic to aquatic life with long lasting effects.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

Category 2

Reproductive toxicity, Category 1B

H360FD: May damage fertility. May damage the unborn child.

### 2.2 Label elements

#### Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Danger

Hazard statements :

H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H360FD	May damage fertility. May damage the unborn child.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements : **Prevention:**

P201	Obtain special instructions before use.
P264	Wash skin thoroughly after handling.
P273	Avoid release to the environment.
P280	Wear protective gloves/ protective clothing/ eye protection/ face protection.

**Response:**

P308 + P313	IF exposed or concerned: Get medical advice/ attention.
P391	Collect spillage.

#### Hazardous components which must be listed on the label:

2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane  
Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2)

### 2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

### SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

##### Components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane	1675-54-3 216-823-5 603-073-00-2 01-2119456619-26	Skin Irrit. 2; H315 Eye Irrit. 2; H319 Skin Sens. 1; H317 Aquatic Chronic 2; H411  specific concentration limit Eye Irrit. 2; H319 >= 5 % Skin Irrit. 2; H315 >= 5 %	>= 50 - < 70
Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2)	933999-84-9  01-2119463471-41	Skin Irrit. 2; H315 Eye Irrit. 2; H319 Skin Sens. 1A; H317 Repr. 1B; H360FD Aquatic Chronic 3; H412	>= 10 - < 20
Quartz (SiO <sub>2</sub> )	14808-60-7 238-878-4	STOT RE 1; H372 (Lungs)	>= 1 - < 10

For explanation of abbreviations see section 16.

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

General advice : In the case of accident or if you feel unwell, seek medical advice immediately.  
When symptoms persist or in all cases of doubt seek medical advice.

Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).

If inhaled : If inhaled, remove to fresh air.  
Get medical attention.

In case of skin contact : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Get medical attention.  
Wash clothing before reuse.  
Thoroughly clean shoes before reuse.

In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.  
If easy to do, remove contact lens, if worn.  
Get medical attention.

If swallowed : If swallowed, DO NOT induce vomiting.  
Get medical attention.  
Rinse mouth thoroughly with water.

### 4.2 Most important symptoms and effects, both acute and delayed

Risks : Causes skin irritation.  
May cause an allergic skin reaction.  
Causes serious eye irritation.  
May damage fertility. May damage the unborn child.

### 4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

---

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

Suitable extinguishing media : Water spray  
Alcohol-resistant foam  
Carbon dioxide (CO<sub>2</sub>)  
Dry chemical

Unsuitable extinguishing media : High volume water jet

### 5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-fighting : Exposure to combustion products may be a hazard to health.

Hazardous combustion products : Carbon oxides  
Chlorine compounds  
Silicon oxides

### 5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.  
Use personal protective equipment.

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.  
Use water spray to cool unopened containers.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Remove undamaged containers from fire area if it is safe to do so.  
Evacuate area.

---

### SECTION 6: Accidental release measures

#### 6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.  
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

#### 6.2 Environmental precautions

Environmental precautions : Avoid release to the environment.  
Prevent further leakage or spillage if safe to do so.  
Retain and dispose of contaminated wash water.  
Local authorities should be advised if significant spillages cannot be contained.

#### 6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.  
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.  
Clean up remaining materials from spill with suitable absorbent.  
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.  
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

#### 6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

---

### SECTION 7: Handling and storage

#### 7.1 Precautions for safe handling

Technical measures	:	See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.
Local/Total ventilation	:	If sufficient ventilation is unavailable, use with local exhaust ventilation.
Advice on safe handling	:	Do not get on skin or clothing. Avoid breathing dust, fume, gas, mist, vapours or spray. Do not swallow. Do not get in eyes.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

Wash skin thoroughly after handling.  
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment  
Keep container tightly closed.  
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place. When using do not eat, drink or smoke. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before re-use.

### 7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep in properly labelled containers. Store locked up. Keep tightly closed. Store in accordance with the particular national regulations.

Advice on common storage : Do not store with the following product types:  
Strong oxidizing agents  
Self-reactive substances and mixtures  
Organic peroxides  
Explosives  
Gases

Storage class (TRGS 510) : 6.1C

Recommended storage temperature : 5 - 35 °C

### 7.3 Specific end use(s)

Specific use(s) : No data available

## SECTION 8: Exposure controls/personal protection

### 8.1 Control parameters

#### Occupational Exposure Limits

Components	CAS-No.	Value type (Form of exposure)	Control parameters	Basis
Quartz (SiO <sub>2</sub> )	14808-60-7	TWA (Respirable dust)	0,1 mg/m <sup>3</sup>	2004/37/EC
Further information: Carcinogens or mutagens				

**This substance(s) is not bioavailable and therefore does not contribute to a dust inhalation hazard.**

Quartz (SiO<sub>2</sub>)

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

### Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006

Substance name	End Use	Exposure routes	Potential health effects	Value	
Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2)	Workers	Inhalation	Long-term systemic effects	3,88 mg/m3	
	Workers	Inhalation	Acute systemic effects	3,88 mg/m3	
	Workers	Inhalation	Long-term local effects	0,44 mg/m3	
	Workers	Skin contact	Long-term systemic effects	2,2 mg/kg bw/day	
	Workers	Skin contact	Long-term local effects	0,0226 mg/cm2	
	Workers	Skin contact	Acute local effects	0,0226 mg/cm2	
	Consumers	Inhalation	Long-term systemic effects	1,94 mg/m3	
	Consumers	Inhalation	Acute systemic effects	1,94 mg/m3	
	Consumers	Inhalation	Long-term local effects	0,27 mg/m3	
	Consumers	Skin contact	Long-term systemic effects	1,1 mg/kg bw/day	
	Consumers	Skin contact	Long-term local effects	0,0136 mg/cm2	
	Consumers	Skin contact	Acute local effects	0,0136 mg/cm2	
2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane	Workers	Inhalation	Long-term systemic effects	12,25 mg/m3	
	Workers	Inhalation	Acute systemic effects	12,25 mg/m3	
	Workers	Skin contact	Long-term systemic effects	8,33 mg/kg bw/day	
	Workers	Skin contact	Acute systemic effects	8,33 mg/kg bw/day	
	Consumers	Skin contact	Long-term systemic effects	3,571 mg/kg bw/day	
	Consumers	Skin contact	Acute systemic effects	3,571 mg/kg bw/day	
	Consumers	Ingestion	Long-term systemic effects	0,75 mg/kg bw/day	
	Consumers	Ingestion	Acute systemic effects	0,75 mg/kg	

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

			fects	bw/day
--	--	--	-------	--------

### Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006

Substance name	Environmental Compartment	Value
Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2)	Fresh water	0,093 mg/l
	Freshwater - intermittent	0,093 mg/l
	Marine water	0,009 mg/l
	Sewage treatment plant	1 mg/l
	Fresh water sediment	2,29 mg/kg dry weight (d.w.)
	Marine sediment	0,229 mg/kg dry weight (d.w.)
	Soil	1,8 mg/kg dry weight (d.w.)
2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane	Fresh water	0,006 mg/l
	Freshwater - intermittent	0,018 mg/l
	Marine water	0,001 mg/l
	Marine water - intermittent	0,002 mg/l
	Sewage treatment plant	10 mg/l
	Fresh water sediment	0,996 mg/kg dry weight (d.w.)
	Marine sediment	0,1 mg/kg dry weight (d.w.)
	Soil	0,196 mg/kg dry weight (d.w.)
	Secondary Poisoning	11 mg/kg food

## 8.2 Exposure controls

### Engineering measures

- Minimize workplace exposure concentrations.
- If sufficient ventilation is unavailable, use with local exhaust ventilation.

### Personal protective equipment

Eye/face protection : Wear the following personal protective equipment:  
Safety goggles  
Equipment should conform to DIN EN 166

### Hand protection

Material : Nitrile rubber  
Break through time : > 480 min  
Glove thickness : 0,7 mm  
Directive : Equipment should conform to DIN EN 374

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the





# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Auto-ignition temperature : Not applicable

Decomposition temperature : No data available

pH : substance/mixture is non-soluble (in water)

Viscosity  
Viscosity, kinematic : Not applicable

Solubility(ies)  
Water solubility : insoluble

Partition coefficient: n-  
octanol/water : Not applicable

Vapour pressure : Not applicable

Density : 1,42 g/cm<sup>3</sup> (20 °C)

Relative vapour density : Not applicable

Particle characteristics  
Particle size : No data available

### 9.2 Other information

Explosives : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Evaporation rate : Not applicable

---

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

Not classified as a reactivity hazard.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

### 10.2 Chemical stability

Stable under normal conditions.

### 10.3 Possibility of hazardous reactions

Hazardous reactions : Can react with strong oxidizing agents.

### 10.4 Conditions to avoid

Conditions to avoid : None known.

### 10.5 Incompatible materials

Materials to avoid : Oxidizing agents

### 10.6 Hazardous decomposition products

No hazardous decomposition products are known.

---

## SECTION 11: Toxicological information

### 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure : Skin contact  
Ingestion  
Eye contact

#### Acute toxicity

|| Not classified based on available information.

#### Components:

##### **2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:**

Acute oral toxicity : LD50 (Rat): > 2.000 mg/kg  
Method: OECD Test Guideline 420  
Assessment: The substance or mixture has no acute oral toxicity  
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rat): > 2.000 mg/kg  
Method: OECD Test Guideline 402  
Assessment: The substance or mixture has no acute dermal toxicity  
Remarks: Based on data from similar materials

##### **Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):**

|| Acute oral toxicity : LD50 (Rat): > 2.000 mg/kg  
Method: OECD Test Guideline 401  
Remarks: The test was conducted according to guideline

Acute inhalation toxicity : LC50 (Rat): > 0,035 mg/l  
Exposure time: 4 h  
Test atmosphere: dust/mist

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

Acute dermal toxicity : LD50 (Rat): > 2.000 mg/kg  
Method: OECD Test Guideline 402  
Assessment: The substance or mixture has no acute dermal toxicity  
Remarks: The test was conducted according to guideline

### Quartz (SiO<sub>2</sub>):

Acute oral toxicity : LD50 (Rat): > 22.500 mg/kg

### Skin corrosion/irritation

Causes skin irritation.

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Result : Skin irritation  
Remarks : Based on national or regional regulation.

#### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Species : Rabbit  
Result : Skin irritation

### Quartz (SiO<sub>2</sub>):

Species : Rabbit  
Method : OECD Test Guideline 404  
Result : No skin irritation  
Remarks : Based on data from similar materials

### Serious eye damage/eye irritation

Causes serious eye irritation.

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Result : Irritation to eyes, reversing within 21 days  
Remarks : Based on national or regional regulation.

#### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Species : Rabbit  
Method : OECD Test Guideline 405  
Result : Irritation to eyes, reversing within 21 days  
Remarks : The test was conducted equivalent or similar to guideline

### Quartz (SiO<sub>2</sub>):

Species : Rabbit  
Method : OECD Test Guideline 405  
Result : No eye irritation  
Remarks : Based on data from similar materials

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

---

### Respiratory or skin sensitisation

#### Skin sensitisation

|| May cause an allergic skin reaction.

#### Respiratory sensitisation

|| Not classified based on available information.

#### Components:

##### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Test Type : Maximisation Test  
Exposure routes : Skin contact  
Species : Guinea pig  
Method : OECD Test Guideline 406  
Result : positive  
  
Assessment : Probability or evidence of skin sensitisation in humans

##### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

|| Test Type : Local lymph node assay (LLNA)  
|| Exposure routes : Skin contact  
|| Species : Mouse  
|| Method : OECD Test Guideline 429  
|| Result : positive  
|| Remarks : The test was conducted equivalent or similar to guideline  
  
Assessment : Probability or evidence of high skin sensitisation rate in humans

### Germ cell mutagenicity

|| Not classified based on available information.

#### Components:

##### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: equivocal  
  
Test Type: Chromosome aberration test in vitro  
Result: positive  
  
Test Type: DNA damage and repair, unscheduled DNA synthesis in mammalian cells (in vitro)  
Result: negative  
  
Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Mouse  
Application Route: Ingestion  
Result: negative

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version 5.0      Revision Date: 12.11.2024      SDS Number: 8169397-00011      Date of last issue: 25.06.2024  
Date of first issue: 09.04.2021

### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Method: OECD Test Guideline 471  
Result: positive  
Remarks: The test was conducted according to guideline

Test Type: in vitro micronucleus test  
Method: OECD Test Guideline 487  
Result: positive  
Remarks: The test was conducted according to guideline

Genotoxicity in vivo : Test Type: Unscheduled DNA synthesis (UDS) test with  
mammalian liver cells in vivo  
Species: Rat  
Application Route: Ingestion  
Method: OECD Test Guideline 486  
Result: negative  
Remarks: The test was conducted according to guideline

### Carcinogenicity

Not classified based on available information.

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Species : Rat  
Application Route : Ingestion  
Exposure time : 24 Months  
Method : OECD Test Guideline 453  
Result : negative

Species : Mouse  
Application Route : Skin contact  
Exposure time : 24 Months  
Method : OECD Test Guideline 453  
Result : negative

### Reproductive toxicity

May damage fertility. May damage the unborn child.

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Effects on fertility : Test Type: Two-generation reproduction toxicity study  
Species: Rat  
Application Route: Ingestion  
Method: OECD Test Guideline 416  
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rabbit  
Application Route: Skin contact

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

Result: negative

### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Effects on fertility	:	Test Type: One-generation reproduction toxicity study Species: Rat Application Route: Ingestion Method: OECD Test Guideline 443 Result: positive Remarks: The test was conducted according to guideline
Effects on foetal development	:	Test Type: Embryo-foetal development Species: Rabbit Application Route: Ingestion Method: OECD Test Guideline 414 Result: positive Remarks: The test was conducted according to guideline
Reproductive toxicity - Assessment	:	Clear evidence of adverse effects on sexual function and fertility, based on animal experiments., Clear evidence of adverse effects on development, based on animal experiments.

### STOT - single exposure

|| Not classified based on available information.

### STOT - repeated exposure

|| Not classified based on available information.

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Assessment : No significant health effects observed in animals at concentrations of 200 mg/kg bw or less.

#### Quartz (SiO<sub>2</sub>):

Exposure routes : inhalation (dust/mist/fume)  
Target Organs : Lungs  
Assessment : Shown to produce significant health effects in animals at concentrations of 0.02 mg/l/6h/d or less.

### Repeated dose toxicity

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Species : Rat  
NOAEL : 50 mg/kg  
LOAEL : 250 mg/kg  
Application Route : Ingestion  
Exposure time : 90 Days  
Method : OECD Test Guideline 408

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Species	:	Mouse
NOAEL	:	>= 100 mg/kg
Application Route	:	Skin contact
Exposure time	:	13 Weeks
Method	:	OECD Test Guideline 411

### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Species	:	Rat
NOAEL	:	>= 300 mg/kg
Application Route	:	Ingestion
Exposure time	:	90 Days
Method	:	OECD Test Guideline 408
Remarks	:	The test was conducted according to guideline

### Quartz (SiO<sub>2</sub>):

Species	:	Humans
LOAEL	:	0,053 mg/m <sup>3</sup>
Application Route	:	Inhalation
Remarks	:	This substance(s) is not bioavailable and therefore does not contribute to a dust inhalation hazard.

### Aspiration toxicity

|| Not classified based on available information.

## 11.2 Information on other hazards

### Endocrine disrupting properties

#### Product:

Assessment	:	The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.
------------	---	---

---

## SECTION 12: Ecological information

### 12.1 Toxicity

#### Components:

#### **2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:**

Toxicity to fish	:	LL50 (Oncorhynchus mykiss (rainbow trout)): > 1 - 10 mg/l Exposure time: 96 h Test substance: Water Accommodated Fraction Method: OECD Test Guideline 203 Remarks: Based on data from similar materials
------------------	---	---

Toxicity to daphnia and other	:	EL50 (Daphnia magna (Water flea)): > 1 - 10 mg/l
-------------------------------	---	--



# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

aquatic invertebrates		Exposure time: 48 h Test substance: Water Accommodated Fraction Remarks: Based on data from similar materials
Toxicity to algae/aquatic plants	:	EL50 (Scenedesmus capricornutum (fresh water algae)): > 10 - 100 mg/l Exposure time: 72 h Test substance: Water Accommodated Fraction Remarks: Based on data from similar materials  NOELR (Scenedesmus capricornutum (fresh water algae)): > 1 mg/l Exposure time: 72 h Test substance: Water Accommodated Fraction Remarks: Based on data from similar materials
Toxicity to microorganisms	:	IC50 : > 100 mg/l Exposure time: 3 h Remarks: Based on data from similar materials
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	:	NOEC: > 0,1 - 1 mg/l Exposure time: 21 d Species: Daphnia magna (Water flea) Remarks: Based on data from similar materials

### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Toxicity to fish	:	LC50 (Oncorhynchus mykiss (rainbow trout)): 30 mg/l Exposure time: 96 h Method: OECD Test Guideline 203 Remarks: The test was conducted according to guideline
Toxicity to daphnia and other aquatic invertebrates	:	EC50 (Daphnia magna (Water flea)): 47 mg/l Exposure time: 48 h Method: OECD Test Guideline 202 Remarks: The test was conducted according to guideline
Toxicity to algae/aquatic plants	:	ErC50 (Raphidocelis subcapitata (freshwater green alga)): 27 mg/l Exposure time: 72 h Method: OECD Test Guideline 201 Remarks: The test was conducted according to guideline
Toxicity to microorganisms	:	EC50 (activated sludge): > 100 mg/l Exposure time: 3 h Method: OECD Test Guideline 209 Remarks: The test was conducted according to guideline
Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity)	:	EC10: > 1 mg/l Exposure time: 21 d Species: Daphnia magna (Water flea) Method: OECD Test Guideline 211 Remarks: The test was conducted according to guideline

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021



Based on data from similar materials

### Quartz (SiO<sub>2</sub>):

Toxicity to fish : LC50 (Danio rerio (zebra fish)): 508 mg/l  
Exposure time: 96 h  
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 731 mg/l  
Exposure time: 48 h  
Remarks: Based on data from similar materials

## 12.2 Persistence and degradability

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Biodegradability : Result: Not readily biodegradable.  
Biodegradation: 5 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301F

#### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Biodegradability : Result: Not readily biodegradable.  
Biodegradation: 47 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301D  
Remarks: The test was conducted according to guideline

## 12.3 Bioaccumulative potential

### Components:

#### 2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane:

Partition coefficient: n-octanol/water : log Pow: 3,5

#### Reaction products of hexane-1,6-diol with 2-(chloromethyl)oxirane (1:2):

Partition coefficient: n-octanol/water : log Pow: 0,822  
Method: OECD Test Guideline 107  
Remarks: The test was conducted according to guideline

## 12.4 Mobility in soil

No data available

## 12.5 Results of PBT and vPvB assessment

### Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

0.1% or higher.

### 12.6 Endocrine disrupting properties

**Product:**

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

### 12.7 Other adverse effects

No data available

---

## SECTION 13: Disposal considerations

### 13.1 Waste treatment methods

Product	: Dispose of in accordance with local regulations. According to the European Waste Catalogue, Waste Codes are not product specific, but application specific. Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities. Do not dispose of waste into sewer.
Contaminated packaging	: Empty containers should be taken to an approved waste handling site for recycling or disposal. If not otherwise specified: Dispose of as unused product.
Waste Code	: The following Waste Codes are only suggestions:  used product 08 04 09*, waste adhesives and sealants containing organic solvents or other hazardous substances  unused product 08 04 09*, waste adhesives and sealants containing organic solvents or other hazardous substances  uncleaned packagings 15 01 10*, packaging containing residues of or contaminated by hazardous substances  Acc. Packaging Act properly emptied packaging: Properly emptied, non-contaminated packaging of non-hazardous products can be supplied to a system for the collection of sales packaging.

---

## SECTION 14: Transport information

### 14.1 UN number or ID number

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

**ADN** : UN 3077  
**ADR** : UN 3077  
**RID** : UN 3077  
**IMDG** : UN 3077  
**IATA** : UN 3077

### 14.2 UN proper shipping name

**ADN** : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.  
(2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane)

**ADR** : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.  
(2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane)

**RID** : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.  
(2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane)

**IMDG** : ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.  
(2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane)

**IATA** : Environmentally hazardous substance, solid, n.o.s.  
(2,2'-[(1-Methylethylidene)bis(4,1-phenyleneoxymethylene)]bisoxirane)

### 14.3 Transport hazard class(es)

	Class	Subsidiary risks
<b>ADN</b>	: 9	
<b>ADR</b>	: 9	
<b>RID</b>	: 9	
<b>IMDG</b>	: 9	
<b>IATA</b>	: 9	

### 14.4 Packing group

**ADN**  
Packing group : III  
Classification Code : M7  
Hazard Identification Number : 90  
Labels : 9

**ADR**  
Packing group : III  
Classification Code : M7

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Hazard Identification Number : 90  
Labels : 9  
Tunnel restriction code : (-)

### RID

Packing group : III  
Classification Code : M7  
Hazard Identification Number : 90  
Labels : 9

### IMDG

Packing group : III  
Labels : 9  
EmS Code : F-A, S-F

### IATA (Cargo)

Packing instruction (cargo aircraft) : 956  
Packing instruction (LQ) : Y956  
Packing group : III  
Labels : Miscellaneous

### IATA (Passenger)

Packing instruction (passenger aircraft) : 956  
Packing instruction (LQ) : Y956  
Packing group : III  
Labels : Miscellaneous

## 14.5 Environmental hazards

### ADN

Environmentally hazardous : yes

### ADR

Environmentally hazardous : yes

### RID

Environmentally hazardous : yes

### IMDG

Marine pollutant : yes

### IATA (Passenger)

Environmentally hazardous : yes

### IATA (Cargo)

Environmentally hazardous : yes

## 14.6 Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

## 14.7 Maritime transport in bulk according to IMO instruments

Remarks : Not applicable for product as supplied.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

### SECTION 15: Regulatory information

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles (Annex XVII)

Substance(s) or mixture(s) are listed here according to their appearance in the regulation, irrespective of their use/purpose or the conditions of the restriction. Please refer to the conditions in corresponding Regulation to determine whether an entry is applicable to the placing on the market or not.

Conditions of restriction for the following entries should be considered:  
Number on list 75: If you intend to use this product as tattoo ink, please contact your vendor.

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : Not applicable

Regulation (EC) on substances that deplete the ozone layer : Not applicable

Regulation (EU) 2019/1021 on persistent organic pollutants (recast) : Not applicable

Regulation (EU) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

E2	ENVIRONMENTAL HAZARDS	Quantity 1	Quantity 2
		200 t	500 t

Water hazard class (Germany) : WGK 2 obviously hazardous to water  
Classification according to AwSV, Annex 1 (5.2)

TA Luft List (Germany) : 5.2.1: Total dust:  
Not applicable  
5.2.2: Inorganic substances in powdered form:  
Not applicable

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

5.2.4: Inorganic substances in gaseous form:  
Not applicable  
5.2.5: Organic Substances:  
Not applicable  
5.2.7.1.1: Carcinogenic substance:  
Not applicable  
5.2.7.1.1: Quartz fine dust PM4:  
others: 2,49 % Quartz (SiO<sub>2</sub>)  
5.2.7.1.1: Formaldehyde:  
Not applicable  
5.2.7.1.1: fibres:  
Not applicable  
5.2.7.2: Poorly degradable, easily enrichable and highly toxic  
organic substances:  
Not applicable

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial  
emissions (integrated pollution prevention and control)  
Volatile organic compounds (VOC) content: < 0,1 %

### Other regulations:

Take note of Directive 94/33/EC on the protection of young people at work or stricter national  
regulations, where applicable.

Take note of Law on the protection of mothers at work, in education and in studies (Maternity  
Protection Act - MuSchG).

The product is subject to the supply restrictions of the Ordinance on the Prohibition of Chemi-  
cals.

### 15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

---

## SECTION 16: Other information

Other information : Items where changes have been made to the previous version  
are highlighted in the body of this document by two vertical  
lines.

### Full text of H-Statements

H315 : Causes skin irritation.  
H317 : May cause an allergic skin reaction.  
H319 : Causes serious eye irritation.  
H360FD : May damage fertility. May damage the unborn child.  
H372 : Causes damage to organs through prolonged or repeated  
exposure if inhaled.  
H411 : Toxic to aquatic life with long lasting effects.  
H412 : Harmful to aquatic life with long lasting effects.

# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

### Full text of other abbreviations

Aquatic Chronic	:	Long-term (chronic) aquatic hazard
Eye Irrit.	:	Eye irritation
Repr.	:	Reproductive toxicity
Skin Irrit.	:	Skin irritation
Skin Sens.	:	Skin sensitisation
STOT RE	:	Specific target organ toxicity - repeated exposure
2004/37/EC	:	Europe. Directive 2004/37/EC on the protection of workers from the risks related to exposure to carcinogens or mutagens at work
2004/37/EC / TWA	:	Long term exposure limit

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - Agreement concerning the International Carriage of Dangerous Goods by Road; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; SVHC - Substance of Very High Concern; TCSI - Taiwan Chemical Substance Inventory; TECI - Thailand Existing Chemicals Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

### Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

### Classification of the mixture:

Skin Irrit. 2 H315

### Classification procedure:

Calculation method



# SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006, as amended by  
Commission Regulation (EU) 2020/878



## WIT-PE 510 - 585 ML (Comp. A)

Version	Revision Date:	SDS Number:	Date of last issue: 25.06.2024
5.0	12.11.2024	8169397-00011	Date of first issue: 09.04.2021

---

Eye Irrit. 2	H319	Calculation method
Skin Sens. 1	H317	Calculation method
Aquatic Chronic 2	H411	Calculation method
Repr. 1B	H360FD	Calculation method

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

DE / EN