

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

### 1. PRODUCT AND COMPANY IDENTIFICATION

Product name : WSCRNCLNR-ACTIVE-500ML

Product code : 089025

#### Manufacturer or supplier's details

Company : Wurth Lanka (PVT) LTD

Address : 375/B, High Level Road  
Makumbura, Pannipitya, Sri Lanka

Telephone : 0094-112894930

Emergency telephone number : 0094-777328880

E-mail address : prodsafe@wuerth.com

Telefax : 0094-112894955

#### Recommended use of the chemical and restrictions on use

Recommended use :  
Cleaning agent  
Detergent

Restrictions on use : Not applicable

---

### 2. HAZARDS IDENTIFICATION



#### GHS Classification

Aerosols : Category 1

Serious eye damage/eye irritation : Category 2A

Specific target organ toxicity - single exposure : Category 3

#### GHS label elements

Hazard pictograms :  

Signal word : Danger

Hazard statements : H222 Extremely flammable aerosol.

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

H229 Pressurised container: May burst if heated.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.

Precautionary statements :

### Prevention:

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P211 Do not spray on an open flame or other ignition source.  
P251 Do not pierce or burn, even after use.  
P261 Avoid breathing spray.  
P264+P265 Wash hands thoroughly after handling. Do not touch eyes.  
P271 Use only outdoors or in a well-ventilated area.  
P280 Wear eye protection/ face protection.

### Response:

P304 + P340 + P319 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Get medical help if you feel unwell.  
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P337 + P317 If eye irritation persists: Get medical help.

### Storage:

P405 Store locked up.  
P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

### Disposal:

P501 Dispose of contents/ container to an approved waste disposal plant.

### Other hazards which do not result in classification

None known.

## 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

### Components

Chemical name	CAS-No.	Concentration (% w/w)
Propan-2-ol	67-63-0	>= 10 - < 20
Butane	106-97-8	>= 1 - < 5
Isobutane	75-28-5	>= 1 - < 5
Propane	74-98-6	>= 1 - < 5
1-Methoxy-2-propanol	107-98-2	>= 1 - < 5
(R)-p-mentha-1,8-diene	5989-27-5	>= 0.1 - < 0.25

## 4. FIRST AID MEASURES

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.  
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.  
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water.  
Get medical attention if symptoms occur.
- In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.  
If easy to do, remove contact lens, if worn.  
Get medical attention.
- If swallowed : If swallowed, DO NOT induce vomiting.  
Get medical attention if symptoms occur.  
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Causes serious eye irritation.  
May cause drowsiness or dizziness.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.
- 

### 5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray  
Alcohol-resistant foam  
Carbon dioxide (CO<sub>2</sub>)  
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Flash back possible over considerable distance.  
Vapours may form explosive mixtures with air.  
Exposure to combustion products may be a hazard to health.  
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
- Hazardous combustion products : Carbon oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.  
Use water spray to cool unopened containers.  
Remove undamaged containers from fire area if it is safe to do so.
-

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

Evacuate area.

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus. Use personal protective equipment.

---

### 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition. Use personal protective equipment. Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

Environmental precautions : Avoid release to the environment. Prevent further leakage or spillage if safe to do so. Prevent spreading over a wide area (e.g. by containment or oil barriers). Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up : Non-sparking tools should be used. Soak up with inert absorbent material. Suppress (knock down) gases/vapours/mists with a water spray jet. For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absorbent. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

---

### 7. HANDLING AND STORAGE

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use with local exhaust ventilation.

Advice on safe handling : Avoid breathing spray. Do not swallow. Do not get in eyes. Avoid prolonged or repeated contact with skin. Wash skin thoroughly after handling. Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

---

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

Take precautionary measures against static discharges.  
Take care to prevent spills, waste and minimize release to the environment.  
Do not spray on an open flame or other ignition source.

Conditions for safe storage : Store locked up.  
Keep in a cool, well-ventilated place.  
Store in accordance with the particular national regulations.  
Do not pierce or burn, even after use.  
Keep cool. Protect from sunlight.

Materials to avoid : Do not store with the following product types:  
Self-reactive substances and mixtures  
Organic peroxides  
Oxidizing agents  
Flammable liquids  
Pyrophoric liquids  
Pyrophoric solids  
Self-heating substances and mixtures  
Explosives

Recommended storage temperature : > 5 - < 40 °C

### 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

#### Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Propan-2-ol	67-63-0	TWA	200 ppm	ACGIH
		STEL	400 ppm	ACGIH
Butane	106-97-8	STEL	1,000 ppm	ACGIH
Isobutane	75-28-5	STEL	1,000 ppm	ACGIH
1-Methoxy-2-propanol	107-98-2	TWA	50 ppm	ACGIH
		STEL	100 ppm	ACGIH

#### Biological occupational exposure limits

Components	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
Propan-2-ol	67-63-0	Acetone	Urine	End of shift at end of work-week	40 mg/l	ACGIH BEI

Engineering measures : Minimize workplace exposure concentrations.  
Use with local exhaust ventilation.

#### Personal protective equipment

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

- Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.
- Filter type : Self-contained breathing apparatus
- Hand protection
- Remarks : not required Wash hands before breaks and at the end of workday.
- Eye protection : Wear the following personal protective equipment:  
Safety goggles
- Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.  
Wear the following personal protective equipment:  
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).
- Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.  
When using do not eat, drink or smoke.  
Wash contaminated clothing before re-use.
- 

### 9. PHYSICAL AND CHEMICAL PROPERTIES

- Appearance : Aerosol containing a dissolved gas
- Propellant : Propane, Butane, Isobutane
- Colour : colourless
- Odour : fruity
- Odour Threshold : No data available
- pH : 9.5  
Concentration: 100 %  
pH value is valid for liquid portion in the aerosol can
- Melting point/freezing point : No data available
- Initial boiling point and boiling range : Not applicable

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

Flash point	:	34 °C	
			Flash point is only valid for liquid portion in the aerosol can.
Evaporation rate	:	Not applicable	
Flammability (solid, gas)	:	Extremely flammable aerosol.	
Upper explosion limit / Upper flammability limit	:	No data available	
Lower explosion limit / Lower flammability limit	:	No data available	
Vapour pressure	:	Not applicable	
Relative vapour density	:	Not applicable	
Density	:	0.98 g/cm <sup>3</sup> (20 °C)	
Solubility(ies) Water solubility	:	completely soluble	
Partition coefficient: n-octanol/water	:	Not applicable	
Auto-ignition temperature	:	No data available	
Decomposition temperature	:	No data available	
Viscosity Viscosity, kinematic	:	Not applicable	
Explosive properties	:	Not explosive	
Oxidizing properties	:	The substance or mixture is not classified as oxidizing.	
Particle size	:	Not applicable	

---

### 10. STABILITY AND REACTIVITY

Reactivity	:	Not classified as a reactivity hazard.
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Extremely flammable aerosol. Vapours may form explosive mixture with air. If the temperature rises there is danger of the vessels bursting due to the high vapor pressure. Can react with strong oxidizing agents.
Conditions to avoid	:	Heat, flames and sparks.

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

Incompatible materials : Oxidizing agents  
Acids

Hazardous decomposition products : No hazardous decomposition products are known.

---

### 11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure : Inhalation  
Skin contact  
Ingestion  
Eye contact

#### Acute toxicity

Not classified based on available information.

#### Product:

Acute oral toxicity : Acute toxicity estimate: > 5,000 mg/kg  
Method: Calculation method

Acute inhalation toxicity : Acute toxicity estimate: > 40 mg/l  
Exposure time: 4 h  
Test atmosphere: vapour  
Method: Calculation method

#### Components:

##### **Propan-2-ol:**

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 25 mg/l  
Exposure time: 6 h  
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg

##### **Butane:**

Acute inhalation toxicity : LC50 (Rat): 658 mg/l  
Exposure time: 4 h  
Test atmosphere: vapour

##### **Isobutane:**

Acute inhalation toxicity : LC50 (Mouse): 260200 ppm  
Exposure time: 4 h  
Test atmosphere: gas

##### **Propane:**

Acute inhalation toxicity : LC50 (Rat): > 800000 ppm  
Exposure time: 15 min  
Test atmosphere: gas



# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

### 1-Methoxy-2-propanol:

Acute oral toxicity : LD50 (Rat): 4,016 mg/kg

Acute inhalation toxicity : LC50 (Mouse): < 22.2 mg/l  
Exposure time: 6 h  
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg  
Assessment: The substance or mixture has no acute dermal toxicity

### (R)-p-mentha-1,8-diene:

Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg  
Method: OECD Test Guideline 423  
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg  
Remarks: Based on data from similar materials

### Skin corrosion/irritation

Not classified based on available information.

### Components:

#### Propan-2-ol:

Species : Rabbit  
Result : No skin irritation

#### 1-Methoxy-2-propanol:

Species : Rabbit  
Result : No skin irritation

#### (R)-p-mentha-1,8-diene:

Species : Rabbit  
Method : OECD Test Guideline 404  
Result : Skin irritation

### Serious eye damage/eye irritation

Causes serious eye irritation.

### Components:

#### Propan-2-ol:

Species : Rabbit  
Result : Irritation to eyes, reversing within 21 days

#### 1-Methoxy-2-propanol:

Species : Rabbit  
Result : No eye irritation

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

### **(R)-p-mentha-1,8-diene:**

Species : Rabbit  
Method : OECD Test Guideline 405  
Result : No eye irritation

### **Respiratory or skin sensitisation**

#### **Skin sensitisation**

Not classified based on available information.

#### **Respiratory sensitisation**

Not classified based on available information.

### **Components:**

#### **Propan-2-ol:**

Test Type : Buehler Test  
Exposure routes : Skin contact  
Species : Guinea pig  
Method : OECD Test Guideline 406  
Result : negative

#### **1-Methoxy-2-propanol:**

Test Type : Maximisation Test  
Exposure routes : Skin contact  
Species : Guinea pig  
Result : negative

### **(R)-p-mentha-1,8-diene:**

Test Type : Local lymph node assay (LLNA)  
Exposure routes : Skin contact  
Species : Mouse  
Method : OECD Test Guideline 429  
Result : positive

Assessment : Probability or evidence of low to moderate skin sensitisation rate in humans

### **Germ cell mutagenicity**

Not classified based on available information.

### **Components:**

#### **Propan-2-ol:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Test Type: In vitro mammalian cell gene mutation test  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo)

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

cytogenetic assay)  
Species: Mouse  
Application Route: Intraperitoneal injection  
Result: negative

### **Butane:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo  
cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative  
Remarks: Based on data from similar materials

### **Isobutane:**

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro  
Method: OECD Test Guideline 473  
Result: negative  
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo  
cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative  
Remarks: Based on data from similar materials

### **Propane:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo  
cytogenetic assay)  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 474  
Result: negative

### **1-Methoxy-2-propanol:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Result: negative

Test Type: Chromosome aberration test in vitro  
Result: negative

Test Type: In vitro mammalian cell gene mutation test  
Result: negative

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

Test Type: In vitro sister chromatid exchange assay in mammalian cells  
Result: equivocal

Test Type: DNA damage and repair, unscheduled DNA synthesis in mammalian cells (in vitro)  
Method: OECD Test Guideline 482  
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)  
Species: Mouse  
Application Route: Intraperitoneal injection  
Result: negative

### **(R)-p-mentha-1,8-diene:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)  
Method: OECD Test Guideline 471  
Result: negative  
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test  
Result: negative

Test Type: Chromosome aberration test in vitro  
Result: negative

Genotoxicity in vivo : Test Type: In vivo mammalian alkaline comet assay  
Species: Rat  
Application Route: Ingestion  
Result: negative

### **Carcinogenicity**

Not classified based on available information.

### **Components:**

#### **Propan-2-ol:**

Species : Rat  
Application Route : inhalation (vapour)  
Exposure time : 104 weeks  
Method : OECD Test Guideline 451  
Result : negative

#### **1-Methoxy-2-propanol:**

Species : Rat  
Application Route : inhalation (vapour)  
Exposure time : 2 Years  
Method : OECD Test Guideline 453  
Result : negative

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

### **(R)-p-mentha-1,8-diene:**

Species : Mouse  
Application Route : Ingestion  
Exposure time : 103 weeks  
Result : negative

### **Reproductive toxicity**

Not classified based on available information.

### **Components:**

#### **Propan-2-ol:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study  
Species: Rat  
Application Route: Ingestion  
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rat  
Application Route: Ingestion  
Result: negative

#### **Butane:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

#### **Isobutane:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: Inhalation  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

#### **Propane:**

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test  
Species: Rat  
Application Route: inhalation (gas)  
Method: OECD Test Guideline 422  
Result: negative

### **1-Methoxy-2-propanol:**

Effects on fertility : Test Type: Two-generation reproduction toxicity study  
Species: Rat  
Application Route: inhalation (vapour)  
Method: OECD Test Guideline 416  
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rat  
Application Route: inhalation (vapour)  
Result: negative

### **(R)-p-mentha-1,8-diene:**

Effects on foetal development : Test Type: Embryo-foetal development  
Species: Rat  
Application Route: Ingestion  
Result: negative

### **STOT - single exposure**

May cause drowsiness or dizziness.

#### **Components:**

##### **Propan-2-ol:**

Assessment : May cause drowsiness or dizziness.

##### **Butane:**

Assessment : May cause drowsiness or dizziness.

##### **Isobutane:**

Assessment : May cause drowsiness or dizziness.

##### **Propane:**

Assessment : May cause drowsiness or dizziness.

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

### 1-Methoxy-2-propanol:

Assessment : May cause drowsiness or dizziness.

### STOT - repeated exposure

Not classified based on available information.

### Components:

#### (R)-p-mentha-1,8-diene:

Assessment : No significant health effects observed in animals at concentrations of 100 mg/kg bw or less.

### Repeated dose toxicity

#### Components:

##### Propan-2-ol:

Species : Rat  
NOAEL : 12.5 mg/l  
Application Route : inhalation (vapour)  
Exposure time : 104 Weeks

##### Butane:

Species : Rat  
NOAEL : 9000 ppm  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

##### Isobutane:

Species : Rat  
NOAEL : 9000 ppm  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

##### Propane:

Species : Rat  
NOAEL : 7.214 mg/l  
Application Route : inhalation (gas)  
Exposure time : 6 Weeks  
Method : OECD Test Guideline 422

### 1-Methoxy-2-propanol:

Species : Rat  
NOAEL : 919 mg/kg  
Application Route : Ingestion  
Exposure time : 35 Days

Species : Rat

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

NOAEL : 1.1 mg/l  
Application Route : inhalation (vapour)  
Exposure time : 2 yr  
Method : OECD Test Guideline 453

Species : Rabbit  
NOAEL : 1,838 mg/kg  
Application Route : Skin contact  
Exposure time : 90 Days

### **(R)-p-mentha-1,8-diene:**

Species : Rat, male  
NOAEL : 5 mg/kg  
LOAEL : 30 mg/kg  
Application Route : Ingestion  
Exposure time : 13 Weeks

### **Aspiration toxicity**

Not classified based on available information.

### **Components:**

#### **(R)-p-mentha-1,8-diene:**

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

---

## 12. ECOLOGICAL INFORMATION

### **Ecotoxicity**

#### **Components:**

##### **Propan-2-ol:**

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l  
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 10,000 mg/l  
Exposure time: 24 h

Toxicity to microorganisms : EC50 (Pseudomonas putida): > 1,050 mg/l  
Exposure time: 16 h

##### **1-Methoxy-2-propanol:**

Toxicity to fish : LC50 (Leuciscus idus (Golden orfe)): 6,812 mg/l  
Exposure time: 96 h  
Method: DIN 38412

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 23,300 mg/l  
Exposure time: 48 h

Toxicity to algae/aquatic : ErC50 ( Skeletonema costatum (marine diatom)): 6,745 mg/l



# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

plants      Exposure time: 72 h  
Method: ISO 10253

Toxicity to microorganisms      :      IC50: > 1,000 mg/l  
Exposure time: 3 h  
Method: OECD Test Guideline 209

### **(R)-p-mentha-1,8-diene:**

Toxicity to fish      :      LC50 (Pimephales promelas (fathead minnow)): 0.720 mg/l  
Exposure time: 96 h

Toxicity to daphnia and other      :      EC50 (Daphnia magna (Water flea)): 307 µg/l  
aquatic invertebrates      Exposure time: 48 h  
Method: OECD Test Guideline 202

Toxicity to algae/aquatic      :      ErC50 ( Pseudokirchneriella subcapitata (green algae)): 0.25  
plants      mg/l  
Exposure time: 72 h  
Method: OECD Test Guideline 201

EC10 ( Pseudokirchneriella subcapitata (green algae)): 0.14  
mg/l  
Exposure time: 72 h  
Method: OECD Test Guideline 201

M-Factor (Acute aquatic tox-      :      1  
icity)

Toxicity to microorganisms      :      EC50: > 100 mg/l  
Exposure time: 3 h  
Method: OECD Test Guideline 209  
Remarks: Based on data from similar materials

Toxicity to fish (Chronic tox-      :      EC10: 0.37 mg/l  
icity)      Exposure time: 8 d  
Species: Pimephales promelas (fathead minnow)

Toxicity to daphnia and other      :      EC10: 0.153 mg/l  
aquatic invertebrates (Chron-      Exposure time: 21 d  
ic toxicity)      Species: Daphnia magna (Water flea)  
Method: OECD Test Guideline 211

### **Persistence and degradability**

#### **Components:**

##### **Propan-2-ol:**

Biodegradability      :      Result: rapidly degradable

BOD/COD      :      BOD: 1.19 (BOD5)COD: 2.23BOD/COD: 53 %

##### **Butane:**

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version 6.2      Revision Date: 10/31/2023      SDS Number: 10630546-00014      Date of last issue: 07/26/2023  
Date of first issue: 06/04/2012

---

**Biodegradability** : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

### **Isobutane:**

**Biodegradability** : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

### **Propane:**

**Biodegradability** : Result: Readily biodegradable.  
Biodegradation: 100 %  
Exposure time: 385.5 h  
Remarks: Based on data from similar materials

### **1-Methoxy-2-propanol:**

**Biodegradability** : Result: Readily biodegradable.  
Biodegradation: 96 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301E

### **(R)-p-mentha-1,8-diene:**

**Biodegradability** : Result: Readily biodegradable.  
Biodegradation: 71.4 %  
Exposure time: 28 d  
Method: OECD Test Guideline 301B

## **Bioaccumulative potential**

### **Components:**

#### **Propan-2-ol:**

Partition coefficient: n-octanol/water : log Pow: 0.05

#### **Butane:**

Partition coefficient: n-octanol/water : log Pow: 2.31

#### **Isobutane:**

Partition coefficient: n-octanol/water : log Pow: 2.8

#### **1-Methoxy-2-propanol:**

Partition coefficient: n-octanol/water : log Pow: < 1

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version	Revision Date:	SDS Number:	Date of last issue: 07/26/2023
6.2	10/31/2023	10630546-00014	Date of first issue: 06/04/2012

### (R)-p-mentha-1,8-diene:

Partition coefficient: n-octanol/water : log Pow: 4.38

### Mobility in soil

No data available

### Other adverse effects

No data available

## 13. DISPOSAL CONSIDERATIONS

### Disposal methods

Waste from residues : Do not dispose of waste into sewer.

Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.  
Empty containers retain residue and can be dangerous.  
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.  
If not otherwise specified: Dispose of as unused product.  
Please ensure aerosol cans are sprayed completely empty (including propellant)

## 14. TRANSPORT INFORMATION

### International Regulations

#### UNRTDG

UN number : UN 1950  
Proper shipping name : AEROSOLS  
Class : 2.1  
Packing group : Not assigned by regulation  
Labels : 2.1  
Environmentally hazardous : no

#### IATA-DGR

UN/ID No. : UN 1950  
Proper shipping name : Aerosols, flammable  
Class : 2.1  
Packing group : Not assigned by regulation  
Labels : Flammable Gas  
Packing instruction (cargo aircraft) : 203  
Packing instruction (passenger aircraft) : 203

#### IMDG-Code

UN number : UN 1950  
Proper shipping name : AEROSOLS

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version	Revision Date:	SDS Number:	Date of last issue: 07/26/2023
6.2	10/31/2023	10630546-00014	Date of first issue: 06/04/2012

Class : 2.1  
Packing group : Not assigned by regulation  
Labels : 2.1  
EmS Code : F-D, S-U  
Marine pollutant : no

### Transport in bulk according to IMO instruments

Not applicable for product as supplied.

### Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

## 15. REGULATORY INFORMATION

### Safety, health and environmental regulations/legislation specific for the substance or mixture

## 16. OTHER INFORMATION

Revision Date : 10/31/2023

### Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

### Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)

ACGIH BEI : ACGIH - Biological Exposure Indices (BEI)

ACGIH / TWA : 8-hour, time-weighted average

ACGIH / STEL : Short-term exposure limit

AllC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Or-

# SAFETY DATA SHEET

according to the Globally Harmonized System



## WSCRNCLNR-ACTIVE-500ML

Version	Revision Date:	SDS Number:	Date of last issue: 07/26/2023
6.2	10/31/2023	10630546-00014	Date of first issue: 06/04/2012

---

ganisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

LK / EN