

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Section 1: Identification

Product name : KD BOND + SEAL GREY 600ML
Product code : 0890 100 182

Manufacturer or supplier's details

Company : Wurth NewZealand Ltd
Address : 99 McLauglins Road
Wiri, Auckland 2104
Telephone : +64 9 262 3040
Emergency telephone number : 0800 764 766
E-mail address : prodsafe@wuerth.com
Telefax : +64 9 262 3030

Recommended use of the chemical and restrictions on use

Recommended use : Adhesives
Sealant
Restrictions on use : Not applicable


Section 2: Hazard identification**GHS Classification**

Flammable liquids : Category 4
Respiratory sensitisation : Category 1
Skin sensitisation : Category 1
Carcinogenicity : Category 2
Reproductive toxicity : Category 2
Specific target organ toxicity - repeated exposure : Category 2 (Auditory system, Central nervous system)

GHS label elements

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

- Hazard pictograms : 
- Signal word : Danger
- Hazard statements : H227 Combustible liquid.
H317 May cause an allergic skin reaction.
H334 May cause allergy or asthma symptoms or breathing difficulties if inhaled.
H351 Suspected of causing cancer.
H361 Suspected of damaging fertility or the unborn child.
H373 May cause damage to organs (Auditory system, Central nervous system) through prolonged or repeated exposure.
- Precautionary statements : **Prevention:**
P201 Obtain special instructions before use.
P202 Do not handle until all safety precautions have been read and understood.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P261 Avoid breathing vapours.
P272 Contaminated work clothing should not be allowed out of the workplace.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
P284 Wear respiratory protection.
- Response:**
P302 + P352 IF ON SKIN: Wash with plenty of water.
P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P308 + P313 IF exposed or concerned: Get medical advice/ attention.
P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
P342 + P311 If experiencing respiratory symptoms: Call a POISON CENTER/ doctor.
- Storage:**
P403 + P235 Store in a well-ventilated place. Keep cool.
P405 Store locked up.
- Disposal:**
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards which do not result in classification

Excessive exposure may aggravate preexisting asthma and other respiratory disorders (e.g. emphysema, bronchitis, reactive airways dysfunction syndrome).
Vapours may form explosive mixture with air.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
 Date of first issue: 19.04.2016

Section 3: Composition/information on ingredients

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Limestone	1317-65-3	>= 20 -< 30
Polyvinyl chloride	9002-86-2	>= 1 -< 10
Methylene-bis-4,1-(N-phenylene-N'-butylurea)	77703-56-1	>= 2.5 -< 10
Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter ≤ 10 µm]	13463-67-7	>= 1 -< 10
Xylene	1330-20-7	>= 1 -< 2.5
Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%)	64742-82-1	>= 1 -< 2.5
4,4'-Diphenylmethane diisocyanate	101-68-8	>= 0.1 -< 1

Section 4: First-aid measures

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
 When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.
 If not breathing, give artificial respiration.
 If breathing is difficult, give oxygen.
 Get medical attention.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water.
 Remove contaminated clothing and shoes.
 Get medical attention.
 Wash clothing before reuse.
 Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
 Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
 Get medical attention.
 Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Respiratory symptoms, including pulmonary edema, may be delayed.
 Excessive exposure may aggravate preexisting asthma and other respiratory disorders (e.g. emphysema, bronchitis, reactive airways dysfunction syndrome).
 May cause an allergic skin reaction.
 May cause allergy or asthma symptoms or breathing difficulties if inhaled.
 Suspected of causing cancer.
 Suspected of damaging fertility or the unborn child.
 May cause damage to organs through prolonged or repeated exposure.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Notes to physician : when the potential for exposure exists (see section 8).
: Treat symptomatically and supportively.

Section 5: Fire-fighting measures

Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
Water spray in large fire situations

Unsuitable extinguishing media : High volume water jet

Specific hazards during fire-fighting : Do not use a solid water stream as it may scatter and spread fire.
Flash back possible over considerable distance.
Vapours may form explosive mixtures with air.
Exposure to combustion products may be a hazard to health.
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.

Hazardous combustion products : Carbon oxides
Metal oxides
Nitrogen oxides (NO_x)
Chlorine compounds

Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

Section 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
After approximately one hour, transfer to waste container and do not seal, due to evolution of carbon dioxide.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

Section 7: Handling and storage

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : If sufficient ventilation is unavailable, use with local exhaust ventilation.

Advice on safe handling : Do not get on skin or clothing.
Do not breathe vapours.
Do not swallow.
Avoid contact with eyes.
Wash skin thoroughly after handling.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Keep container tightly closed.
Keep away from water.
Protect from moisture.
Already sensitised individuals, and those susceptible to asthma, allergies, chronic or recurrent respiratory disease, should consult their physician regarding working with respiratory irritants or sensitisers.
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
Take precautionary measures against static discharges.
Do not eat, drink or smoke when using this product.
Take care to prevent spills, waste and minimize release to the environment.

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
When using do not eat, drink or smoke.
Contaminated work clothing should not be allowed out of the workplace.
Wash contaminated clothing before re-use.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
 Date of first issue: 19.04.2016

Conditions for safe storage : Keep in properly labelled containers.
 Store locked up.
 Protect from moisture.
 Keep in a cool, well-ventilated place.
 Store in accordance with the particular national regulations.
 Keep away from heat and sources of ignition.

Materials to avoid : Do not store with the following product types:
 Strong oxidizing agents

Storage period : 12 Months

Section 8: Exposure controls/personal protection
Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Limestone	1317-65-3	WES-TWA	10 mg/m ³ (Calcium carbonate)	NZ OEL
Polyvinyl chloride	9002-86-2	TWA (Respirable particulate matter)	1 mg/m ³	ACGIH
Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter ≤ 10 µm]	13463-67-7	WES-TWA	10 mg/m ³	NZ OEL
		TWA (Respirable particulate matter)	2.5 mg/m ³ (Titanium dioxide)	ACGIH
Xylene	1330-20-7	WES-TWA	50 ppm 217 mg/m ³	NZ OEL
	Further information: Ototoxin, Exposure can also be estimated by biological monitoring			
		TWA	20 ppm	ACGIH
Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%)	64742-82-1	WES-TWA	300 ppm 890 mg/m ³	NZ OEL
		WES-STEL	500 ppm 1,480 mg/m ³	NZ OEL
4,4'-Diphenylmethane diisocyanate	101-68-8	WES-TWA (Inhalable Fraction and Vapour)	0.02 mg/m ³ (NCO)	NZ OEL
	Further information: Skin sensitiser, Respiratory sensitiser			
		WES-STEL (Inhalable Fraction and Vapour)	0.07 mg/m ³ (NCO)	NZ OEL

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
 Date of first issue: 19.04.2016

Further information: Skin sensitiser, Respiratory sensitiser			
	TWA	0.005 ppm	ACGIH

Biological occupational exposure limits

Components	CAS-No.	Control parameters	Biological specimen	Sam-pling time	Permissible concentra-tion	Basis
Xylene	1330-20-7	Methylhip-puric acid	Urine	End of shift	1.5 g/l	NZ BEI
		Methylhip-puric acids	Urine	End of shift (As soon as possible after exposure ceases)	0.3 g/g cre-atinine	ACGIH BEI
4,4'-Diphenylmethane diisocyanate	101-68-8	4,4-Diaminodi-phenyl	Urine	End of exposure or end of shift	10 µg/g creatinine	NZ BEI

Engineering measures : Processing may form hazardous compounds (see section 10).
 Ensure adequate ventilation, especially in confined areas.
 Minimize workplace exposure concentrations.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or expo-sure assessment demonstrates exposures outside the rec-ommended guidelines, use respiratory protection.

Filter type : Combined particulates and organic vapour type

Hand protection

Material : Fluorinated rubber

Break through time : > 30 min

Glove thickness : 0.4 mm

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous sub-stance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufactur-er. Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
 Safety glasses

Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
 Wear the following personal protective equipment:
 If assessment demonstrates that there is a risk of explosive atmospheres or flash fires, use flame retardant antistatic protective clothing.

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

Section 9: Physical and chemical properties

Appearance	:	paste
Colour	:	grey
Odour	:	characteristic
Odour Threshold	:	No data available
pH	:	substance/mixture is non-soluble (in water)
Melting point/freezing point	:	No data available
Initial boiling point and boiling range	:	No data available
Flash point	:	76 °C
Evaporation rate	:	No data available
Flammability (solid, gas)	:	Not applicable
Flammability (liquids)	:	Ignitable (see flash point)
Upper explosion limit / Upper flammability limit	:	No data available
Lower explosion limit / Lower flammability limit	:	No data available
Vapour pressure	:	No data available
Relative vapour density	:	No data available
Density	:	ca. 1.26 g/cm ³ (20 °C)
Solubility(ies)	:	
Water solubility	:	insoluble
Partition coefficient: n-octanol/water	:	Not applicable
Auto-ignition temperature	:	No data available
Decomposition temperature	:	No data available
Viscosity	:	
Viscosity, kinematic	:	> 20.5 mm ² /s (40 °C)

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle characteristics
Particle size : Not applicable

Section 10: Stability and reactivity

Reactivity : Not classified as a reactivity hazard.

Chemical stability : Stable if used as directed. Follow precautionary advice and avoid incompatible materials and conditions.
Polymerises at high temperatures with evolution of carbon dioxide.

Possibility of hazardous reactions : Combustible liquid.
Vapours may form explosive mixture with air.
Isocyanates react with many materials and the rate of reaction increases with temperature as well as increased contact; these reactions can become violent. Contact is increased by stirring or if the other material mixes with the isocyanate.
Exothermic reaction with acids, amines and alcohols
Reacts with water to form carbon dioxide and heat
Isocyanates are not soluble in water and sink to the bottom, but react slowly at the interface. The reaction forms carbon dioxide gas and a layer of solid polyurea.
Hazardous decomposition products will be formed upon contact with water or humid air.

Conditions to avoid : Exposure to moisture
Heat, flames and sparks.

Incompatible materials : Oxidizing agents
Acids
Bases
Water
Alcohols
Amines
Ammonia
Aluminium
Zinc
Brass
Tin
Copper
Galvanised metals
Humid air

Hazardous decomposition products : No hazardous decomposition products are known.

Section 11: Toxicological information

Exposure routes : Inhalation
Skin contact

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

- Acute oral toxicity : Acute toxicity estimate: > 2,000 mg/kg
Method: Calculation method
- Acute inhalation toxicity : Acute toxicity estimate: > 5 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Method: Calculation method
- Acute dermal toxicity : Acute toxicity estimate: > 2,000 mg/kg
Method: Calculation method

Components:**Limestone:**

- Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 420
Assessment: The substance or mixture has no acute oral toxicity
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): > 3 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Method: OECD Test Guideline 403
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 402
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

- Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 401
Assessment: The substance or mixture has no acute oral toxicity
- Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 402
Assessment: The substance or mixture has no acute dermal toxicity

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 6.82 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Assessment: The substance or mixture has no acute inhalation toxicity

Xylene:

Acute oral toxicity : Acute toxicity estimate: 500 mg/kg
Method: Expert judgement
Remarks: Based on national or regional regulation.

Acute inhalation toxicity : LC50 (Rat): 27.571 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Acute dermal toxicity : Acute toxicity estimate: 1,100 mg/kg
Method: Expert judgement
Remarks: Based on national or regional regulation.

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Acute oral toxicity : LD50 (Rat): > 15,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 13.1 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rat): > 3,400 mg/kg

4,4'-Diphenylmethane diisocyanate:

Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Assessment: The substance or mixture has no acute oral toxicity
Remarks: Based on data from similar materials

Acute inhalation toxicity : Acute toxicity estimate: 0.0501 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist
Method: Expert judgement
Remarks: Based on national or regional regulation.

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg
Remarks: Based on data from similar materials

Skin corrosion/irritation

Not classified based on available information.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Components:**Limestone:**

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation
Remarks : Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Species : Rabbit
Result : No skin irritation

Xylene:

Species : Rabbit
Result : Skin irritation

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Species : Rabbit
Method : OECD Test Guideline 404
Result : No skin irritation

Assessment : Repeated exposure may cause skin dryness or cracking.

4,4'-Diphenylmethane diisocyanate:

Species : Rabbit
Method : OECD Test Guideline 404
Result : Skin irritation
Remarks : Based on data from similar materials

Serious eye damage/eye irritation

Not classified based on available information.

Components:**Limestone:**

Species : Rabbit
Result : No eye irritation
Method : OECD Test Guideline 405
Remarks : Based on data from similar materials

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Species	:	Rabbit
Result	:	No eye irritation
Method	:	OECD Test Guideline 405

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Species	:	Rabbit
Result	:	No eye irritation

Xylene:

Species	:	Rabbit
Result	:	Irritation to eyes, reversing within 21 days

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Species	:	Rabbit
Result	:	No eye irritation
Method	:	OECD Test Guideline 405

4,4'-Diphenylmethane diisocyanate:

Result	:	Irritation to eyes, reversing within 7 days
Remarks	:	Based on national or regional regulation.

Respiratory or skin sensitisation**Skin sensitisation**

May cause an allergic skin reaction.

Respiratory sensitisation

May cause allergy or asthma symptoms or breathing difficulties if inhaled.

Components:**Limestone:**

Test Type	:	Local lymph node assay (LLNA)
Exposure routes	:	Skin contact
Species	:	Mouse
Method	:	OECD Test Guideline 429
Result	:	negative
Remarks	:	Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Test Type	:	Maximisation Test
Exposure routes	:	Skin contact
Species	:	Guinea pig
Method	:	OECD Test Guideline 406
Result	:	negative

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Test Type : Local lymph node assay (LLNA)
Exposure routes : Skin contact
Species : Mouse
Result : negative

Xylene:

Test Type : Local lymph node assay (LLNA)
Exposure routes : Skin contact
Species : Mouse
Result : negative

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative

4,4'-Diphenylmethane diisocyanate:

Test Type : Buehler Test
Exposure routes : Skin contact
Species : Guinea pig
Result : positive

Assessment : Probability or evidence of skin sensitisation in humans

Exposure routes : Inhalation
Species : Rat
Result : positive
Remarks : Based on data from similar materials

Assessment : Probability of respiratory sensitisation in humans based on animal testing

Chronic toxicity**Germ cell mutagenicity**

Not classified based on available information.

Components:**Limestone:**

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Test Type: Chromosome aberration test in vitro

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Method: OECD Test Guideline 473
Result: negative
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test
Method: OECD Test Guideline 476
Result: negative
Remarks: Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative

Test Type: In vitro mammalian cell gene mutation test
Method: OECD Test Guideline 476
Result: negative

Test Type: Chromosome aberration test in vitro
Method: OECD Test Guideline 473
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: Skin contact
Method: OECD Test Guideline 474
Result: negative

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: In vivo micronucleus test
Species: Mouse
Result: negative

Xylene:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Test Type: Chromosome aberration test in vitro
Result: negative

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Test Type: In vitro sister chromatid exchange assay in mammalian cells

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Result: negative

Genotoxicity in vivo : Test Type: Rodent dominant lethal test (germ cell) (in vivo)
Species: Mouse
Application Route: Skin contact
Result: negative

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro
Result: negative

Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative
Remarks: Based on data from similar materials

4,4'-Diphenylmethane diisocyanate:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (dust/mist/fume)
Method: OECD Test Guideline 474
Result: negative

Carcinogenicity

Suspected of causing cancer.

Components:**Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:**

Species : Rat
Application Route : inhalation (dust/mist/fume)
Exposure time : 2 Years
Method : OECD Test Guideline 453
Result : positive
Remarks : The mechanism or mode of action may not be relevant in humans.

Carcinogenicity - Assessment : Limited evidence of carcinogenicity in inhalation studies with animals.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Xylene:

Species : Rat
Application Route : Ingestion
Exposure time : 103 weeks
Result : negative

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 105 weeks
Result : negative
Remarks : Based on data from similar materials

4,4'-Diphenylmethane diisocyanate:

Species : Rat
Application Route : inhalation (dust/mist/fume)
Exposure time : 2 Years
Result : positive
Remarks : Based on data from similar materials

Carcinogenicity - Assessment : Limited evidence of carcinogenicity in animal studies

Reproductive toxicity

Suspected of damaging fertility or the unborn child.

Components:**Limestone:**

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 422
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 422
Result: negative
Remarks: Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Effects on fertility : Test Type: One-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Method: OECD Test Guideline 415
Result: negative

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rabbit
Application Route: Ingestion
Method: OECD Test Guideline 414
Result: negative

Xylene:

Effects on fertility : Test Type: One-generation reproduction toxicity study
Species: Rat
Application Route: inhalation (vapour)
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (vapour)
Result: negative

Reproductive toxicity - Assessment : Some evidence of adverse effects on sexual function and fertility, and/or on development, based on animal experiments.
Remarks: Based on national or regional regulation.

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Effects on fertility : Test Type: One-generation reproduction toxicity study
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (vapour)
Result: negative

4,4'-Diphenylmethane diisocyanate:

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (dust/mist/fume)
Result: negative
Remarks: Based on data from similar materials

STOT - single exposure

Not classified based on available information.

Components:**Xylene:**

Assessment : May cause respiratory irritation.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Assessment : May cause drowsiness or dizziness.

4,4'-Diphenylmethane diisocyanate:

Assessment : May cause respiratory irritation.

STOT - repeated exposure

May cause damage to organs (Auditory system, Central nervous system) through prolonged or repeated exposure.

Components:**Xylene:**

Exposure routes : inhalation (vapour)
Target Organs : Auditory system
Assessment : Shown to produce significant health effects in animals at concentrations of >0.2 to 1 mg/l/6h/d.

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Exposure routes : Inhalation
Target Organs : Central nervous system
Assessment : Causes damage to organs through prolonged or repeated exposure.

4,4'-Diphenylmethane diisocyanate:

Assessment : Causes damage to organs through prolonged or repeated exposure.
Remarks : Based on national or regional regulation.

Repeated dose toxicity**Components:****Limestone:**

Species : Rat
NOAEL : > 300 mg/kg
Application Route : Ingestion
Exposure time : 28 Days
Method : OECD Test Guideline 422
Remarks : Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

Species : Rat
NOAEL : >= 1,000 mg/kg
Application Route : Ingestion
Exposure time : 28 Days
Method : OECD Test Guideline 407

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

Species : Rat
NOAEL : 24,000 mg/kg
Application Route : Ingestion
Exposure time : 28 Days

Species : Rat
NOAEL : 10 mg/m³
Application Route : inhalation (dust/mist/fume)
Exposure time : 2 yr

Xylene:

Species : Rat
LOAEL : > 0.2 - 1 mg/l
Application Route : inhalation (vapour)
Exposure time : 13 Weeks
Remarks : Based on data from similar materials

Species : Rat
LOAEL : 150 mg/kg
Application Route : Ingestion
Exposure time : 90 Days

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Species : Rat
NOAEL : 1,056 mg/kg
Application Route : Ingestion
Exposure time : 90 Days

Species : Rat
NOAEL : 3.950 mg/l
LOAEL : 7.400 mg/l
Application Route : Inhalation
Exposure time : 90 Days

4,4'-Diphenylmethane diisocyanate:

Species : Rat
NOAEL : 0,2 mg/m³
LOAEL : 1 mg/m³
Application Route : inhalation (dust/mist/fume)
Exposure time : 2 yr
Remarks : Based on data from similar materials

Aspiration toxicity

Not classified based on available information.

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Components:**Xylene:**

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Experience with human exposure**Components:****Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):**

Inhalation : Symptoms: central nervous system effects

Section 12: Ecological information**Ecotoxicity****Components:****Limestone:**

- Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 100 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 203
Remarks: Based on data from similar materials
- Toxicity to daphnia and other aquatic invertebrates : LL50 (Daphnia magna (Water flea)): > 100 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202
Remarks: Based on data from similar materials
- Toxicity to algae/aquatic plants : EL50 (Desmodesmus subspicatus (green algae)): > 14 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: No toxicity at the limit of solubility
Based on data from similar materials
- EL10 (Desmodesmus subspicatus (green algae)): > 14 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: No toxicity at the limit of solubility
Based on data from similar materials
- Toxicity to microorganisms : EC50: > 100 mg/l

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

Exposure time: 3 h
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Methylene-bis-4,1-(N-phenylene-N'-butylurea):

- Toxicity to fish : LC50 (Danio rerio (zebra fish)): > 250 mg/l
Exposure time: 96 h
Method: OECD Test Guideline 203
- Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 100 mg/l
Exposure time: 48 h
Method: OECD Test Guideline 202
- Toxicity to algae/aquatic plants : EL50 (Desmodesmus subspicatus (green algae)): > 100 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
- NOELR (Desmodesmus subspicatus (green algae)): 100 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
- Toxicity to microorganisms : NOEC (activated sludge): 100 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209

Titanium dioxide; [in powder form containing 1 % or more of particles with aerodynamic diameter $\leq 10 \mu\text{m}$]:

- Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): > 100 mg/l
Exposure time: 96 h
Method: OECD Test Guideline 203
- Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 100 mg/l
Exposure time: 48 h
- Toxicity to algae/aquatic plants : EC50 (Skeletonema costatum (marine diatom)): > 10,000 mg/l
Exposure time: 72 h
- Toxicity to microorganisms : EC50: > 1,000 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209

Xylene:

- Toxicity to fish : LC50 (Oncorhynchus mykiss (rainbow trout)): 13.5 mg/l
Exposure time: 96 h
- Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 1 - 10 mg/l
Exposure time: 24 h
Method: OECD Test Guideline 202

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EC50 (Skeletonema costatum (marine diatom)): 10 mg/l
Exposure time: 72 h

Toxicity to fish (Chronic toxicity) : NOEC (Danio rerio (zebra fish)): > 0.1 - < 1 mg/l
Exposure time: 35 d
Method: OECD Test Guideline 210
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : EL10 (Daphnia magna (Water flea)): > 1 - 10 mg/l
Exposure time: 21 d
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

Toxicity to microorganisms : NOEC: > 100 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 10 - 30 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 203

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 10 - 22 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): 4.1 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201

NOELR (Pseudokirchneriella subcapitata (green algae)): 0.76 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC (Daphnia magna (Water flea)): 0.097 mg/l
Exposure time: 21 d
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

4,4'-Diphenylmethane diisocyanate:

Toxicity to fish : LC50 (Oryzias latipes (Orange-red killifish)): > 3,000 mg/l

KD BOND + SEAL GREY 600ML

Version 9.1 Revision Date: 24.09.2024 SDS Number: 10766963-00014 Date of last issue: 09.06.2024
Date of first issue: 19.04.2016

- Exposure time: 96 h
Remarks: Based on data from similar materials
- Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 129.7 mg/l
Exposure time: 24 h
Method: OECD Test Guideline 202
- Toxicity to algae/aquatic plants : EC50 (Desmodesmus subspicatus (green algae)): > 1,640 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials
- NOEC (Desmodesmus subspicatus (green algae)): 1,640 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials
- Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOEC (Daphnia magna (Water flea)): 10 mg/l
Exposure time: 21 d
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials
- Toxicity to microorganisms : EC50: > 100 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Persistence and degradability**Components:****Methylene-bis-4,1-(N-phenylene-N'-butylurea):**

- Biodegradability : Result: Not readily biodegradable.
Biodegradation: 11 %
Exposure time: 28 d
Method: OECD Test Guideline 301B

Xylene:

- Biodegradability : Result: Readily biodegradable.
Biodegradation: > 70 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

- Biodegradability : Result: Readily biodegradable.
Biodegradation: 75.9 %
Exposure time: 31 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

4,4'-Diphenylmethane diisocyanate:

Biodegradability : Result: Not readily biodegradable.
Biodegradation: 0 %
Exposure time: 28 d
Method: OECD Test Guideline 302
Remarks: Based on data from similar materials

Bioaccumulative potential**Components:****Methylene-bis-4,1-(N-phenylene-N'-butylurea):**

Partition coefficient: n- : log Pow: 5.5
octanol/water Method: OECD Test Guideline 107

Xylene:

Partition coefficient: n- : log Pow: 3.16
octanol/water Remarks: Calculation

Hydrocarbons, C9-C12, n-alkanes, isoalkanes, cyclics, aromatics (2-25%):

Partition coefficient: n- : Pow: > 4
octanol/water

4,4'-Diphenylmethane diisocyanate:

Bioaccumulation : Species: Cyprinus carpio (Carp)
Bioconcentration factor (BCF): 200

Partition coefficient: n- : log Pow: 4.51
octanol/water

Mobility in soil

No data available

Other adverse effects

No data available

Section 13: Disposal considerations**Disposal methods**

Waste from residues : Do not dispose of waste into sewer.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Section 14: Transport information**International Regulations****UNRTDG**

UN number	:	Not applicable
Proper shipping name	:	Not applicable
Class	:	Not applicable
Subsidiary risk	:	Not applicable
Packing group	:	Not applicable
Labels	:	Not applicable
Environmentally hazardous	:	no

IATA-DGR

UN/ID No.	:	Not applicable
Proper shipping name	:	Not applicable
Class	:	Not applicable
Subsidiary risk	:	Not applicable
Packing group	:	Not applicable
Labels	:	Not applicable
Packing instruction (cargo aircraft)	:	Not applicable
Packing instruction (passenger aircraft)	:	Not applicable

IMDG-Code

UN number	:	Not applicable
Proper shipping name	:	Not applicable
Class	:	Not applicable
Subsidiary risk	:	Not applicable
Packing group	:	Not applicable
Labels	:	Not applicable
EmS Code	:	Not applicable
Marine pollutant	:	Not applicable

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

National Regulations**NZS 5433**

UN number	:	Not applicable
Proper shipping name	:	Not applicable
Class	:	Not applicable
Subsidiary risk	:	Not applicable
Packing group	:	Not applicable
Labels	:	Not applicable
Hazchem Code	:	Not applicable

Special precautions for user

Not applicable

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

Section 15: Regulatory information**Safety, health and environmental regulations/legislation specific for the substance or mixture****HSNO Approval Number**

HSR002680 Surface Coatings and Colourants Combustible Carcinogenic Group Standard

Tolerable Exposure Limits (TEL)

Chemical name	Environmental compartment	Reference concentration
xylene	Air	0.87 mg/m ³
xylene	Water	0.6 mg/l

Environmental Exposure Limits (EEL)

Not applicable

HSW Controls

Certified handler certificate not required.

Tracking hazardous substance not required.

Refer to the Health and Safety at Work (Hazardous Substances) Regulations 2017, for further information.

The components of this product are reported in the following inventories:

NZIoC : All ingredients listed or exempt.

Section 16: Other information

Revision Date : 24.09.2024

Further informationSources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Date format : dd.mm.yyyy

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)
 ACGIH BEI : ACGIH - Biological Exposure Indices (BEI)
 NZ BEI : New Zealand. Biological Exposure Indices
 NZ OEL : New Zealand. Workplace Exposure Standards for Atmospheric Contaminants

ACGIH / TWA : 8-hour, time-weighted average
 NZ OEL / WES-TWA : Workplace Exposure Standard - Time Weighted average
 NZ OEL / WES-STEL : Workplace Exposure Standard - Short-Term Exposure Limit

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); EC_x - Concentration associated with x% response; EL_x - Loading rate associated with x% response; EmS - Emergency Schedule;

KD BOND + SEAL GREY 600ML

Version	Revision Date:	SDS Number:	Date of last issue: 09.06.2024
9.1	24.09.2024	10766963-00014	Date of first issue: 19.04.2016

ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

NZ / EN