

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

1. PRODUCT AND COMPANY IDENTIFICATION

Product name : 702
Product code : 089025 702 12

Manufacturer or supplier's details

Company : Wurth Lanka (PVT) LTD
Address : 375/B, High Level Road
Makumbura, Pannipitya, Sri Lanka
Telephone : 0094-112894930
Emergency telephone number : 0094-777328880
E-mail address : prodsafe@wuerth.com
Telefax : 0094-112894955

Recommended use of the chemical and restrictions on use

Recommended use :
Cleaning agent
Detergent
Restrictions on use : Not applicable

2. HAZARDS IDENTIFICATION

GHS Classification

Aerosols : Category 1
Serious eye damage/eye irritation : Category 2A
Specific target organ toxicity - single exposure : Category 3

GHS label elements

Hazard pictograms :  
Signal word : Danger
Hazard statements : H222 Extremely flammable aerosol.

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

H229 Pressurised container: May burst if heated.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Precautionary statements :

Prevention:
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Do not pierce or burn, even after use.
P261 Avoid breathing spray.
P264+P265 Wash hands thoroughly after handling. Do not touch eyes.
P271 Use only outdoors or with adequate ventilation.
P280 Wear eye protection/ face protection.

Response:
P304 + P340 + P319 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Get medical help if you feel unwell.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337 + P317 If eye irritation persists: Get medical help.

Storage:
P405 Store locked up.
P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.

Disposal:
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards which do not result in classification

None known.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Propan-2-ol	67-63-0	>= 10 - < 20
Butane	106-97-8	>= 1 - < 5
Isobutane	75-28-5	>= 1 - < 5
Propane	74-98-6	>= 1 - < 5
1-Methoxy-2-propanol	107-98-2	>= 1 - < 5
(R)-p-mentha-1,8-diene	5989-27-5	>= 0.1 - < 0.25

4. FIRST AID MEASURES

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

- General advice : In the case of accident or if you feel unwell, seek medical advice immediately.
When symptoms persist or in all cases of doubt seek medical advice.
- If inhaled : If inhaled, remove to fresh air.
Get medical attention if symptoms occur.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water.
Get medical attention if symptoms occur.
- In case of eye contact : In case of contact, immediately flush eyes with plenty of water for at least 15 minutes.
If easy to do, remove contact lens, if worn.
Get medical attention.
- If swallowed : If swallowed, DO NOT induce vomiting.
Get medical attention if symptoms occur.
Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Causes serious eye irritation.
May cause drowsiness or dizziness.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.
-

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Flash back possible over considerable distance.
Vapours may form explosive mixtures with air.
Exposure to combustion products may be a hazard to health.
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
- Hazardous combustion products : Carbon oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do
-

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

so.
Evacuate area.

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Remove all sources of ignition.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

7. HANDLING AND STORAGE

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use with local exhaust ventilation.

Advice on safe handling : Avoid breathing spray.
Do not swallow.
Do not get in eyes.
Avoid prolonged or repeated contact with skin.
Wash skin thoroughly after handling.
Handle in accordance with good industrial hygiene and safety

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

practice, based on the results of the workplace exposure assessment
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
Take precautionary measures against static discharges.
Take care to prevent spills, waste and minimize release to the environment.
Do not spray on an open flame or other ignition source.

Conditions for safe storage : Store locked up.
Keep in a cool, well-ventilated place.
Store in accordance with the particular national regulations.
Do not pierce or burn, even after use.
Keep cool. Protect from sunlight.

Materials to avoid : Do not store with the following product types:
Self-reactive substances and mixtures
Organic peroxides
Oxidizing agents
Flammable liquids
Pyrophoric liquids
Pyrophoric solids
Self-heating substances and mixtures
Explosives

Recommended storage temperature : > 5 - < 40 °C

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Propan-2-ol	67-63-0	TWA	200 ppm	ACGIH
		STEL	400 ppm	ACGIH
Butane	106-97-8	STEL	1,000 ppm	ACGIH
Isobutane	75-28-5	STEL	1,000 ppm	ACGIH
1-Methoxy-2-propanol	107-98-2	TWA	50 ppm	ACGIH
		STEL	100 ppm	ACGIH
(R)-p-mentha-1,8-diene	5989-27-5	TWA	20 ppm	ACGIH

Biological occupational exposure limits

Components	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
Propan-2-ol	67-63-0	Acetone	Urine	End of shift at end of work-week	40 mg/l	ACGIH BEI

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Engineering measures : Minimize workplace exposure concentrations.
Use with local exhaust ventilation.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.

Filter type : Self-contained breathing apparatus

Hand protection

Remarks : not required Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
Safety goggles

Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Wear the following personal protective equipment:
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a dissolved gas

Propellant : Propane, Butane, Isobutane

Colour : colourless

Odour : fruity

Odour Threshold : No data available

pH : 9.5
Concentration: 100 %
pH value is valid for liquid portion in the aerosol can

Melting point/freezing point : No data available

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Initial boiling point and boiling range : Not applicable

Flash point : 34 °C
Flash point is only valid for liquid portion in the aerosol can.

Evaporation rate : Not applicable

Flammability (solid, gas) : Extremely flammable aerosol.

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Vapour pressure : Not applicable

Relative vapour density : Not applicable

Density : 0.98 g/cm³ (20 °C)

Solubility(ies)
Water solubility : completely soluble

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity
Viscosity, kinematic : Not applicable

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

Particle characteristics
Particle size : Not applicable

10. STABILITY AND REACTIVITY

Reactivity : Not classified as a reactivity hazard.

Chemical stability : Stable under normal conditions.

Possibility of hazardous reac- : Extremely flammable aerosol.

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

tions Vapours may form explosive mixture with air.
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
Can react with strong oxidizing agents.

Conditions to avoid : Heat, flames and sparks.

Incompatible materials : Oxidizing agents
Acids

Hazardous decomposition products : No hazardous decomposition products are known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute oral toxicity : Acute toxicity estimate: > 5,000 mg/kg
Method: Calculation method

Acute inhalation toxicity : Acute toxicity estimate: > 40 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Method: Calculation method

Components:

Propan-2-ol:

Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 25 mg/l
Exposure time: 6 h
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg

Butane:

Acute inhalation toxicity : LC50 (Rat): 658 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Isobutane:

Acute inhalation toxicity : LC50 (Mouse): 260200 ppm
Exposure time: 4 h
Test atmosphere: gas

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Propane:

Acute inhalation toxicity : LC50 (Rat): > 800000 ppm
Exposure time: 15 min
Test atmosphere: gas

1-Methoxy-2-propanol:

Acute oral toxicity : LD50 (Rat): 4,016 mg/kg

Acute inhalation toxicity : LC50 (Mouse): < 22.2 mg/l
Exposure time: 6 h
Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rat): > 2,000 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity

(R)-p-mentha-1,8-diene:

Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 423
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg
Remarks: Based on data from similar materials

Skin corrosion/irritation

Not classified based on available information.

Components:

Propan-2-ol:

Species : Rabbit
Result : No skin irritation

1-Methoxy-2-propanol:

Species : Rabbit
Result : No skin irritation

(R)-p-mentha-1,8-diene:

Species : Rabbit
Method : OECD Test Guideline 404
Result : Skin irritation

Serious eye damage/eye irritation

Causes serious eye irritation.

Components:

Propan-2-ol:

Species : Rabbit

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Result : Irritation to eyes, reversing within 21 days

1-Methoxy-2-propanol:

Species : Rabbit
Result : No eye irritation

(R)-p-mentha-1,8-diene:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:

Propan-2-ol:

Test Type : Buehler Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative

1-Methoxy-2-propanol:

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Result : negative

(R)-p-mentha-1,8-diene:

Test Type : Local lymph node assay (LLNA)
Exposure routes : Skin contact
Species : Mouse
Method : OECD Test Guideline 429
Result : positive

Assessment : Probability or evidence of low to moderate skin sensitisation rate in humans

Germ cell mutagenicity

Not classified based on available information.

Components:

Propan-2-ol:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Result: negative

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Intraperitoneal injection
Result: negative

Butane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 474
Result: negative
Remarks: Based on data from similar materials

Isobutane:

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro
Method: OECD Test Guideline 473
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 474
Result: negative
Remarks: Based on data from similar materials

Propane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 474
Result: negative

1-Methoxy-2-propanol:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Test Type: Chromosome aberration test in vitro
Result: negative

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Test Type: In vitro sister chromatid exchange assay in mammalian cells
Result: equivocal

Test Type: DNA damage and repair, unscheduled DNA synthesis in mammalian cells (in vitro)
Method: OECD Test Guideline 482
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Intraperitoneal injection
Result: negative

(R)-p-mentha-1,8-diene:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Test Type: Chromosome aberration test in vitro
Result: negative

Genotoxicity in vivo : Test Type: In vivo mammalian alkaline comet assay
Species: Rat
Application Route: Ingestion
Result: negative

Carcinogenicity

Not classified based on available information.

Components:

Propan-2-ol:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 104 weeks
Method : OECD Test Guideline 451
Result : negative

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

1-Methoxy-2-propanol:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 2 Years
Method : OECD Test Guideline 453
Result : negative

(R)-p-mentha-1,8-diene:

Species : Mouse
Application Route : Ingestion
Exposure time : 103 weeks
Result : negative

Reproductive toxicity

Not classified based on available information.

Components:

Propan-2-ol:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative

Butane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Isobutane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: Inhalation
Method: OECD Test Guideline 422
Result: negative

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Propane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

1-Methoxy-2-propanol:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: inhalation (vapour)
Method: OECD Test Guideline 416
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (vapour)
Result: negative

(R)-p-mentha-1,8-diene:

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative

STOT - single exposure

May cause drowsiness or dizziness.

Components:

Propan-2-ol:

Assessment : May cause drowsiness or dizziness.

Butane:

Assessment : May cause drowsiness or dizziness.

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Isobutane:

Assessment : May cause drowsiness or dizziness.

Propane:

Assessment : May cause drowsiness or dizziness.

1-Methoxy-2-propanol:

Assessment : May cause drowsiness or dizziness.

STOT - repeated exposure

Not classified based on available information.

Components:

(R)-p-mentha-1,8-diene:

Assessment : No significant health effects observed in animals at concentrations of 100 mg/kg bw or less.

Repeated dose toxicity

Components:

Propan-2-ol:

Species : Rat
NOAEL : 12.5 mg/l
Application Route : inhalation (vapour)
Exposure time : 104 Weeks

Butane:

Species : Rat
NOAEL : 9000 ppm
Application Route : inhalation (gas)
Exposure time : 6 Weeks
Method : OECD Test Guideline 422

Isobutane:

Species : Rat
NOAEL : 9000 ppm
Application Route : inhalation (gas)
Exposure time : 6 Weeks
Method : OECD Test Guideline 422

Propane:

Species : Rat
NOAEL : 7.214 mg/l
Application Route : inhalation (gas)
Exposure time : 6 Weeks
Method : OECD Test Guideline 422

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

1-Methoxy-2-propanol:

Species : Rat
NOAEL : 919 mg/kg
Application Route : Ingestion
Exposure time : 35 Days

Species : Rat
NOAEL : 1.1 mg/l
Application Route : inhalation (vapour)
Exposure time : 2 yr
Method : OECD Test Guideline 453

Species : Rabbit
NOAEL : 1,838 mg/kg
Application Route : Skin contact
Exposure time : 90 Days

(R)-p-mentha-1,8-diene:

Species : Rat, male
NOAEL : 5 mg/kg
LOAEL : 30 mg/kg
Application Route : Ingestion
Exposure time : 13 Weeks

Aspiration toxicity

Not classified based on available information.

Components:

(R)-p-mentha-1,8-diene:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

12. ECOLOGICAL INFORMATION

Ecotoxicity

Components:

Propan-2-ol:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 10,000 mg/l
Exposure time: 24 h

Toxicity to microorganisms : EC50 (Pseudomonas putida): > 1,050 mg/l
Exposure time: 16 h

1-Methoxy-2-propanol:

Toxicity to fish : LC50 (Leuciscus idus (Golden orfe)): 6,812 mg/l

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Exposure time: 96 h
Method: DIN 38412

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 23,300 mg/l
Exposure time: 48 h

Toxicity to algae/aquatic plants : ErC50 (Skeletonema costatum (marine diatom)): 6,745 mg/l
Exposure time: 72 h
Method: ISO 10253

Toxicity to microorganisms : IC50: > 1,000 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209

(R)-p-mentha-1,8-diene:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 0.720 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 307 µg/l
Exposure time: 48 h
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : ErC50 (Pseudokirchneriella subcapitata (green algae)): 0.25 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

EC10 (Pseudokirchneriella subcapitata (green algae)): 0.14 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

M-Factor (Acute aquatic toxicity) : 1

Toxicity to microorganisms : EC50: > 100 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Toxicity to fish (Chronic toxicity) : EC10: 0.37 mg/l
Exposure time: 8 d
Species: Pimephales promelas (fathead minnow)

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : EC10: 0.153 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211

Persistence and degradability

Components:

Propan-2-ol:

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version 7.0 Revision Date: 11/26/2024 SDS Number: 10630546-00016 Date of last issue: 06/04/2024
Date of first issue: 06/04/2012

Biodegradability : Result: rapidly degradable

BOD/COD : BOD: 1,19 (BOD5)
COD: 2,23
BOD/COD: 53 %

Butane:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 100 %
Exposure time: 385.5 h
Remarks: Based on data from similar materials

Isobutane:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 100 %
Exposure time: 385.5 h
Remarks: Based on data from similar materials

Propane:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 100 %
Exposure time: 385.5 h
Remarks: Based on data from similar materials

1-Methoxy-2-propanol:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 96 %
Exposure time: 28 d
Method: OECD Test Guideline 301E

(R)-p-mentha-1,8-diene:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 71.4 %
Exposure time: 28 d
Method: OECD Test Guideline 301B

Bioaccumulative potential

Components:

Propan-2-ol:

Partition coefficient: n-octanol/water : log Pow: 0.05

Butane:

Partition coefficient: n-octanol/water : log Pow: 2.31

Isobutane:

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Partition coefficient: n-octanol/water : log Pow: 2.8

1-Methoxy-2-propanol:

Partition coefficient: n-octanol/water : log Pow: < 1

(R)-p-mentha-1,8-diene:

Partition coefficient: n-octanol/water : log Pow: 4.38

Mobility in soil

No data available

Other adverse effects

No data available

13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of waste into sewer.

Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.
Please ensure aerosol cans are sprayed completely empty (including propellant)

14. TRANSPORT INFORMATION

International Regulations

UNRTDG

UN number : UN 1950
Proper shipping name : AEROSOLS
Class : 2.1
Packing group : Not assigned by regulation
Labels : 2.1
Environmentally hazardous : no

IATA-DGR

UN/ID No. : UN 1950
Proper shipping name : Aerosols, flammable
Class : 2.1
Packing group : Not assigned by regulation

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Labels : Flammable Gas
Packing instruction (cargo aircraft) : 203
Packing instruction (passenger aircraft) : 203

IMDG-Code

UN number : UN 1950
Proper shipping name : AEROSOLS

Class : 2.1
Packing group : Not assigned by regulation
Labels : 2.1
EmS Code : F-D, S-U
Marine pollutant : no

Transport in bulk according to IMO instruments

Not applicable for product as supplied.

Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

15. REGULATORY INFORMATION

Safety, health and environmental regulations/legislation specific for the substance or mixture

16. OTHER INFORMATION

Revision Date : 11/26/2024

Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

Date format : dd.mm.yyyy

Full text of other abbreviations

ACGIH : USA. ACGIH Threshold Limit Values (TLV)
ACGIH BEI : ACGIH - Biological Exposure Indices (BEI)

ACGIH / TWA : 8-hour, time-weighted average
ACGIH / STEL : Short-term exposure limit

AIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR -

SAFETY DATA SHEET

according to the Globally Harmonized System



702

Version	Revision Date:	SDS Number:	Date of last issue: 06/04/2024
7.0	11/26/2024	10630546-00016	Date of first issue: 06/04/2012

Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECl - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

LK / EN