

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

1. PRODUCT AND COMPANY IDENTIFICATION

Product name : Silicon Spray

Product code : 0893221

Manufacturer or supplier's details

Company : Wurth Lanka (PVT) LTD

Address : 375/B, High Level Road
Makumbura, Pannipitya, Sri Lanka

Telephone : 0094-112894930

Emergency telephone number : 0094-777328880

E-mail address : prodsafe@wuerth.com

Telefax : 0094-112894955

Recommended use of the chemical and restrictions on use

Recommended use :
Preservative
Lubricant

Restrictions on use : Not applicable

2. HAZARDS IDENTIFICATION

GHS Classification

Aerosols : Category 1

Skin corrosion/irritation : Category 2

Short-term (acute) aquatic hazard : Category 3

Long-term (chronic) aquatic hazard : Category 3

GHS label elements

Hazard pictograms :



Signal word : Danger

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Hazard statements : H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.
H315 Causes skin irritation.
H412 Harmful to aquatic life with long lasting effects.

Precautionary statements : **Prevention:**
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Do not pierce or burn, even after use.
P264 Wash hands thoroughly after handling.
P273 Avoid release to the environment.
P280 Wear protective gloves.
Response:
P302 + P352 IF ON SKIN: Wash with plenty of water.
P332 + P317 If skin irritation occurs: Get medical help.
P362 + P364 Take off contaminated clothing and wash it before reuse.
Storage:
P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/ 122 °F.
Disposal:
P501 Dispose of contents/ container to an approved waste disposal plant.

Other hazards which do not result in classification

May displace oxygen and cause rapid suffocation.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Components

Chemical name	CAS-No.	Concentration (% w/w)
Butane	106-97-8	>= 30 - < 50
Propane	74-98-6	>= 20 - < 30
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	64742-49-0	>= 10 - < 20
Hydrocarbons, C6, isoalkanes, <5% n-hexane	64742-49-0	>= 5 - < 10
Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics	64742-48-9	>= 1 - < 2.5
Propan-2-ol	67-63-0	>= 1 - < 5
(R)-p-mentha-1,8-diene	5989-27-5	>= 0.1 - < 0.25

4. FIRST AID MEASURES

General advice : In the case of accident or if you feel unwell, seek medical advice immediately.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

- If inhaled : When symptoms persist or in all cases of doubt seek medical advice.
: If inhaled, remove to fresh air.
: If not breathing, give artificial respiration.
: If breathing is difficult, give oxygen.
: Get medical attention immediately.
- In case of skin contact : In case of contact, immediately flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes.
: Get medical attention.
: Wash clothing before reuse.
: Thoroughly clean shoes before reuse.
- In case of eye contact : Flush eyes with water as a precaution.
: Get medical attention if irritation develops and persists.
- If swallowed : If swallowed, DO NOT induce vomiting.
: Get medical attention if symptoms occur.
: Rinse mouth thoroughly with water.
- Most important symptoms and effects, both acute and delayed : Causes skin irritation.
: Gas reduces oxygen available for breathing.
- Protection of first-aiders : First Aid responders should pay attention to self-protection, and use the recommended personal protective equipment when the potential for exposure exists (see section 8).
- Notes to physician : Treat symptomatically and supportively.

5. FIREFIGHTING MEASURES

- Suitable extinguishing media : Water spray
: Alcohol-resistant foam
: Carbon dioxide (CO₂)
: Dry chemical
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire-fighting : Flash back possible over considerable distance.
: Vapours may form explosive mixtures with air.
: Exposure to combustion products may be a hazard to health.
: If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
- Hazardous combustion products : Carbon oxides
: Silicon oxides
- Specific extinguishing methods : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Use water spray to cool unopened containers.
Remove undamaged containers from fire area if it is safe to do so.
Evacuate area.

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
Use personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Evacuate personnel to safe areas.
Remove all sources of ignition.
Ventilate the area.
Use personal protective equipment.
Follow safe handling advice (see section 7) and personal protective equipment recommendations (see section 8).

Environmental precautions : Avoid release to the environment.
Prevent further leakage or spillage if safe to do so.
Prevent spreading over a wide area (e.g. by containment or oil barriers).
Retain and dispose of contaminated wash water.
Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up : Non-sparking tools should be used.
Soak up with inert absorbent material.
Suppress (knock down) gases/vapours/mists with a water spray jet.
For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container.
Clean up remaining materials from spill with suitable absorbent.
Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable.
Sections 13 and 15 of this SDS provide information regarding certain local or national requirements.

7. HANDLING AND STORAGE

Technical measures : See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Advice on safe handling : Do not get on skin or clothing.
Avoid inhalation of vapour or mist.
Do not swallow.
Avoid contact with eyes.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Wash skin thoroughly after handling.
Handle in accordance with good industrial hygiene and safety practice, based on the results of the workplace exposure assessment
Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
Take precautionary measures against static discharges.
Take care to prevent spills, waste and minimize release to the environment.
Do not spray on an open flame or other ignition source.

Conditions for safe storage : Keep in a cool, well-ventilated place.
Store in accordance with the particular national regulations.
Do not pierce or burn, even after use.
Keep cool. Protect from sunlight.

Materials to avoid : Do not store with the following product types:
Self-reactive substances and mixtures
Organic peroxides
Oxidizing agents
Flammable liquids
Pyrophoric liquids
Pyrophoric solids
Self-heating substances and mixtures
Explosives

Recommended storage temperature : < 40 °C

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
Butane	106-97-8	STEL	1,000 ppm	ACGIH
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	64742-49-0	TWA	400 ppm	ACGIH
		STEL	500 ppm	ACGIH
Hydrocarbons, C6, isoalkanes, <5% n-hexane	64742-49-0	TWA	200 ppm	ACGIH
Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics	64742-48-9	TWA (Inhalable particulate matter)	5 mg/m ³	ACGIH
Propan-2-ol	67-63-0	TWA	200 ppm	ACGIH
		STEL	400 ppm	ACGIH

Biological occupational exposure limits

Components	CAS-No.	Control parameters	Biological specimen	Sampling time	Permissible concentration	Basis
------------	---------	--------------------	---------------------	---------------	---------------------------	-------

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Propan-2-ol	67-63-0	Acetone	Urine	End of shift at end of work-week	40 mg/l	ACGIH BEI
-------------	---------	---------	-------	----------------------------------	---------	-----------

Engineering measures : Minimize workplace exposure concentrations.
Use with local exhaust ventilation.

Personal protective equipment

Respiratory protection : If adequate local exhaust ventilation is not available or exposure assessment demonstrates exposures outside the recommended guidelines, use respiratory protection.

Filter type : Self-contained breathing apparatus

Hand protection

Material : Nitrile rubber
Break through time : > 480 min
Glove thickness : 0.35 mm

Remarks : Choose gloves to protect hands against chemicals depending on the concentration and quantity of the hazardous substance and specific to place of work. For special applications, we recommend clarifying the resistance to chemicals of the aforementioned protective gloves with the glove manufacturer. Wash hands before breaks and at the end of workday.

Eye protection : Wear the following personal protective equipment:
Safety glasses

Skin and body protection : Select appropriate protective clothing based on chemical resistance data and an assessment of the local exposure potential.
Wear the following personal protective equipment:
Skin contact must be avoided by using impervious protective clothing (gloves, aprons, boots, etc).

Hygiene measures : If exposure to chemical is likely during typical use, provide eye flushing systems and safety showers close to the working place.
When using do not eat, drink or smoke.
Wash contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : Aerosol containing a liquefied gas

Propellant : Propane, Butane

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Colour : colourless

Odour : characteristic

Odour Threshold : No data available

pH : substance/mixture is non-soluble (in water)

Melting point/freezing point : No data available

Initial boiling point and boiling range : -42 - 165 °C

Flash point : 3.5 °C
(1,013.25 hPa)
Flash point is only valid for liquid portion in the aerosol can.

Evaporation rate : Not applicable

Flammability (solid, gas) : Extremely flammable aerosol.

Upper explosion limit / Upper flammability limit : 12.0 %(V)

Lower explosion limit / Lower flammability limit : 0.8 %(V)

Vapour pressure : 8,530 hPa (20 °C)

Relative vapour density : Not applicable

Density : 0.757 g/cm³ (20 °C)

Solubility(ies)
Water solubility : insoluble

Partition coefficient: n-octanol/water : Not applicable

Auto-ignition temperature : 287 °C

Decomposition temperature : No data available

Viscosity
Viscosity, dynamic : 1 mPa.s (20 °C)
Viscosity, kinematic : 1 mm²/s (40 °C)

Explosive properties : Not explosive

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Oxidizing properties : The substance or mixture is not classified as oxidizing.
Particle characteristics
Particle size : Not applicable

10. STABILITY AND REACTIVITY

Reactivity : Not classified as a reactivity hazard.
Chemical stability : Stable under normal conditions.
Possibility of hazardous reactions : Extremely flammable aerosol.
Vapours may form explosive mixture with air.
If the temperature rises there is danger of the vessels bursting due to the high vapor pressure.
Can react with strong oxidizing agents.
Conditions to avoid : Heat, flames and sparks.
Incompatible materials : Oxidizing agents
Hazardous decomposition products : No hazardous decomposition products are known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure : Inhalation
Skin contact
Ingestion
Eye contact

Acute toxicity

Not classified based on available information.

Product:

Acute inhalation toxicity : Acute toxicity estimate: > 40 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Method: Calculation method

Components:

Butane:

Acute inhalation toxicity : LC50 (Rat): 658 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Propane:

Acute inhalation toxicity : LC50 (Rat): > 800000 ppm
Exposure time: 15 min

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Test atmosphere: gas

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

- Acute oral toxicity : LD50 (Rat): > 5,840 mg/kg
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): > 23.3 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rat): > 2,800 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

- Acute oral toxicity : LD50 (Rat): 16,750 mg/kg
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): 259.354 mg/l
Exposure time: 4 h
Test atmosphere: vapour
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rabbit): > 3,350 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

- Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
Remarks: Based on data from similar materials
- Acute inhalation toxicity : LC50 (Rat): > 4,951 mg/m³
Exposure time: 4 h
Test atmosphere: vapour
Assessment: The substance or mixture has no acute inhalation toxicity
Remarks: Based on data from similar materials
- Acute dermal toxicity : LD50 (Rabbit): > 3,160 mg/kg
Assessment: The substance or mixture has no acute dermal toxicity
Remarks: Based on data from similar materials

Propan-2-ol:

- Acute oral toxicity : LD50 (Rat): > 5,000 mg/kg
- Acute inhalation toxicity : LC50 (Rat): > 25 mg/l
Exposure time: 6 h

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Test atmosphere: vapour

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg

(R)-p-mentha-1,8-diene:

Acute oral toxicity : LD50 (Rat): > 2,000 mg/kg
Method: OECD Test Guideline 423
Remarks: Based on data from similar materials

Acute dermal toxicity : LD50 (Rabbit): > 5,000 mg/kg
Remarks: Based on data from similar materials

Skin corrosion/irritation

Causes skin irritation.

Components:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Species : Rabbit
Result : Skin irritation
Remarks : Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Species : Rabbit
Method : OECD Test Guideline 404
Result : Skin irritation

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rabbit
Result : Mild skin irritation

Assessment : Repeated exposure may cause skin dryness or cracking.

Propan-2-ol:

Species : Rabbit
Result : No skin irritation

(R)-p-mentha-1,8-diene:

Species : Rabbit
Method : OECD Test Guideline 404
Result : Skin irritation

Serious eye damage/eye irritation

Not classified based on available information.

Components:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Species : Rabbit

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Result : No eye irritation
Remarks : Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Species : Rabbit
Result : No eye irritation
Remarks : Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation
Remarks : Based on data from similar materials

Propan-2-ol:

Species : Rabbit
Result : Irritation to eyes, reversing within 21 days

(R)-p-mentha-1,8-diene:

Species : Rabbit
Method : OECD Test Guideline 405
Result : No eye irritation

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Components:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Test Type : Maximisation Test
Exposure routes : Skin contact
Species : Guinea pig
Result : negative
Remarks : Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Test Type : Local lymph node assay (LLNA)
Exposure routes : Skin contact
Species : Mouse
Result : negative
Remarks : Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Test Type : Maximisation Test
Exposure routes : Skin contact

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Species : Guinea pig
Result : negative
Remarks : Based on data from similar materials

Propan-2-ol:

Test Type : Buehler Test
Exposure routes : Skin contact
Species : Guinea pig
Method : OECD Test Guideline 406
Result : negative

(R)-p-mentha-1,8-diene:

Test Type : Local lymph node assay (LLNA)
Exposure routes : Skin contact
Species : Mouse
Method : OECD Test Guideline 429
Result : positive

Assessment : Probability or evidence of low to moderate skin sensitisation rate in humans

Germ cell mutagenicity

Not classified based on available information.

Components:

Butane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 474
Result: negative
Remarks: Based on data from similar materials

Propane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 474
Result: negative

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Genotoxicity in vitro : Test Type: Chromosome aberration test in vitro

Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Result: negative
Remarks: Based on data from similar materials

Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test
Method: OECD Test Guideline 476
Result: negative
Remarks: Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative
Remarks: Based on data from similar materials

Test Type: Chromosome aberration test in vitro
Result: negative
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mutagenicity (in vivo mammalian bone-marrow cytogenetic test, chromosomal analysis)
Species: Rat
Application Route: inhalation (vapour)
Result: negative

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Genotoxicity in vitro : Test Type: In vitro mammalian cell gene mutation test
Result: negative
Remarks: Based on data from similar materials

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse
Application Route: Ingestion
Result: negative

Propan-2-ol:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Result: negative

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Genotoxicity in vivo : Test Type: Mammalian erythrocyte micronucleus test (in vivo cytogenetic assay)
Species: Mouse

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Application Route: Intraperitoneal injection
Result: negative

(R)-p-mentha-1,8-diene:

Genotoxicity in vitro : Test Type: Bacterial reverse mutation assay (AMES)
Method: OECD Test Guideline 471
Result: negative
Remarks: Based on data from similar materials

Test Type: In vitro mammalian cell gene mutation test
Result: negative

Test Type: Chromosome aberration test in vitro
Result: negative

Genotoxicity in vivo : Test Type: In vivo mammalian alkaline comet assay
Species: Rat
Application Route: Ingestion
Result: negative

Carcinogenicity

Not classified based on available information.

Components:

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 2 Years
Result : negative
Remarks : Based on data from similar materials

Species : Mouse
Application Route : inhalation (vapour)
Exposure time : 2 Years
Result : negative
Remarks : Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 105 weeks
Result : negative
Remarks : Based on data from similar materials

Propan-2-ol:

Species : Rat
Application Route : inhalation (vapour)
Exposure time : 104 weeks

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Method : OECD Test Guideline 451
Result : negative

(R)-p-mentha-1,8-diene:

Species : Mouse
Application Route : Ingestion
Exposure time : 103 weeks
Result : negative

Reproductive toxicity

Not classified based on available information.

Components:

Butane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Propane:

Effects on fertility : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Effects on foetal development : Test Type: Combined repeated dose toxicity study with the reproduction/developmental toxicity screening test
Species: Rat
Application Route: inhalation (gas)
Method: OECD Test Guideline 422
Result: negative

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Fertility/early embryonic development
Species: Rat

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Effects on fertility : Test Type: Reproduction/Developmental toxicity screening test
Species: Rat
Application Route: inhalation (vapour)
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: inhalation (vapour)
Result: negative
Remarks: Based on data from similar materials

Propan-2-ol:

Effects on fertility : Test Type: Two-generation reproduction toxicity study
Species: Rat
Application Route: Ingestion
Result: negative

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative

(R)-p-mentha-1,8-diene:

Effects on foetal development : Test Type: Embryo-foetal development
Species: Rat
Application Route: Ingestion
Result: negative

STOT - single exposure

Not classified based on available information.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Product:

Assessment : The substance or mixture is not classified as specific target organ toxicant, single exposure.

Components:

Butane:

Assessment : May cause drowsiness or dizziness.

Propane:

Assessment : May cause drowsiness or dizziness.

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Assessment : May cause drowsiness or dizziness.

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Assessment : May cause drowsiness or dizziness.

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Assessment : May cause drowsiness or dizziness.

Propan-2-ol:

Assessment : May cause drowsiness or dizziness.

STOT - repeated exposure

Not classified based on available information.

Components:

(R)-p-mentha-1,8-diene:

Assessment : No significant health effects observed in animals at concentrations of 100 mg/kg bw or less.

Repeated dose toxicity

Components:

Butane:

Species : Rat
NOAEL : 9000 ppm
Application Route : inhalation (gas)
Exposure time : 6 Weeks
Method : OECD Test Guideline 422

Propane:

Species : Rat
NOAEL : 7.214 mg/l
Application Route : inhalation (gas)

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Exposure time : 6 Weeks
Method : OECD Test Guideline 422

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Species : Rat
NOAEL : 12.47 mg/l
Application Route : Inhalation
Exposure time : 90 Days
Remarks : Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Species : Rat, male
NOAEL : 10.504 mg/l
Application Route : inhalation (vapour)
Exposure time : 90 Days
Remarks : Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Species : Rat
NOAEL : 10,186 mg/m3
Application Route : inhalation (vapour)
Exposure time : 13 Weeks

Propan-2-ol:

Species : Rat
NOAEL : 12.5 mg/l
Application Route : inhalation (vapour)
Exposure time : 104 Weeks

(R)-p-mentha-1,8-diene:

Species : Rat, male
NOAEL : 5 mg/kg
LOAEL : 30 mg/kg
Application Route : Ingestion
Exposure time : 13 Weeks

Aspiration toxicity

Not classified based on available information.

Components:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

(R)-p-mentha-1,8-diene:

The substance or mixture is known to cause human aspiration toxicity hazards or has to be regarded as if it causes a human aspiration toxicity hazard.

12. ECOLOGICAL INFORMATION

Ecotoxicity

Components:

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

- | | | |
|--|---|--|
| Toxicity to fish | : | LL50 (Oncorhynchus mykiss (rainbow trout)): > 13.4 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 203
Remarks: No toxicity at the limit of solubility |
| Toxicity to daphnia and other aquatic invertebrates | : | EL50 (Daphnia magna (Water flea)): 3 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202
Remarks: Based on data from similar materials |
| Toxicity to algae/aquatic plants | : | EL50 (Selenastrum capricornutum (green algae)): > 10 - 100 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials |
| | | NOELR (Selenastrum capricornutum (green algae)): 0.1 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials |
| Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) | : | NOEC: 0.17 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials |

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

- | | | |
|------------------|---|---|
| Toxicity to fish | : | LL50 (Oncorhynchus mykiss (rainbow trout)): > 10 - 100 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction |
|------------------|---|---|

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Method: OECD Test Guideline 203
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 1 - 10 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202
Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EL50 (Selenastrum capricornutum (green algae)): > 10 - 100 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

NOELR (Selenastrum capricornutum (green algae)): 0.1 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : NOELR: > 0.1 - 1 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211
Remarks: Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Toxicity to fish : LL50 (Oncorhynchus mykiss (rainbow trout)): > 10 - 30 mg/l
Exposure time: 96 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 203
Remarks: Based on data from similar materials

Toxicity to daphnia and other aquatic invertebrates : EL50 (Daphnia magna (Water flea)): > 22 - 46 mg/l
Exposure time: 48 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 202
Remarks: Based on data from similar materials

Toxicity to algae/aquatic plants : EL50 (Pseudokirchneriella subcapitata (green algae)): > 1,000 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

NOELR (Pseudokirchneriella subcapitata (green algae)): 1 mg/l
Exposure time: 72 h
Test substance: Water Accommodated Fraction
Method: OECD Test Guideline 201
Remarks: Based on data from similar materials

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Propan-2-ol:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 9,640 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): > 10,000 mg/l
Exposure time: 24 h

Toxicity to microorganisms : EC50 (Pseudomonas putida): > 1,050 mg/l
Exposure time: 16 h

(R)-p-mentha-1,8-diene:

Toxicity to fish : LC50 (Pimephales promelas (fathead minnow)): 0.720 mg/l
Exposure time: 96 h

Toxicity to daphnia and other aquatic invertebrates : EC50 (Daphnia magna (Water flea)): 307 µg/l
Exposure time: 48 h
Method: OECD Test Guideline 202

Toxicity to algae/aquatic plants : ErC50 (Pseudokirchneriella subcapitata (green algae)): 0.25 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

EC10 (Pseudokirchneriella subcapitata (green algae)): 0.14 mg/l
Exposure time: 72 h
Method: OECD Test Guideline 201

M-Factor (Acute aquatic toxicity) : 1

Toxicity to microorganisms : EC50: > 100 mg/l
Exposure time: 3 h
Method: OECD Test Guideline 209
Remarks: Based on data from similar materials

Toxicity to fish (Chronic toxicity) : EC10: 0.37 mg/l
Exposure time: 8 d
Species: Pimephales promelas (fathead minnow)

Toxicity to daphnia and other aquatic invertebrates (Chronic toxicity) : EC10: 0.153 mg/l
Exposure time: 21 d
Species: Daphnia magna (Water flea)
Method: OECD Test Guideline 211

Persistence and degradability

Components:

Butane:

Biodegradability : Result: Readily biodegradable.

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Biodegradation: 100 %
Exposure time: 385.5 h
Remarks: Based on data from similar materials

Propane:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 100 %
Exposure time: 385.5 h
Remarks: Based on data from similar materials

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Biodegradability : Result: Readily biodegradable.
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 98 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Hydrocarbons, C9-C10, n-alkanes, isoalkanes, cyclics, <2% aromatics:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 89 %
Exposure time: 28 d
Method: OECD Test Guideline 301F
Remarks: Based on data from similar materials

Propan-2-ol:

Biodegradability : Result: rapidly degradable
BOD/COD : BOD: 1,19 (BOD5)
COD: 2,23
BOD/COD: 53 %

(R)-p-mentha-1,8-diene:

Biodegradability : Result: Readily biodegradable.
Biodegradation: 71.4 %
Exposure time: 28 d
Method: OECD Test Guideline 301B

Bioaccumulative potential

Components:

Butane:

Partition coefficient: n-octanol/water : log Pow: 2.31

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics:

Partition coefficient: n-octanol/water : log Pow: > 4
Remarks: Based on data from similar materials

Hydrocarbons, C6, isoalkanes, <5% n-hexane:

Partition coefficient: n-octanol/water : log Pow: 3.6

Propan-2-ol:

Partition coefficient: n-octanol/water : log Pow: 0.05

(R)-p-mentha-1,8-diene:

Partition coefficient: n-octanol/water : log Pow: 4.38

Mobility in soil

No data available

Other adverse effects

No data available

13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of waste into sewer.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.
Empty containers retain residue and can be dangerous.
Do not pressurize, cut, weld, braze, solder, drill, grind, or expose such containers to heat, flame, sparks, or other sources of ignition. They may explode and cause injury and/or death.
If not otherwise specified: Dispose of as unused product.
Please ensure aerosol cans are sprayed completely empty (including propellant)

14. TRANSPORT INFORMATION

International Regulations

UNRTDG

UN number : UN 1950
Proper shipping name : AEROSOLS
Class : 2.1
Packing group : Not assigned by regulation

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version 9.0 Revision Date: 04/15/2025 SDS Number: 10633834-00016 Date of last issue: 11/26/2024
Date of first issue: 03/01/2012

Labels : 2.1
Environmentally hazardous : no

IATA-DGR

UN/ID No. : UN 1950
Proper shipping name : Aerosols, flammable
Class : 2.1
Packing group : Not assigned by regulation
Labels : Flammable Gas
Packing instruction (cargo aircraft) : 203
Packing instruction (passenger aircraft) : 203

IMDG-Code

UN number : UN 1950
Proper shipping name : AEROSOLS
((R)-p-mentha-1,8-diene, Hydrocarbons, C7, n-alkanes, isookanes, cyclics)
Class : 2.1
Packing group : Not assigned by regulation
Labels : 2.1
EmS Code : F-D, S-U
Marine pollutant : yes

Transport in bulk according to IMO instruments

Not applicable for product as supplied.

Special precautions for user

The transport classification(s) provided herein are for informational purposes only, and solely based upon the properties of the unpackaged material as it is described within this Safety Data Sheet. Transportation classifications may vary by mode of transportation, package sizes, and variations in regional or country regulations.

15. REGULATORY INFORMATION

Safety, health and environmental regulations/legislation specific for the substance or mixture

16. OTHER INFORMATION

Revision Date : 04/15/2025

Further information

Sources of key data used to compile the Safety Data Sheet : Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, <http://echa.europa.eu/>

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

Date format : dd.mm.yyyy

Full text of other abbreviations

SAFETY DATA SHEET

according to the Globally Harmonized System



Silicon Spray

Version	Revision Date:	SDS Number:	Date of last issue: 11/26/2024
9.0	04/15/2025	10633834-00016	Date of first issue: 03/01/2012

ACGIH : USA. ACGIH Threshold Limit Values (TLV)
ACGIH BEI : ACGIH - Biological Exposure Indices (BEI)

ACGIH / TWA : 8-hour, time-weighted average
ACGIH / STEL : Short-term exposure limit

AIIIC - Australian Inventory of Industrial Chemicals; ANTT - National Agency for Transport by Land of Brazil; ASTM - American Society for the Testing of Materials; bw - Body weight; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; Nch - Chilean Norm; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NOM - Official Mexican Norm; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TDG - Transportation of Dangerous Goods; TECI - Thailand Existing Chemicals Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative; WHMIS - Workplace Hazardous Materials Information System

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

LK / EN